



形状: RB

形状: B

共通仕様	
精度等級	JIS N8級(旧JIS4級)
歯形	並歯
圧力角	20°
材料	S45C相当

※黒染処理は施していません

カタログ品番	モジュール	歯数	形状	基準円直径 PCD	歯先円直径 OD	ボス径 BD	歯幅 W	ボス長さ BW	ボス全長 BL	穴径 d	質量 kg
MSB1.5-12	モジュール 1.5	12	RB	18	21	21	15	15	30	6	0.06
MSB1.5-13		13	RB	19.5	22.5	22.5	15	15	30	6	0.072
MSB1.5-14		14	B	21	24	16	15	10	25	6	0.048
MSB1.5-15		15	B	22.5	25.5	18	15	10	25	6	0.058
MSB1.5-16		16	B	24	27	20	15	10	25	6	0.069
MSB1.5-17		17	B	25.5	28.5	21	15	10	25	6	0.078
MSB1.5-18		18	B	27	30	22	15	10	25	6	0.088
MSB1.5-19		19	B	28.5	31.5	23	15	10	25	6	0.1
MSB1.5-20		20	B	30	33	24	15	10	25	6	0.12
MSB1.5-21		21	B	31.5	34.5	25	15	10	25	6	0.13
MSB1.5-22		22	B	33	36	26	15	10	25	6	0.13
MSB1.5-23		23	B	34.5	37.5	27	15	10	25	6	0.15
MSB1.5-24		24	B	36	39	28	15	10	25	6	0.17
MSB1.5-25		25	B	37.5	40.5	30	15	10	25	6	0.19
MSB1.5-26		26	B	39	42	32	15	10	25	8	0.2
MSB1.5-27		27	B	40.5	43.5	34	15	10	25	8	0.22
MSB1.5-28		28	B	42	45	36	15	10	25	8	0.24
MSB1.5-29		29	B	43.5	46.5	37	15	10	25	8	0.25
MSB1.5-30		30	B	45	48	38	15	10	25	8	0.27
MSB1.5-32		32	B	48	51	40	15	10	25	8	0.31
MSB1.5-34		34	B	51	54	40	15	10	25	8	0.33
MSB1.5-35		35	B	52.5	55.5	42	15	10	25	8	0.36
MSB1.5-36		36	B	54	57	45	15	10	25	8	0.39
MSB1.5-38		38	B	57	60	45	15	10	25	10	0.41
MSB1.5-40		40	B	60	63	45	15	10	25	10	0.45
MSB1.5-42		42	B	63	66	45	15	10	25	10	0.48
MSB1.5-44		44	B	66	69	45	15	10	25	10	0.52
MSB1.5-45		45	B	67.5	70.5	45	15	10	25	10	0.53
MSB1.5-46		46	B	69	72	45	15	10	25	10	0.55
MSB1.5-48		48	B	72	75	45	15	10	25	10	0.59
MSB1.5-50		50	B	75	78	45	15	10	25	10	0.63
MSB1.5-52		52	B	78	81	50	15	10	25	13	0.69
MSB1.5-54	54	B	81	84	50	15	10	25	13	0.74	
MSB1.5-55	55	B	82.5	85.5	50	15	10	25	13	0.76	
MSB1.5-56	56	B	84	87	50	15	10	25	13	0.78	
MSB1.5-58	58	B	87	90	50	15	10	25	13	0.83	
MSB1.5-60	60	B	90	93	50	15	10	25	13	0.88	
MSB1.5-62	62	B	93	96	55	15	10	25	13	0.96	
MSB1.5-64	64	B	96	99	55	15	10	25	13	1.01	
MSB1.5-65	65	B	97.5	100.5	55	15	10	25	13	1.04	
MSB1.5-66	66	B	99	102	55	15	10	25	13	1.07	
MSB1.5-68	68	B	102	105	55	15	10	25	13	1.12	
MSB1.5-70	70	B	105	108	55	15	10	25	13	1.18	
MSB1.5-72	72	B	108	111	55	15	10	25	13	1.24	
MSB1.5-75	75	B	112.5	115.5	60	15	10	25	13	1.38	
MSB1.5-76	76	B	114	117	60	15	10	25	13	1.41	
MSB1.5-80	80	B	120	123	60	15	10	25	13	1.54	

※ご要望に応じた、軸穴加工、キー加工、止めねじ加工を承ります。別途、お問い合わせください。