



SANKO M25 スプロケット

(単位:mm)



A 型 (SS400)
酸洗材



B 型
(機械構造用炭素鋼)

歯数	外径 O.D.	ピッチ径 P.C.D.	B 型					A 型			
			軸孔径B		ボス		概略 重量 kg	材質	軸孔径 B	概略 重量 kg	材質
			下孔	最大	径B.D	長さB.L					
9	21	18.57	6	7	12	15	0.02	6	0.005	SS400	
10	24	20.55	6	8	14	15	0.02	6	0.006		
11	26	22.54	6	8	16	15	0.03	6	0.007		
12	28	24.53	6	9	18	15	0.03	6	0.008		
13	30	26.53	6	10	20	20	0.04	6	0.01		
14	32	28.54	6	10	20	20	0.05	6	0.01		
15	34	30.54	6	10	20	20	0.05	6	0.01		
16	36	32.55	8	14	25	20	0.06	6	0.02		
17	38	34.56	8	14	25	20	0.07	6	0.02		
18	40	36.57	8	14	25	20	0.07	6	0.02		
19	42	38.58	8	16	25	20	0.08	6	0.03		
20	44	40.59	8	16	25	20	0.08	6	0.03		
21	46	42.61	8	16	30	20	0.12	6	0.03		
22	48	44.62	8	16	30	20	0.12	8	0.03		
23	50	46.63	8	16	30	20	0.12	8	0.04		
24	52	48.65	8	16	30	20	0.13	8	0.04		
25	54	50.66	8	20	35	20	0.16	8	0.04		
26	56	52.68	8	20	40	20	0.20	8	0.05		
27	58	54.70	8	20	40	20	0.21	8	0.05		
28	60	56.71	8	20	40	20	0.21	8	0.05		
29	62	58.73	8	20	45	25	0.32	8	0.06		
30	64	60.75	8	20	45	25	0.33	10	0.06		
31	66	62.77	10	22	45	25	0.34	10	0.06		
32	68	64.78	10	22	50	25	0.40	10	0.07		
33	70	66.80	10	22	50	25	0.40	10	0.07		
34	72	68.82	10	22	50	25	0.40	10	0.08		
35	74	70.84	10	22	50	25	0.40	10	0.08		
36	76	72.86	10	22	50	25	0.40	10	0.09		
37	78	74.88	10	22	50	25	0.42	10	0.09		
38	80	76.90	10	22	50	25	0.42	10	0.09		
39	82	78.91	10	22	50	25	0.43	10	0.10		
40	84	80.93	10	22	50	25	0.43	10	0.11		
41	86	82.95	10	30	50	25	0.43	10	0.11		
42	89	84.97	10	30	50	25	0.44	10	0.12		
43	91	86.99	10	30	50	25	0.44	10	0.12		
44	93	89.01	10	30	50	25	0.45	10	0.13		
45	95	91.03	10	30	50	25	0.46	10	0.14		
46	97	93.05	10	30	50	25	0.47	10	0.14		
47	99	95.07	10	30	50	25	0.47	10	0.16		
48	101	97.09	10	30	50	25	0.48	10	0.16		
50	105	101.13	10	30	50	25	0.50	10	0.17		
54	113	109.21	10	30	50	25	0.52	10	0.20		
60	125	121.33	10	30	50	30	0.65	10	0.25		
65	135	131.43	12	30	50	30	0.69	10	0.29		
70	145	141.54	12	30	50	30	0.75	10	0.35		
75	155	151.64	12	30	50	30	0.79	12	0.39		
80	165	161.74	12	30	50	30	0.83	12	0.43		

機械構造用
炭素鋼

○A・B共歯先硬化は施していません。