





天びん・はかり セレクションガイド

● 分銅内蔵 ● 防塵・防水 ● 分銅内蔵&防塵・防水

ひょう量 最小表示	300 g未満	300 g以上、1 kg未満	1 kg以上、5 kg未満	5 kg以上、10 kg未満	10 kg以上														
1 μg (0.001 mg)	<ul style="list-style-type: none"> ● BA-6 ¥1,000,000~ ¥1,300,000 ● BM-5 ¥800,000 ● BM-20 ¥800,000 ● BM-22 ¥700,000 5.1 g/1 μg 22g/10 μg ● BM-5D ¥600,000 2.1 g/1 μg 5.2 g/10 μg 																		
	 <p>BA-T</p>					<p>凡例：</p> <table border="1"> <tr> <td>型名</td> <td>定価(税抜)</td> </tr> <tr> <td>● BM-20</td> <td>¥800,000</td> </tr> <tr> <td>● BM-22</td> <td>¥700,000</td> </tr> <tr> <td>5.1 g/1 μg</td> <td></td> </tr> <tr> <td>22 g/10 μg</td> <td></td> </tr> <tr> <td>...</td> <td>...</td> </tr> <tr> <td colspan="2">マルチレンジの型名</td> </tr> </table>	型名	定価(税抜)	● BM-20	¥800,000	● BM-22	¥700,000	5.1 g/1 μg		22 g/10 μg		マルチレンジの型名
型名	定価(税抜)																		
● BM-20	¥800,000																		
● BM-22	¥700,000																		
5.1 g/1 μg																			
22 g/10 μg																			
...	...																		
マルチレンジの型名																			
10 μg (0.01 mg)	<ul style="list-style-type: none"> ● BA-125/225 ¥350,000~ ¥700,000 ● BM-252 ¥450,000 ● GH-252 ¥280,000 101 g/10 μg 250 g/0.1 mg ● GH-202 ¥260,000 51 g/10 μg 220 g/0.1 mg ● GR-202 ¥240,000 42 g/10 μg 210 g/0.1 mg HR-202i ¥228,000 51 g/10 μg 220 g/0.1 mg 																		
	 <p>GR</p>																		
0.1 mg (0.0001 g)	<ul style="list-style-type: none"> ● BM-200 ¥320,000 ● GH-200 ¥199,000 ● GH-120 ¥179,000 ● GR-200 ¥179,000 ● GR-120 ¥159,000 ● GR-60 ¥139,000 ● HR-250AZ ¥148,000 ● HR-150AZ ¥138,000 ● HR-100AZ ¥128,000 ● HR-251AZ ¥128,000 62 g/0.1 mg、252 g/1 mg HR-250A ¥138,000 HR-150A ¥128,000 HR-100A ¥118,000 HR-251A ¥118,000 62 g/0.1 mg、252 g/1 mg ● GX-124A~ ¥150,000~ 224AE ¥250,000 GF-224A ¥150,000 GF-12 4A ¥140,000 EJ-54D2B(0.2 mg) ¥54,800 	<ul style="list-style-type: none"> ● BM-500 ¥420,000 ● BM-300 ¥370,000 ● GH-300 ¥249,000 ● GR-300 ¥229,000 HR-300i ¥225,000 ● GX-324AE ¥270,000 ● GX-324A ¥190,000 GF-324A ¥170,000 	<ul style="list-style-type: none"> ● MC-1000 ¥300,000 																
	 <p>GX-A</p>																		
1 mg (0.001 g)	<ul style="list-style-type: none"> ● GX-203A ¥99,000 ● GX-203AWP ¥119,000 GF-203A ¥84,000 ● GF-203AWP ¥109,000 ● FX-200iWP ¥94,000 ● FX-120iWP ¥79,000 ● FZ-200i ¥84,000 ● FZ-120i ¥79,000 FX-200i ¥64,000 FX-120i ¥59,000 EJ-123B ¥49,800 	<ul style="list-style-type: none"> ● GX-303A~ ¥124,000~ 603A ¥160,000 ● GX-403AWP~ ¥150,000~ 603AWP ¥170,000 GF-303A~ ¥99,000~ 603A ¥139,000 ● GF-403AWP~ ¥139,000~ 603AWP ¥149,000 ● FZ-300iWP ¥119,000 ● FX-300iWP ¥99,000 ● FZ-500i ¥99,000 ● FZ-300i ¥89,000 FX-500i ¥79,000 FX-300i ¥69,000 EJ-303B ¥51,800 	<ul style="list-style-type: none"> ● GX-1603A ¥220,000 ● GX-1003A ¥190,000 GF-1603A ¥199,000 GF-1003A ¥169,000 	<ul style="list-style-type: none"> ● MC-6100 ¥300,000 ● MC-10K ¥400,000 															
	 <p>GX-M</p>																		
10 mg (0.01 g)	<ul style="list-style-type: none"> EK-200i ¥41,800 EK-120i ¥41,800 EJ-200B ¥30,800 EJ-120B ¥29,800 EW-150i ¥29,800 30 g/0.01 g 60 g/0.02 g 150 g/0.05 g HT-120 ¥22,000 	<ul style="list-style-type: none"> EK-610i ¥49,800 EK-410i ¥41,800 EK-300i ¥41,800 EJ-610B ¥45,800 EJ-410B ¥35,800 EJ-300B ¥31,800 	<ul style="list-style-type: none"> ● GX-2002A ~ ¥99,000~ 4002A ¥140,000 GF-2002A ~ ¥84,000~ 4002A ¥129,000 ● GX-2002AWP ¥119,000 ● GX-4002AWP ¥150,000 ● GF-2002AWP ¥109,000 ● GF-4002AWP ¥139,000 ● FZ-1200iWP~ ¥99,000~ 3000iWP ¥119,000 ● FX1200iWP~ ¥79,000~ 3000iWP ¥99,000 ● FZ-1200i~3000i ¥79,000~ ¥89,000 FX-1200i~3000i ¥59,000~ ¥69,000 EJ-1202B ¥49,800 EJ-3002B ¥51,600 	<ul style="list-style-type: none"> ● GX-6002A~ ¥160,000~ 10002A ¥180,000 GF-6002A~ ¥145,000~ 10002A ¥165,000 ● GX-6002AWP ¥170,000 ● GF-6002AWP ¥155,000 ● FZ-5000i ¥99,000 FX-5000i ¥79,000 ● GX-8202M ¥200,000 ● GX-8202MD ¥160,000 0.01 g(0~2.2 kg) 0.1 g(2.2~8.2 kg) ● GF-8202M ¥185,000 ● GF-8202MD ¥145,000 0.01 g(0~2.2 kg) 0.1 g(2.2~8.2 kg) 	<ul style="list-style-type: none"> ● MC-30K ¥400,000 ● GX-10002A ¥180,000 GF-10002A ¥165,000 ● GX-10202M ¥240,000 ● GF-10202M ¥225,000 														

※価格は標準価格(税抜)です。