

材質

SUS304WPB**E541~E580**

RoHS指令適合品

製品番号 Part No.	基準荷重 (P1) N	荷重長さ (L1) mm	許容荷重 (P2) N	許容荷重時 長さ (L2) mm	ばね定数 (k) N/mm	自由長さ (Lf) mm	線径 (d) mm	外径 (OD) mm	総巻数 (Nt)	初張力 (Pi) N	1袋内 個数 個	1袋価格 円
E541	0.93	11.3	1.52	14.1	0.218	8.6	0.26	2.5	15.5	0.333	20	1,500
E542	0.93	15.2	1.52	19.5	0.140	11.0	0.26	2.5	24.5	0.333	20	1,500
E543	0.93	21.7	1.52	28.5	0.087	14.9	0.26	2.5	39.5	0.333	20	1,500
E544	0.93	31.5	1.52	42.1	0.056	20.9	0.26	2.5	62.5	0.333	20	1,500
E545	0.98	14.9	1.62	19.0	0.154	10.5	0.29	3.2	15.5	0.304	20	1,500
E546	0.98	20.0	1.62	26.5	0.099	13.2	0.29	3.2	24.5	0.304	20	1,500
E547	0.98	28.5	1.62	38.8	0.062	17.5	0.29	3.2	39.5	0.304	20	1,500
E548	0.98	41.5	1.62	57.7	0.039	24.2	0.29	3.2	62.5	0.304	20	1,500
E549	0.98	18.9	1.72	25.4	0.114	12.7	0.32	4.0	15.5	0.275	20	1,500
E550	0.98	25.3	1.72	35.5	0.073	15.6	0.32	4.0	24.5	0.275	20	1,500
E551	0.98	36.1	1.72	52.4	0.045	20.4	0.32	4.0	39.5	0.275	20	1,500
E552	0.98	52.5	1.72	78.4	0.028	27.7	0.32	4.0	62.5	0.275	20	1,500
E553	0.98	24.7	1.77	34.6	0.079	15.2	0.35	5.0	15.5	0.226	20	1,500
E554	0.98	32.9	1.77	48.0	0.052	18.4	0.35	5.0	24.5	0.226	20	1,500
E555	0.98	47.7	1.77	72.7	0.031	23.6	0.35	5.0	39.5	0.226	20	1,500
E556	0.98	68.4	1.77	106.5	0.021	31.7	0.35	5.0	62.5	0.226	20	1,500
E557	1.18	32.7	2.06	45.9	0.067	18.7	0.40	6.3	15.5	0.245	20	1,500
E558	1.18	43.9	2.06	64.4	0.043	22.3	0.40	6.3	24.5	0.245	20	1,500
E559	1.18	63.5	2.06	96.8	0.026	28.3	0.40	6.3	39.5	0.245	20	1,500
E560	1.18	90.3	2.06	140.3	0.018	37.5	0.40	6.3	62.5	0.245	20	1,500
E561	1.37	18.8	2.26	24.1	0.166	13.0	0.35	4.0	15.5	0.412	20	1,500
E562	1.37	25.3	2.26	33.6	0.106	16.2	0.35	4.0	24.5	0.412	20	1,500
E563	1.37	36.0	2.26	49.5	0.066	21.4	0.35	4.0	39.5	0.412	20	1,500
E564	1.37	52.3	2.26	73.2	0.042	29.5	0.35	4.0	62.5	0.412	20	1,500
E565	1.37	11.4	2.16	13.7	0.352	9.0	0.29	2.5	15.5	0.520	20	1,500
E566	1.37	15.4	2.16	18.9	0.225	11.6	0.29	2.5	24.5	0.520	20	1,500
E567	1.37	22.0	2.16	27.6	0.141	16.0	0.29	2.5	39.5	0.520	20	1,500
E568	1.37	32.2	2.16	41.0	0.089	22.6	0.29	2.5	62.5	0.520	20	1,500
E569	1.37	14.7	2.21	18.3	0.235	10.9	0.32	3.2	15.5	0.471	20	1,500
E570	1.37	19.8	2.21	25.3	0.151	13.8	0.32	3.2	24.5	0.471	20	1,500
E571	1.37	28.2	2.21	37.0	0.094	18.6	0.32	3.2	39.5	0.471	20	1,500
E572	1.37	41.1	2.21	55.0	0.060	26.0	0.32	3.2	62.5	0.471	20	1,500
E573	1.57	23.8	2.65	31.4	0.141	15.8	0.40	5.0	15.5	0.441	20	1,500
E574	1.57	31.9	2.65	43.9	0.090	19.4	0.40	5.0	24.5	0.441	20	1,500
E575	1.57	45.2	2.65	64.2	0.057	25.4	0.40	5.0	39.5	0.441	20	1,500
E576	1.57	65.7	2.65	95.4	0.036	34.6	0.40	5.0	62.5	0.441	20	1,500
E577	1.67	30.7	2.94	42.3	0.110	19.3	0.45	6.3	15.5	0.412	20	1,500
E578	1.67	41.2	2.94	59.2	0.071	23.4	0.45	6.3	24.5	0.412	20	1,500
E579	1.67	58.5	2.94	87.4	0.044	30.1	0.45	6.3	39.5	0.412	20	1,500
E580	1.67	84.6	2.94	129.5	0.028	40.5	0.45	6.3	62.5	0.412	10	1,500

●ご注文例：製品番号をご指定ください。 C101

●仕様は予告なく変更する場合があります。 ●必要数量が多い場合には別冊のロット別価格表をご覧ください。