

Specifications

Function			CS1762A	CS1764A	
Computer Connections			2	4	
Port Selection			Front Panel Pushbuttons; Hotkey		
Connectors	Console Ports	KB	1 x USB Type A F (White; front panel)	1 x USB Type A F (Black; rear panel)	
		Video	1 x DVI-I F (white)		
		Mouse	1 x USB Type A F (white; front panel)	1 x USB Type A F (Black; rear panel)	
		Speakers	1 x Mini Stereo Jack F (Green; rear panel)	2 x Mini Stereo Jack F (Green; 1 x front panel, 1 x rear panel)	
		Mic.	1 x Mini Stereo Jack F (Pink; rear panel)	2 x Mini Stereo Jack F (Pink; 1 x front panel, 1 x rear panel)	
	KVM Ports	KB/ Mouse	2 x USB Type B F (White)	4 x USB Type B F (White)	
		Video	2 x DVI-I F (White)	4 x DVI-I F (White)	
		Speakers	2 x Mini Stereo Jack F (Green)	4 x Mini Stereo Jack F (Green)	
		Mic.	2 x Mini Stereo Jack F (Pink)	2 x Mini Stereo Jack F (Pink)	
	Power		1 x DC Jack	1 x DC Jack	
USB Hub		2 x USB Type A F (Black, rear panel)	2 x USB Type A F (White; 1 x front panel, 1 x rear panel)		
Switches	Selected	2 x Pushbutton	4 x Pushbutton		
LEDs	On Line / Selected	2 (Orange)	4 (Orange)		
	USB Link	2 (Green)	4 (Green)		
Emulation	KB / Mouse	USB			
Video			1920 x 1200		
Scan Interval			1–99 secs. (5 secs. default)		
Power Consumption			DC 5.3V, 9.0 W	DC 5.3V, 10.7 W	