

GKS 100

ピッチ100mil、先端形状・バネ圧等豊富なラインナップ

- ・ フラックスがたまりにくい、セルフクリーニングタイプあり
- ・ -100℃～200℃と広範囲の温度下で使用可能なタイプあり

プローブ型番の見方

※赤字はこのシリーズ固定

GKS-100

3

07

150

A

30

00

L,E,C

シリーズ名
GKS-100

先端材質 先端形状
2=スチール
3=ベリ銅

直径
1.50mm
→150

表面処理
金メッキ
→A(F)






ばね圧
3.0N
→30

カラーの高さ
00


オプション
全長 L/Long E/Extra Long
高低温 C/ばね圧1.5N, 2N, 3Nのみ
LC/詳細はP11 メカニカルデータ参照

GKS-100

100mil=2.54mm ピッチ

先端外観	プローブ型番		
	先端材質	先端形状	直径mm(型番)
	GKS-100-006-225-A-△△00-◇		
	0	06	2.25(225)
	GKS-100-006-323-A-△△00-◇		
	0	06	3.23(323)
	GKS-100-201-090-A-△△00-◇		
	2	01	0.90(090)
	GKS-100-302-□□□-A-△△00-◇		
	3	02	0.90(090) 1.50(150)
	GKS-100-303-150-A-△△00-◇		
	3	03	1.50(150)
	GKS-100-204-106-A-△△00-◇		
	2	04	1.06(106)
	GKS-100-204-□□□-A-△△00-◇		
	2	04	1.30(130) 1.50(150)
	GKS-100-305-□□□-A-△△00-◇		
	3	05	0.50(050) 0.64(064) 0.90(090) 1.30(130)
	GKS-100-306-□□□-A-△△00-◇		
	3	06	1.30(130) 1.50(150) 2.00(200) 2.50(250) 3.00(300)
	GKS-100-307-090-A-△△00-◇		
	3	07	0.90(090)
	GKS-100-307-□□□-A-△△00-◇		
	3	07	1.50(150) 1.70(170) 2.50(250)
	GKS-100-209-060-A-△△00-◇		
	2	09	0.60(060)
	GKS-100-313-090-A-△△00-◇		
	3	13	0.90(090)
	GKS-100-214-□□□-A-△△00-◇		
	2	14	0.50(050) 0.80(080)
	GKS-100-214-106-A-△△00-◇		
	2	14	1.06(106)
	GKS-100-214-□□□-A-△△00-◇		
	2	14	1.30(130) 1.50(150)

注1:標準品より0.5または0.9mm長くなります
注2:ばね圧は2.0Nのみ
注3:中央先端は標準品より0.4mm長くなります
注4:最大ストローク4.7mm
注5:標準品より5mm長くなります

先端外観	プローブ型番		
	先端材質	先端形状	直径mm(型番)
	GKS-100-314-130-A-△△00-◇		
	3	14	1.30(130)
	GKS-100-217-170-A-△△00-◇		
	2	17	1.70(170)
	GKS-100-319-180-A-△△00-◇		
	3	19	1.80(180)
	GKS-100-219-180-F-1001		
	2	19	1.80(180)
	GKS-100-224-□□□-A-△△00-◇		
	2	24	1.30(130) 1.50(150)
	GKS-100-225-□□□-A-△△00-◇		
	2	25	1.30(130) 1.50(150)
	GKS-100-231-090-A-△△00-◇		
	2	31	0.90(090)
	GKS-100-233-106-A-△△00-◇		
	2	33	1.06(106)
	GKS-100-238-090-A-△△00-◇		
	2	38	0.90(090)
	GKS-100-355-064-A-△△00-◇		
	3	55	0.64(064)
	GKS-100-277-090-A-△△00-◇		
	2	77	0.90(090)
	GKS-100-288-□□□-A-△△00-◇		
	2	88	1.50(150) 1.90(190)
	GKS-100-289-050-A-△△00-◇		
	2	89	0.50(050)
	GKS-100-291-090-A-△△00-◇		
	2	91	0.90(090)
	GKS-100-291-130-A-△△00-◇		
	2	91	1.30(130)
	GKS-100-293-160-A-△△00-◇		
	2	93	1.60(160)
	GKS-100-297-090-A-△△00-◇		
	2	97	0.90(090)
	GKS-100-298-090-A-△△00-◇		
	2	98	0.90(090)