

ウィングポンプシリーズ仕様表

■ 灯油・軽油・オイル □ 水

画像																									
シリーズ	YATSUNAMI						KING						HWA												
油用型式 (5,000cP以下)	No.0-15	No.1-20	No.2-25	No.3-32	No.5-40	No.7-50	No.0-15	No.1-20	No.2-25	No.3-32	No.5-40	No.7-50	-												
接液部材質	本体:FC 要部:CAC ハンドル:AL パッキン:NBR(ノンアスベスト)												-												
重量(kg)	5.3		7.2		8.9		13.6		22.3		4.4		6.0		7.8		11.0		19.0						
水用型式	BC-No.0	BC-No.1	BC-No.2	BC-No.3	BC-No.5	BC-No.7							HWA-0	HWA-2											
接液部材質	本体要部:CAC/SUS ハンドル:AL パッキン:PTFE/NBR(ノンアスベスト)												-												
重量(kg)	5.5		7.4		9.5		15.0		24.6				2.5		3.4										
吐出量(cc/1ストローク)	240		400		650		1100		2000		175		240		400		650		1100		240		400		
接続フランジ (相フランジ付/HWA除く)	Rc1/2 (15A)	Rc3/4 (20A)	Rc1 (25A)	Rc1*1/4 (32A)	Rc1*1/2 (40A)	Rc2 (50A)	Rc1/2 (15A)	Rc3/4 (20A)	Rc1 (25A)	Rc1*1/4 (32A)	Rc1*1/2 (40A)	Rc2 (50A)	Rc1/2 (15A)	Rc3/4 (20A)											
図面 本体寸法	A	180		208		245		295		329		180		203		232		265		312		55		70	
	B	132		146		168		198		235		126		137		155		168		197		60		70	
	C	165		177		204		235		282		153		170		190		211		234		102		120	
	D	330		365		400		460		600		330		360		400		460		600		365		400	
	E	135		145		179		195		225		131		141		165		183		215		94		104	
	F	67		75		95		103		115		64		71		75		95		103		88		98	

画像																					
シリーズ	YATSUNAMI																				
油用型式 (5,000cP以下)	5K-15	5K-20	5K-25	5K-32	5K-40	5K-50	10K-15	10K-20	10K-25	10K-32	10K-40	10K-50									
接液部材質	本体:FC 要部:CAC ハンドル:AL パッキン:NBR(ノンアスベスト)																				
重量(kg)	5.9		7.6		10.5		13.6		20.7		6.6		9.0		11.5		14.6		20.7		
水用型式	BC5K-15	BC5K-20	BC5K-25	BC5K-32	BC5K-40	BC5K-50	BC10K-15	BC10K-20	BC10K-25	BC10K-32	BC10K-40	BC10K-50									
接液部材質	本体要部:CAC/SUS ハンドル:AL パッキン:PTFE/NBR(ノンアスベスト)																				
重量(kg)	6.1		7.9		11.2		15.0		22.8		6.8		9.3		13.0		17.5		25.0		
吐出量(cc/1ストローク)	240		400		650		1100		2000		240		400		650		1100		2000		
接続フランジ径 (丸型溶接)	JIS5K-15A	JIS5K-20A	JIS5K-25A	JIS5K-32A	JIS5K-40A	JIS5K-50A	JIS10K-15A	JIS10K-20A	JIS10K-25A	JIS10K-32A	JIS10K-40A	JIS10K-50A									
図面 本体寸法	A	194		210		248		293		329		200		220		250		298		330	
	B	132		146		168		198		235		132		146		168		198		235	
	C	165		177		204		235		282		165		177		204		235		282	
	D	330		365		400		460		600		330		365		400		460		600	
	E	135		145		165		195		225		135		145		165		195		225	
	F	70		75		93		100		115		70		75		93		100		115	

