

リングエルボ

C3604/C3771



RoHS指令相当品

品番	寸法(外ネジ×パイプ径(ナットのネジ))	価格	入数
RL-1104	PT1/8×φ4 (PF1/8)	500	200
RL-1105	φ5	500	200
RL-1106	φ6	500	200
RL-1102	φ6.35 (PF1/4)	700	100
RL-1108	φ8	700	100
RL-1103	φ9.53 (PF3/8)	1,100	50
RL-1110	φ10	1,100	50
RL-1206	PT1/4×φ6 (PF1/4)	700	75
RL-1202	φ6.35	700	75
RL-1208	φ8	700	75
RL-1203	φ9.53 (PF3/8)	1,050	50
RL-1210	φ10	1,050	50
RL-1212	φ12 (PF1/2)	1,680	35
RL-1204	φ12.7	1,680	35
RL-1306	PT3/8×φ6 (PF1/4)	880	50
RL-1302	φ6.35	880	50
RL-1308	φ8	880	50
RL-1303	φ9.53 (PF3/8)	1,000	50
RL-1310	φ10	1,000	50
RL-1312	φ12 (PF1/2)	1,560	25
RL-1304	φ12.7	1,560	25
RL-1315	φ15 (PF5/8)	2,900	20
RL-1305	φ15.88	2,900	20
RL-1406	PT1/2×φ6 (PF1/4)	1,450	35
RL-1402	φ6.35	1,450	35
RL-1408	φ8	1,450	35
RL-1403	φ9.53 (PF3/8)	1,500	35
RL-1410	φ10	1,500	35
RL-1412	φ12 (PF1/2)	1,600	30
RL-1404	φ12.7	1,600	30
RL-1415	φ15 (PF5/8)	2,580	20
RL-1405	φ15.88	2,580	20
RL-1460	φ19.05 (PF3/4)	4,000	15
RL-1612	PT3/4×φ12 (PF1/2)	4,000	15
RL-1604	φ12.7	4,000	15
RL-1615	φ15 (PF5/8)	4,000	15
RL-1605	φ15.88	4,000	15
RL-1606	φ19.05 (PF3/4)	4,200	15

品番	価格
RL-1106R	660
RL-1108R	860
RL-1206R	860
RL-1208R	860
RL-1210R	1,200
RL-1212R	1,950
RL-1308R	1,130
RL-1310R	1,230
RL-1312R	2,000
RL-1406R	1,900
RL-1408R	1,900
RL-1412R	2,000

両口リングエルボ

C3604/C3771



RoHS指令相当品

品番	寸法(パイプ径(ナットのネジ))	価格	入数
RL-2104	φ4 (PF1/8)	700	150
RL-2105	φ5	700	150
RL-2106	φ6	700	150
RL-2206	φ6 (PF1/4)	800	60
RL-2202	φ6.35	800	60
RL-2208	φ8	800	60
RL-2303	φ9.53 (PF3/8)	1,250	30
RL-2310	φ10	1,250	30
RL-2412	φ12 (PF1/2)	1,900	25
RL-2404	φ12.7	1,900	25
RL-2515	φ15 (PF5/8)	3,500	15
RL-2505	φ15.88	3,500	15
RL-2606	φ19.05 (PF3/4)	5,500	10

品番	価格
RL-2106R	950
RL-2208R	1,080
RL-2310R	1,560
RL-2412R	2,400