

Fittings

フレアジョイント

C3604



品番	寸法(外ネジ×パイプ径)	価格	入数
FS-1106	PT1/8×φ6	300	130
FS-1102	φ6.35	300	130
FS-1108	φ8	310	100
FS-1103	φ9.53	490	70
FS-1110	φ10	490	70
FS-1206	PT1/4×φ6	305	100
FS-1202	φ6.35	305	100
FS-1208	φ8	310	100
FS-1203	φ9.53	490	70
FS-1210	φ10	490	70
FS-1212	φ12	760	40
FS-1204	φ12.7	760	40
FS-1306	PT3/8×φ6	390	85
FS-1302	φ6.35	390	85
FS-1308	φ8	400	85
FS-1303	φ9.53	490	60
FS-1310	φ10	490	60
FS-1312	φ12	760	40
FS-1304	φ12.7	760	40
FS-1315	φ15	1,500	30
FS-1305	φ15.88	1,500	30
FS-1406	PT1/2×φ6	640	50
FS-1402	φ6.35	640	50
FS-1408	φ8	650	50
FS-1403	φ9.53	730	40
FS-1410	φ10	730	40
FS-1412	φ12	780	40
FS-1404	φ12.7	780	40
FS-1415	φ15	1,600	25
FS-1405	φ15.88	1,600	25
FS-1615	PT3/4×φ15	1,900	20
FS-1605	φ15.88	1,900	20
FS-1606	φ19.05	2,200	15

フレアエルボ

C3604/C3771



品番	寸法(外ネジ×パイプ径)	価格	入数
FL-1106	PT1/8×φ6	650	100
FL-1102	φ6.35	650	100
FL-1108	φ8	660	80
FL-1103	φ9.53	980	50
FL-1110	φ10	980	50
FL-1206	PT1/4×φ6	650	75
FL-1202	φ6.35	650	75
FL-1208	φ8	660	75
FL-1203	φ9.53	980	50
FL-1210	φ10	980	50
FL-1212	φ12	1,600	30
FL-1204	φ12.7	1,600	30
FL-1306	PT3/8×φ6	900	60
FL-1302	φ6.35	900	60
FL-1308	φ8	900	50
FL-1303	φ9.53	980	40
FL-1310	φ10	980	40
FL-1312	φ12	1,600	30
FL-1304	φ12.7	1,600	30
FL-1406	PT1/2×φ6	1,400	40
FL-1402	φ6.35	1,400	40
FL-1408	φ8	1,400	40
FL-1403	φ9.53	1,500	30
FL-1410	φ10	1,500	30
FL-1412	φ12	1,560	30
FL-1404	φ12.7	1,560	30
FL-1415	φ15	3,500	20
FL-1405	φ15.88	3,500	20
FL-1615	PT3/4×φ15	4,500	15
FL-1605	φ15.88	4,500	15
FL-1606	φ19.05	4,800	12

両口フレアジョイント

C3604



品番	寸法(パイプ径)	価格	入数
FS-2006	φ6	500	75
FS-2022	φ6.35	500	75
FS-2008	φ8	520	75
FS-2033	φ9.53	770	50
FS-2010	φ10	770	50
FS-2012	φ12	1,120	30
FS-2044	φ12.7	1,120	30
FS-2015	φ15	2,400	15
FS-2055	φ15.88	2,400	15
FS-2066	φ19.05	3,200	10

両口フレアエルボ

C3604/C3771



品番	寸法(パイプ径)	価格	入数
FL-2006	φ6	850	70
FL-2022	φ6.35	850	70
FL-2008	φ8	870	60
FL-2033	φ9.53	1,270	30
FL-2010	φ10	1,270	30
FL-2012	φ12	1,950	20
FL-2044	φ12.7	1,950	20
FL-2015	φ15	4,300	15
FL-2055	φ15.88	4,300	15
FL-2066	φ19.05	5,400	10