

## 三方フlea-チーズ

C3604/C3771



品番	寸法(パイプ径)	価格	入数
FT-3206	φ6	1,200	45
FT-3202	φ6.35	1,200	45
FT-3208	φ8	1,250	45
FT-3303	φ9.53	1,700	20
FT-3310	φ10	1,700	20
FT-3412	φ12	2,700	15
FT-3404	φ12.7	2,700	15
FT-3515	φ15	5,200	10
FT-3505	φ15.88	5,200	10
FT-3606	φ19.05	7,800	6

## ゲージフィッティング

C3604



品番	寸法(内ネジ×パイプ径)	価格	入数
FG-1206	PF1/4×φ6	660	80
FG-1202	φ6.35	660	80
FG-1208	φ8	670	80
FG-1203	φ9.53	800	60
FG-1210	φ10	800	60
FG-1306	PF3/8×φ6	750	50
FG-1302	φ6.35	750	50
FG-1308	φ8	760	50
FG-1303	φ9.53	800	50
FG-1310	φ10	800	50

## 内ネジ・フlea-ジョイント

C3604



品番	寸法(内ネジ×パイプ径)	価格	入数
FF-1106	PT1/8×φ6	650	100
FF-1102	φ6.35	650	100
FF-1108	φ8	660	100
FF-1206	PT1/4×φ6	660	80
FF-1202	φ6.35	660	80
FF-1208	φ8	670	80
FF-1203	φ9.53	800	60
FF-1210	φ10	800	60
FF-1306	PT3/8×φ6	750	50
FF-1302	φ6.35	750	50
FF-1308	φ8	760	50
FF-1303	φ9.53	800	50
FF-1310	φ10	800	50
FF-1312	φ12	1,820	40
FF-1304	φ12.7	1,820	40
FF-1408	PT1/2×φ8	1,800	40
FF-1403	φ9.53	1,820	35
FF-1410	φ10	1,820	35
FF-1412	φ12	1,850	35
FF-1404	φ12.7	1,850	35
FF-1415	φ15	3,800	30
FF-1405	φ15.88	3,800	30

## 二方フlea-チーズ

C3604/C3771



品番	寸法	価格	入数
FT-2106	PT1/8×φ6	1,020	60
FT-2102	φ6.35	1,020	60
FT-2108	φ8	1,040	50
FT-2206	PT1/4×φ6	1,020	50
FT-2202	φ6.35	1,020	50
FT-2208	φ8	1,040	50
FT-2203	φ9.53	1,560	25
FT-2210	φ10	1,560	25
FT-2306	PT3/8×φ6	1,370	40
FT-2302	φ6.35	1,370	40
FT-2308	φ8	1,380	40
FT-2303	φ9.53	1,560	25
FT-2310	φ10	1,560	25
FT-2312	φ12	2,450	20
FT-2304	φ12.7	2,450	20
FT-2403	PT1/2×φ9.53	2,350	15
FT-2410	φ10	2,350	15
FT-2412	φ12	2,450	15
FT-2404	φ12.7	2,450	15
FT-2415	φ15	4,200	10
FT-2405	φ15.88	4,200	10
FT-2606	PT3/4×φ19.05	5,000	8

## 異径両口フlea-ジョイント

C3604



品番	寸法(パイプ径)	価格	入数
FE-0602	φ6×φ6.35	630	75
FE-0608	φ8	640	75
FE-0603	φ9.53	1,100	50
FE-0610	φ10	1,100	50
FE-0208	φ6.35×φ8	640	75
FE-0203	φ9.53	1,100	50
FE-0210	φ10	1,100	50
FE-0803	φ8×φ9.53	1,100	50
FE-0810	φ10	1,100	50
FE-0310	φ9.53×φ10	1,200	50
FE-0312	φ12	1,900	35
FE-0304	φ12.7	1,900	35
FE-0315	φ15	2,500	
FE-0305	φ15.88	2,500	
FE-1012	φ10×φ12	1,900	30
FE-1004	φ12.7	1,900	30
FE-1015	φ15	2,500	
FE-1005	φ15.88	2,500	
FE-1204	φ12×φ12.7	1,900	30
FE-1215	φ15	2,300	20
FE-1205	φ15.88	2,300	20
FE-0415	φ12.7×φ15	2,300	20
FE-0405	φ15.88	2,300	20