

丸ニップル

C3604



RoHS 指令相当品

| 品番 | 寸法 | 価格 | 入数 | 品番 | 価格 |
|----------|-------|-------|-----|---------|-------|
| NI-1011R | PT1/8 | 330 | 400 | NI-1011 | 260 |
| NI-1022R | PT1/4 | 450 | 200 | NI-1022 | 340 |
| NI-1033R | PT3/8 | 560 | 100 | NI-1033 | 430 |
| NI-1044R | PT1/2 | 700 | 60 | NI-1044 | 540 |
| NI-1066R | PT3/4 | 1,100 | 35 | NI-1066 | 850 |
| NI-1088R | PT1 | 1,900 | 25 | NI-1088 | 1,500 |

六角ニップル

C3604



RoHS 指令相当品

| 品番 | 寸法 | 価格 | 入数 | 品番 | 価格 |
|----------|-------|-------|-----|---------|-------|
| NT-1011R | PT1/8 | 180 | 300 | NT-1011 | 140 |
| NT-1022R | PT1/4 | 260 | 150 | NT-1022 | 200 |
| NT-1033R | PT3/8 | 380 | 100 | NT-1033 | 300 |
| NT-1044R | PT1/2 | 700 | 50 | NT-1044 | 540 |
| NT-1066R | PT3/4 | 1,400 | 30 | NT-1066 | 1,100 |
| NT-1088R | PT1 | 2,400 | 15 | NT-1088 | 1,900 |

異径六角ニップル

C3604



RoHS 指令相当品

| 品番 | 寸法 | 価格 | 入数 | 品番 | 価格 |
|----------|-------------|-------|-----|---------|-------|
| NE-1012R | PT1/8×PT1/4 | 320 | 200 | NE-1012 | 250 |
| NE-1013R | PT3/8 | 420 | 100 | NE-1013 | 330 |
| NE-1023R | PT1/4×PT3/8 | 410 | 100 | NE-1023 | 320 |
| NE-1024R | PT1/2 | 680 | 60 | NE-1024 | 530 |
| NE-1034R | PT3/8×PT1/2 | 710 | 50 | NE-1034 | 550 |
| NE-1036R | PT3/4 | 1,350 | 30 | NE-1036 | 1,050 |
| NE-1046R | PT1/2×PT3/4 | 1,350 | 30 | NE-1046 | 1,050 |
| NE-1048R | PT1 | 2,800 | 20 | NE-1048 | 2,200 |
| NE-1068R | PT3/4×PT1 | 2,800 | 15 | NE-1068 | 2,200 |

クロス

C3771



RoHS 指令相当品

| 品番 | 寸法 | 価格 | 入数 |
|----------|-------|-------|----|
| KK-1111R | PT1/8 | 2,500 | 75 |
| KK-1222R | PT1/4 | 2,500 | 40 |
| KK-1333R | PT3/8 | 3,400 | 20 |