

## 内ネジエルボ

C3771



### RoHS 指令相当品

品番	寸法	価格	入数
LF-1011R	PT1/8	580	120
LF-1022R	PT1/4	850	75
LF-1033R	PT3/8	1,400	40
LF-1044R	PT1/2	2,500	20
LF-1066R	PT3/4	6,000	10

## 異径内ネジエルボ

C3771



### RoHS 指令相当品

品番	寸法	価格	入数
LF-1012R	PT1/8×PT1/4	920	75
LF-1023R	PT1/4×PT3/8	1,520	40
LF-1034R	PT3/8×PT1/2	2,700	20

## 内・外エルボ

C3771



### RoHS 指令相当品

品番	寸法	価格	入数
LK-1011R	PT1/8 (外) × PT1/8 (内)	580	125
LK-1022R	PT1/4 (外) × PT1/4 (内)	850	75
LK-1033R	PT3/8 (外) × PT3/8 (内)	1,400	50
LK-1044R	PT1/2 (外) × PT1/2 (内)	2,500	25
LK-1066R	PT3/4 (外) × PT3/4 (内)	6,000	10

## 異径内・外エルボ

C3771



### RoHS 指令相当品

品番	寸法	価格	入数
LK-1012R	PT1/8 (外) × PT1/4 (内)	920	75
LK-1021R	PT1/4 (外) × PT1/8 (内)	700	100
LK-1023R	PT3/8 (内)	1,520	40
LK-1032R	PT3/8 (外) × PT1/4 (内)	960	75
LK-1034R	PT1/2 (内)	2,700	20
LK-1043R	PT1/2 (外) × PT3/8 (内)	1,560	40

## 外ネジエルボ

C3771



### RoHS 指令相当品

品番	寸法	価格	入数
LM-1011R	PT1/8	420	250
LM-1022R	PT1/4	600	100
LM-1033R	PT3/8	850	80
LM-1044R	PT1/2	1,250	40
LM-1066R	PT3/4	2,600	20