

FEATURES

- 9 male copper-alloy contacts plated in gold
- Straight body orientation
- E-size waterproof D-Sub connector
- PBT housing material for insulation
- 5A current rating
- 1kVAC voltage rating
- Measures 40 mm x 21 mm x 67.5 mm
- Minimum operating temperature of -40°C
- Maximum operating temperature of +80°C

RS PRO 9 Way Cable Mount D-sub Connector Plug

RS Stock No.: 122-3044



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.