


Polyurethane Tube

PU



Metric Size

| MODEL | ØD | ØA | M | BOX(EA) | COLOR CODE |
|---------|------|------|------|---------|------------|
| PU 0320 | 3.0 | 2.0 | 200M | 6 | |
| PU 0420 | 4.0 | 2.0 | 200M | 6 | WT-White |
| PU 0425 | 4.0 | 2.5 | 200M | 6 | BK-Black |
| PU 0640 | 6.0 | 4.0 | 100M | 6 | RD-Red |
| PU 0850 | 8.0 | 5.0 | 100M | 6 | BU-Blue |
| PU 0855 | 8.0 | 5.5 | 100M | 6 | YL-Yellow |
| PU 1065 | 10.0 | 6.5 | 100M | 3 | GR-Green |
| PU 1280 | 12.0 | 8.0 | 100M | 3 | CL-Clear |
| PU 1290 | 12.0 | 9.0 | 100M | 3 | SL-Silver |
| PU 1612 | 16.0 | 12.0 | 100M | 3 | |



Inch Size

| MODEL | ØD | ØA | M | BOX(EA) | COLOR CODE |
|---------|------|------|------|---------|------------|
| PU 1/8 | 1/8 | 2.0 | 200M | 6 | WT-White |
| PU 5/32 | 5/32 | 2.5 | 200M | 6 | BK-Black |
| PU 3/16 | 3/16 | 3.0 | 100M | 6 | RD-Red |
| PU 1/4 | 1/4 | 4.15 | 100M | 6 | BU-Blue |
| PU 5/16 | 5/16 | 5.0 | 100M | 3 | YL-Yellow |
| PU 3/8 | 3/8 | 6.0 | 100M | 3 | GR-Green |
| PU 1/2 | 1/2 | 8.5 | 100M | 3 | CL-Clear |
| | | | | | SL-Silver |

