

# プレシールe白継手【略号:プレ白】

[適用範囲] 水(飲料水を除く)・冷温水・空気・ガス・油

[適用管種] 配管用炭素鋼钢管(SGP)

水配管用亜鉛めつき钢管(SGPW)



## BL/45°BL/BT/BCr/BS/F/U/10K合F

好評につき  
在庫販売開始

品名	エルボ	45°エルボ	チー	クロス	ソケット	組み法兰ジ	ユニオン	10K合法兰ジ
呼び(B) 型番	BL	45°BL	BT	BCr	BS	F	U	※ 10K合F
1/2	●	●	●	●	●	●	●	●
3/4	●	●	●	●	●	●	●	●
1	●	●	●	●	●	●	●	●
1 1/4	●	●	●	●	●	●	●	●
1 1/2	●	●	●	●	●	●	●	●
2	●	●	●	●	●	●	●	●
2 1/2	●	●	●	★	●	★	★	●
3	●	●	●	★	●	★	★	●
4	●	●	●	★	●	★	★	●
5	○	○	○		○			●
6	○	○	○		○			●

※10K合Fの継手基材は、JIS B 2239の適合品です。

## BRL/BRT/BRS/BU

品名	径違い エルボ	径違い チー	径違い ソケット	ブッシング
呼び(B) 型番	BRL	BRT	BRS	BU
3/4	●	●	●	★
1	●	●	●	★
1/2	●	●	●	★
1 1/4	●	●	●	★
1 1/2	●	●	●	★
1/2	★	●	●	★
1 1/4	●	●	●	★
1	●	●	●	★
3/4	●	●	●	★
1/2	★	●	●	★
1 1/2	●	●	●	★
1	●	●	●	★
3/4	●	●	●	★
1/2	★	●	●	★
2	●	●	●	★
1 1/4	●	●	●	★
1	●	●	●	★
3/4	●	●	●	★
1/2	★	●	●	★
2 1/2	●	●	●	★
1 1/2	●	●	●	★
1 1/4	●	●	●	★
1	●	●	●	★
3/4	●	●	●	★
1/2	★	●	●	★
2	●	●	●	★
1 1/2	●	●	●	★
1 1/4	●	●	●	★
1	●	●	●	★
3/4	●	●	●	★
1/2	●	●	●	★

品名	径違い エルボ	径違い チー	径違い ソケット	ブッシング
呼び(B) 型番	BRL	BRT	BRS	BU
2 1/2	●	●	●	★
2	●	●	●	★
1 1/2	●	●	●	★
3	●	●	●	★
1 1/4	●	●	●	★
1	●	●	●	★
3/4	●	●	●	★
1/2		●	●	★
3	●	●	●	★
2 1/2	●	●	●	★
2	●	●	●	★
1 1/2	●	●	●	★
4	●	●	●	★
1 1/4	●	●	●	★
1		●	●	★
3/4	●	●	●	★
1/2	●	●		★
5	○	○	○	
3		○		
2 1/2		○		
2		○		
1 1/2		○		
3/4		○		
5	○	○	○	
4	○	○	○	
6	○	○		
3		○		
2 1/2		○		
1 1/2		○		

●標準在庫品 ○受注生産品

★は株式会社リケン CKJV が製造するコママーク品です。