

# スパイラルエアホース イエローライン

## SPIRAL YELLOW LINE

### TPS タイプ TPS TYPE



型式 Model	ホース サイズ Hose Size I.D.×O.D.	使用範囲 Service Length (mm)	ホース 全長 Hose Length (mm)	A (mm)	B (mm)	C (mm)	D (mm)	φE (mm)	標準継手 StandardFittings		重量 Weight (g)
									T1	T2	
TPS-803-0105Y	5×8	2,000	2,500	780	500	180	100	42	H5-G2FU	H5-G2F + N-2M-2M	190
TPS-805-0105Y	5×8	4,000	5,000	1,000	500	400	100	42			280
TPS-808-0105Y	5×8	6,000	7,500	1,230	500	630	100	42			370
TPS-810-0105Y	5×8	8,000	10,000	1,400	500	800	100	42			460
TPS-1003-0105Y	6.5×10	2,000	2,500	785	500	185	100	52	H6.5-G2FU	H6.5-G2F	230
TPS-1005-0105Y	6.5×10	4,000	5,000	1,000	500	400	100	52			360
TPS-1008-0105Y	6.5×10	6,000	7,500	1,235	500	635	100	52			500
TPS-1010-0105Y	6.5×10	8,000	10,000	1,400	500	800	100	52			630
TPS-1203-0105Y	8×12	2,000	2,500	780	500	180	100	65	H8-G2FU	H8-G2F	320
TPS-1205-0105Y	8×12	4,000	5,000	990	500	390	100	65			510
TPS-1208-0105Y	8×12	6,000	7,500	1,190	500	590	100	65			700
TPS-1210-0105Y	8×12	8,000	10,000	1,380	500	780	100	65			880
TPS-1603-0105Y	11×16	2,000	2,500	720	500	120	100	108	H11-4FU	H11-4F	580
TPS-1605-0105Y	11×16	4,000	5,000	840	500	240	100	108			900
TPS-1608-0105Y	11×16	6,000	7,500	1,000	500	400	100	108			1,200
TPS-1610-0105Y	11×16	8,000	10,000	1,170	500	570	100	108			1,500

※標準継手以外の継手の取付も可能です。

Other thread fitting are available as custom model.

### SPH タイプ SPH TYPE



型式 Model	ホース サイズ Hose Size I.D.×O.D.	使用範囲 Service Length (mm)	ホース 全長 Hose Length (mm)	A (mm)	B (mm)	C (mm)	D (mm)	φE (mm)	標準継手 StandardFittings		重量 Weight (g)
									T1	T2	
SPH-803-0105Y	5×8	2,000	2,500	780	500	180	100	42	H5-G2FU	H5-G2F + N-2M-2M	180
SPH-805-0105Y	5×8	4,000	5,000	1,000	500	400	100	42			270
SPH-808-0105Y	5×8	6,000	7,500	1,230	500	630	100	42			350
SPH-810-0105Y	5×8	8,000	10,000	1,400	500	800	100	42			440
SPH-1003-0105Y	6.5×10	2,000	2,500	785	500	185	100	52	H6.5-G2FU	H6.5-G2F	220
SPH-1005-0105Y	6.5×10	4,000	5,000	1,000	500	400	100	52			340
SPH-1008-0105Y	6.5×10	6,000	7,500	1,235	500	635	100	52			470
SPH-1010-0105Y	6.5×10	8,000	10,000	1,400	500	800	100	52			600
SPH-1203-0105Y	8×12	2,000	2,500	780	500	180	100	65	H8-G2FU	H8-G2F	300
SPH-1205-0105Y	8×12	4,000	5,000	990	500	390	100	65			480
SPH-1208-0105Y	8×12	6,000	7,500	1,190	500	590	100	65			660
SPH-1210-0105Y	8×12	8,000	10,000	1,380	500	780	100	65			840

安全上のご注意  
ご使用前にP1～P33をご確認ください。