

## 製品概要

Line up

### ● ストライクドリル EZN5D形(5Dタイプ) EZN5D type



- 高精度ソリッドドリル High accuracy solid drill
- 有効加工穴深さ5×Dc Drilling depth 5×Dc
- ねじれ角30° Helix angle :30°
- クーラント穴つき Through coolant hole
- ダブルマージン Double margin



形番 Cat. No.	在庫 Stock	寸法 (mm) Dimensions					標準価格 (円) List Price (JPY)
		φDc	ℓ	L	Lo	φDs	
EZN5DCH0300S03	●	3.0	24	77	77.5	3	10,440
EZN5DCH0310S04	●	3.1	28	81	81.6	4	10,770
EZN5DCH0320S04	●	3.2	28	81	81.6	4	10,770
EZN5DCH0330S04	●	3.3	28	81	81.6	4	10,770
EZN5DCH0340S04	●	3.4	28	81	81.6	4	10,770
EZN5DCH0350S04	●	3.5	28	81	81.6	4	10,770
EZN5DCH0360S04	●	3.6	32	85	85.7	4	11,110
EZN5DCH0370S04	●	3.7	32	85	85.7	4	11,110
EZN5DCH0380S04	●	3.8	32	85	85.7	4	11,110
EZN5DCH0390S04	●	3.9	32	85	85.7	4	11,110
EZN5DCH0400S04	●	4.0	32	85	85.7	4	11,110
EZN5DCH0410S05	●	4.1	36	91	91.7	5	11,880
EZN5DCH0420S05	●	4.2	36	91	91.8	5	11,880
EZN5DCH0430S05	●	4.3	36	91	91.8	5	11,880
EZN5DCH0440S05	●	4.4	36	91	91.8	5	11,880
EZN5DCH0450S05	●	4.5	36	91	91.8	5	11,880
EZN5DCH0460S05	●	4.6	40	94	94.8	5	12,100
EZN5DCH0470S05	●	4.7	40	94	94.9	5	12,100
EZN5DCH0480S05	●	4.8	40	94	94.9	5	12,100
EZN5DCH0490S05	●	4.9	40	94	94.9	5	12,100
EZN5DCH0500S05	●	5.0	40	94	94.9	5	12,100
EZN5DCH0510S06	●	5.1	44	96	96.9	6	13,420
EZN5DCH0520S06	●	5.2	44	96	96.9	6	13,420
EZN5DCH0530S06	●	5.3	44	96	97.0	6	13,420
EZN5DCH0540S06	●	5.4	44	96	97.0	6	13,420
EZN5DCH0550S06	●	5.5	44	96	97.0	6	13,420
EZN5DCH0560S06	●	5.6	48	100	101.0	6	13,750
EZN5DCH0570S06	●	5.7	48	100	101.0	6	13,750
EZN5DCH0580S06	●	5.8	48	100	101.1	6	13,750
EZN5DCH0590S06	●	5.9	48	100	101.1	6	13,750
EZN5DCH0600S06	●	6.0	48	100	101.1	6	13,750
EZN5DCH0610S07	●	6.1	52	105	106.1	7	14,410
EZN5DCH0620S07	●	6.2	52	105	106.1	7	14,410

形番 Cat. No.	在庫 Stock	寸法 (mm) Dimensions					標準価格 (円) List Price (JPY)
		φDc	ℓ	L	Lo	φDs	
EZN5DCH0630S07	●	6.3	52	105	106.1	7	14,410
EZN5DCH0640S07	●	6.4	52	105	106.2	7	14,410
EZN5DCH0650S07	●	6.5	52	105	106.2	7	14,410
EZN5DCH0660S07	●	6.6	56	109	110.2	7	14,850
EZN5DCH0670S07	●	6.7	56	109	110.2	7	14,850
EZN5DCH0680S07	●	6.8	56	109	110.2	7	14,850
EZN5DCH0690S07	●	6.9	56	109	110.3	7	14,850
EZN5DCH0700S07	●	7.0	56	109	110.3	7	14,850
EZN5DCH0710S08	●	7.1	60	114	115.3	8	16,060
EZN5DCH0720S08	●	7.2	60	114	115.3	8	16,060
EZN5DCH0730S08	●	7.3	60	114	115.3	8	16,060
EZN5DCH0740S08	●	7.4	60	114	115.3	8	16,060
EZN5DCH0750S08	●	7.5	60	114	115.4	8	16,060
EZN5DCH0760S08	●	7.6	64	118	119.4	8	16,390
EZN5DCH0770S08	●	7.7	64	118	119.4	8	16,390
EZN5DCH0780S08	●	7.8	64	118	119.4	8	16,390
EZN5DCH0790S08	●	7.9	64	118	119.4	8	16,390
EZN5DCH0800S08	●	8.0	64	118	119.5	8	16,390
EZN5DCH0810S09	●	8.1	68	127	128.5	9	17,600
EZN5DCH0820S09	●	8.2	68	127	128.5	9	17,600
EZN5DCH0830S09	●	8.3	68	127	128.5	9	17,600
EZN5DCH0840S09	●	8.4	68	127	128.5	9	17,600
EZN5DCH0850S09	●	8.5	68	127	128.5	9	17,600
EZN5DCH0860S09	●	8.6	72	127	128.6	9	18,040
EZN5DCH0870S09	●	8.7	72	127	128.6	9	18,040
EZN5DCH0880S09	●	8.8	72	127	128.6	9	18,040
EZN5DCH0890S09	●	8.9	72	127	128.6	9	18,040
EZN5DCH0900S09	●	9.0	72	127	128.6	9	18,040
EZN5DCH0910S10	●	9.1	76	136	137.7	10	19,250
EZN5DCH0920S10	●	9.2	76	136	137.7	10	19,250
EZN5DCH0930S10	●	9.3	76	136	137.7	10	19,250
EZN5DCH0940S10	●	9.4	76	136	137.7	10	19,250
EZN5DCH0950S10	●	9.5	76	136	137.7	10	19,250

●: メーカー在庫品 Standard stock items  
標準価格は2022年12月時点の価格となります。  
標準切削条件は19~20ページをご参照ください