

製品概要

Line up

● ストライクドリル EZN8D形(8Dタイプ) EZN 8D type



- 高精度ソリッドドリル
- 有効加工穴深さ8×Dc
- ねじれ角30°
- クーラント穴つき
- ダブルマージン

High accuracy solid drill
Drilling depth 8×Dc
Helix angle :30°
Through coolant hole
Double margin



形番 Cat. No.	在庫 Stock	寸法 (mm) Dimensions					標準価格 (円) List Price (JPY)
		φDc	ℓ	L	Lo	φDs	
EZN8DCH0300S03	●	3.0	33	81	81.5	3	15,070
EZN8DCH0310S04	●	3.1	39	87	87.6	4	15,400
EZN8DCH0320S04	●	3.2	39	87	87.6	4	15,400
EZN8DCH0330S04	●	3.3	39	87	87.6	4	15,400
EZN8DCH0340S04	●	3.4	39	87	87.6	4	15,400
EZN8DCH0350S04	●	3.5	39	87	87.6	4	15,400
EZN8DCH0360S04	●	3.6	44	92	92.7	4	15,400
EZN8DCH0370S04	●	3.7	44	92	92.7	4	15,400
EZN8DCH0380S04	●	3.8	44	92	92.7	4	15,400
EZN8DCH0390S04	●	3.9	44	92	92.7	4	15,400
EZN8DCH0400S04	●	4.0	44	92	92.7	4	15,400
EZN8DCH0410S05	●	4.1	50	100	100.7	5	16,060
EZN8DCH0420S05	●	4.2	50	100	100.8	5	16,060
EZN8DCH0430S05	●	4.3	50	100	100.8	5	16,060
EZN8DCH0440S05	●	4.4	50	100	100.8	5	16,060
EZN8DCH0450S05	●	4.5	50	100	100.8	5	16,060
EZN8DCH0460S05	●	4.6	55	105	105.8	5	16,280
EZN8DCH0470S05	●	4.7	55	105	105.9	5	16,280
EZN8DCH0480S05	●	4.8	55	105	105.9	5	16,280
EZN8DCH0490S05	●	4.9	55	105	105.9	5	16,280
EZN8DCH0500S05	●	5.0	55	105	105.9	5	16,280
EZN8DCH0510S06	●	5.1	61	114	114.9	6	16,940
EZN8DCH0520S06	●	5.2	61	114	114.9	6	16,940
EZN8DCH0530S06	●	5.3	61	114	115.0	6	16,940
EZN8DCH0540S06	●	5.4	61	114	115.0	6	16,940
EZN8DCH0550S06	●	5.5	61	114	115.0	6	16,940
EZN8DCH0560S06	●	5.6	66	118	119.0	6	17,380
EZN8DCH0570S06	●	5.7	66	118	119.0	6	17,380
EZN8DCH0580S06	●	5.8	66	118	119.1	6	17,380

形番 Cat. No.	在庫 Stock	寸法 (mm) Dimensions					標準価格 (円) List Price (JPY)
		φDc	ℓ	L	Lo	φDs	
EZN8DCH0590S06	●	5.9	66	118	119.1	6	17,380
EZN8DCH0600S06	●	6.0	66	118	119.1	6	17,380
EZN8DCH0610S07	●	6.1	71	125	126.1	7	18,370
EZN8DCH0620S07	●	6.2	71	125	126.1	7	18,370
EZN8DCH0630S07	●	6.3	71	125	126.1	7	18,370
EZN8DCH0640S07	●	6.4	71	125	126.2	7	18,370
EZN8DCH0650S07	●	6.5	71	125	126.2	7	18,370
EZN8DCH0660S07	●	6.6	77	130	131.2	7	18,590
EZN8DCH0670S07	●	6.7	77	130	131.2	7	18,590
EZN8DCH0680S07	●	6.8	77	130	131.2	7	18,590
EZN8DCH0690S07	●	6.9	77	130	131.3	7	18,590
EZN8DCH0700S07	●	7.0	77	130	131.3	7	18,590
EZN8DCH0710S08	●	7.1	82	136	137.3	8	19,910
EZN8DCH0720S08	●	7.2	82	136	137.3	8	19,910
EZN8DCH0730S08	●	7.3	82	136	137.3	8	19,910
EZN8DCH0740S08	●	7.4	82	136	137.3	8	19,910
EZN8DCH0750S08	●	7.5	82	136	137.4	8	19,910
EZN8DCH0760S08	●	7.6	88	142	143.4	8	20,240
EZN8DCH0770S08	●	7.7	88	142	143.4	8	20,240
EZN8DCH0780S08	●	7.8	88	142	143.4	8	20,240
EZN8DCH0790S08	●	7.9	88	142	143.4	8	20,240
EZN8DCH0800S08	●	8.0	88	142	143.5	8	20,240
EZN8DCH0810S09	●	8.1	93	154	155.5	9	21,230
EZN8DCH0820S09	●	8.2	93	154	155.5	9	21,230
EZN8DCH0830S09	●	8.3	93	154	155.5	9	21,230
EZN8DCH0840S09	●	8.4	93	154	155.5	9	21,230
EZN8DCH0850S09	●	8.5	93	154	155.5	9	21,230
EZN8DCH0860S09	●	8.6	99	154	155.6	9	21,450
EZN8DCH0870S09	●	8.7	99	154	155.6	9	21,450

●：メーカー在庫品 Standard stock items
標準価格は2022年12月時点の価格となります。
標準切削条件は19~20ページをご参照ください