

ソケット



中ベースレセプタクル

- 口金:E12
- 定格:250V 1A

#2307H

No.0922-0

- H110×W60×D20
- 11g ●5/250



グローソケット

- 口金:E17
- 定格:250V 1A
- ネジ穴径:φ4.5
- ネジ種類:ナベ小ネジ M4×15mm

#6001H

No.0934-0

- H130×W60×D25
- 17g ●5/300



レセプタクル

- 口金:E26
- 定格:250V 6A

B-60H

No.0910-0

- H170×W60×D45
- 46g ●5/200



ブルスイッチ付ソケット

- 口金:E26
- 定格:250V 6A

B-1662H

No.1662-1

- H140×W80×D50
- 77g ●5/100



引掛ソケット

- 口金:E26
- 使用電球80W以下
- 定格:125V 1A

B-63H(W)

No.0913-0

- H160×W80×D70
- 99g ●5/80



丸型レセプタクル

- 耐熱・磁器製
- 口金:E12
- 定格:300V 1A

SB-1201H

ホワイト

No.1118-5

- H140×W60×D30
- 36g ●50/100



ホワイト



ブラック

丸型レセプタクル

- 耐熱・磁器製
- 口金:E17
- 定格:300V 3A

SB-1713H(W)

ホワイト

No.1124-5

- H140×W60×D30
- 40g ●50/100



SB-1713H(BK)

ブラック

No.1126-3

- H140×W60×D30
- 40g ●50/100



台付レセプタクル

- 耐熱・磁器製
- 口金:E17
- 定格:300V 3A

SB-1714H

ホワイト

No.1124-3

- H140×W60×D30
- 50g ●50/100



丸型レセプタクル

- 耐熱・磁器製
- 口金:E17
- 定格:300V 3A

SB-1715H

ホワイト

No.1118-4

- H140×W60×D45
- 65g ●25/100



ホワイト



ブラック

丸型レセプタクル

- 耐熱・磁器製
- 口金:E26
- 定格:300V 6A

SB-2617H(W)

ホワイト

No.1124-2

- H140×W60×D45
- 90g ●25/100



SB-2617H(BK)

ブラック

No.1126-2

- H140×W60×D45
- 100g ●25/100



丸型レセプタクル

- 耐熱・磁器製
- 口金:E26
- 定格:300V 6A

SB-2618H

ホワイト

No.1124-4

- H140×W60×D45
- 105g ●25/100



台付レセプタクル

- 耐熱・磁器製
- 口金:E26
- 定格:300V 6A

SB-2620H

ホワイト

No.1118-1

- H140×W60×D50
- 120g ●25/100

コード付タップ/
延長コード/
プラグタップ一般配線器具/
照明用配線器具工事用配線器具/
屋外配線配線
小物パーツブラックス
シリーズ

工作・ホビー

ヒューズ・
デスター結束バンド/
コイルチューブ/
ビニールテープモール/
モールパーツエアコン
配管パーツ補修用コード/
切りコードドラム巻
コード