

1	2	3	4	5	6	7	8	9	10	11	12	13
概要	形式説明	仕様一覧表	選定	取付と接続	本体付属装置-1	本体付属装置-2	特性と外形-1	特性と外形-2	認定品リスト	新旧比較表	付録	形式索引

特性と外形 BW50HAG, BW125JAG, BW125RAG, BW125HAG

BW50HAG, BW125JAG, BW125RAG, BW125HAG



BW125形

(写No.KKD07-333)

基本形式		BW50HAG		BW125JAG			BW125RAG			BW125HAG		
極数		2	3	2	3	4	2	3	4	2	3	
定格絶縁電圧 (V)	AC	690			690			690			690	
	DC	250			250			250			250	
スタンダード品 定格遮断容量 (kA)	IEC60947-2 UIS C 8201-2-1 EN60947-2 (Icu/Ics)	AC 690V	—	—	—	—	—	—	—	—	—	
		500V	36/9	15/8	15/8	15/8	36/18	—	—	36/9	—	
		440V	65/17	30/15	30/15	30/15	50/25	—	—	65/17	—	
		415V	65/17	30/15	30/15	30/15	50/25	—	—	65/17	—	
		400V	65/17	30/15	30/15	30/15	50/25	—	—	65/17	—	
		380V	65/17	30/15	30/15	30/15	50/25	—	—	65/17	—	
		240V	125/63	50/25	50/25	50/25	100/50	—	—	125/63	—	
		230V	125/63	50/25	50/25	50/25	100/50	—	—	125/63	—	
		DC 250V	40/20	15/8	—	—	40/20	—	—	40/20	—	
		GB14048.2 (Icu/Ics)	AC 400V	—	30/15	—	—	—	—	—	—	—
230V	—	50/25	—	—	100/50	—	—	—	—			

●標準付属品 (表面形)

- ・本体取付ねじ (M4×70) 2P,3P:2本, 4P:4本
- ・端子ねじ (M8×16) 2P:4本, 3P:6本, 4P:8本
- ・相間バリア 2P:2枚, 3P (中相抜き2P) :4枚, 4P:6枚
- ・取扱説明書

●付属オプション

本体 (表面形) 価格に下記価格を加算してください。

品名	形式記号 [=コード]	納期	希望小売価格 (円) (税抜き)			参照 ページ	
			2P	3P	4P		
接続方式	表面形	—	機種定格一覧表参照			5-4	
	裏面形	X	4,970	6,610	9,350	5-11	
	埋込形	E	8,460	10,600	16,100	5-12	
	挿入形	P	16,500	20,700	—	5-14	
内部付属装置	補助スイッチ (リード線式)	標準	1個	—	4,140	6-18	
		2個	V	—	8,280		
	微小負荷	1個	1	—	4,700		
		2個	2	—	9,410		
	警報スイッチ (リード線式)	標準	1個	K	—	4,140	6-18
		2個	J	—	8,280		
	微小負荷	1個	8	—	4,700		
		2個	9	—	9,410		
	電圧引外し装置 (リード線式)	AC/DC24V	FR	—	—	7,100	6-19
		AC/DC48V	FS	—	—	—	
AC100-120V/DC100-110V		FA	—	—	—		
AC120-130V		F1	—	—	—		
AC200-240V/DC200-220V		FK	—	—	—		
AC277V		FB	—	—	—		
AC380-440V		FP	—	—	—		
AC440-480V		FH	—	—	—		
AC500-550V		FJ	—	—	—		
不足電圧引外し装置 (リード線式)		DC24V	RR	—	—	19,200	6-20
	DC48V	RS	—	—	—		
	DC100-110V	RL	—	—	—		
	DC125V	R5	—	—	—		
	AC100-110V	RA	—	—	—		
	AC110-130V	RT	—	—	—		
	AC200-240V	RK	—	—	—		
	AC277V	RB	—	—	—		
	AC380-415V	RP	—	—	—		
	AC440-480V	RH	—	—	—		
リード線端子台	1個	A	—	—	670	6-24	
	2個	—	—	—	1,350		

(注①) BW125JA□-2Pには付属できません。

◎ 標準品 ○ 準標準品 △ 受注品

●機種定格一覧表

□内指定: 定格電流 [コード]

タイプ	シリーズ名	基本形式 (=商品コード)	定格電流 In (A) [コード]	希望小売価格 (円) (税抜き)	納期
スタンダード品	一般配線用	BW50HAG-2P□	15 [015] 20 [020]	34,700	△
		BW50HAG-3P□	30 [030] 40 [040]	45,900	△
		BW50HAA-3P□	50 [050]	62,000	△
		BW125JAG-2P□	15 [015] 20 [020]	33,300	◎
		BW125JAG-3P□	30 [030] 40 [040]	41,900	◎
		BW125JAG-4P□	50 [050] 60 [060]	62,900	◎
		BW125JAA-3P□	75 [075] 100 [100]	46,700	◎
		BW125RAG-2P□	—	46,500	◎
		BW125RAG-3P□	—	58,100	◎
		BW125RAG-4P□	—	87,100	◎
		BW125RAA-3P□	—	62,900	◎
		BW125HAG-2P□	—	77,600	△
		BW125HAG-3P□	—	97,000	△
		BW125HAA-3P□	—	104,000	△
		BW125JAG-2P□	125 [125]	53,300	◎
		BW125JAG-3P□	—	61,900	◎
		BW125JAG-4P□	—	82,900	◎
		BW125JAA-3P□	—	66,700	◎
		BW125RAG-2P□	—	57,600	◎
		BW125RAG-3P□	—	69,100	◎
		BW125RAG-4P□	—	98,200	◎
		BW125RAA-3P□	—	74,000	◎
		BW125HAG-2P□	—	113,000	△
		BW125HAG-3P□	—	132,400	△
BW125HAA-3P□	—	139,400	△		
電動機保護用	BW125JAM-3P□	75 [075] 90 [090]	41,900	○	
	BW125RAM-3P□	45 [045] 60 [060] 75 [075] 90 [090]	58,000	○	
高インスタント品	BW125JAK-3P□	50 [050] 60 [060]	41,900	○	
	BW125RAK-3P□	75 [075] 100 [100]	58,100	○	
	BW125HAK-3P□	—	97,000	△	
変圧器一次側用	BW125JAT-2P□	60 [060] 75 [075]	35,200	○	
	BW125JAT-3P□	90 [090] 100 [100]	44,100	○	
ノンオート	BW125JAS-2P□	125 [125]	53,300	○	
	BW125JAS-3P□	—	61,900	○	
	BW125RAS-2P□	—	57,600	○	
	BW125RAS-3P□	—	69,100	○	
	BW125RAS-4P□	—	98,200	○	
	瞬時遮断式 ①	BW125JAQ-2P□	450 [450] 600 [600]	33,300	○
BW125JAQ-3P□	800 [800] 1000 [10X]	41,900	○		
BW125RAQ-2P□	1200 [12X]	46,500	○		
BW125RAQ-3P□	(注)450AはBW125JAQのみ	58,100	△		
BW125RAB-2P□	10~20[020] 20~40[040]	51,300	△		
BW125RAB-3P□	40~80[080] 70~140[140]	62,900	△		
		120~240[240] 180~360[360]	—	—	
		300~600[600] 400~800[800]	—	—	
		650~1300[13X]	—	—	

(注①) 定格は瞬時引外し電流値を示します。

◎ 標準品 ○ 準標準品 △ 受注品