


FITTING

SWC SOCKET WELD CONNECTOR

ハーフユニオン (SW)



(METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.	A	B	C	D	E	F	G	H	L	K
3	SWC- 3-0	31	8	16	15	2.5	12	12	24	9	7.5
4	SWC- 4-0	36.3	8	18.3	15.3	3.5	14	14	29	11	10.5
6	SWC- 6-0	36.4	8	18.4	15.4	5	14	14	29	11	10.5
8	SWC- 8-0	36.8	9	18.8	16.8	6	14	15.87	29	11	12
10	SWC-10-0	39.7	10	20.7	18.7	8	17	19	31	12	15
12	SWC-12-0	41.8	12	22.8	22.8	10	22	23	31	12	18.5

※管外径5φも製作しております。


(INCHES)

1/8"	3.18	SWC- 01-0	31	8	16	15	2.5	12	12	24	9	7.5
1/4"	6.35	SWC- 02-0	36.4	8	18.4	15.4	5	14	14	29	11	10.5
5/16"	7.94	SWC-025-0	36.8	9	18.8	16.8	6	14	15.87	29	11	12
3/8"	9.53	SWC- 03-0	39.3	9.5	20.3	17.8	7	17	17.46	31	12	13.8
1/2"	12.7	SWC- 04-0	41.8	12	22.8	22.8	10	22	23	31	12	18.5

A.C.D:FINGER TIGHT±0.5mm (about)
※管外径3φも製作しております。

SWE SOCKET WELD ELBOW

エルボユニオン (SW)



(METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.	A	B	C	D	E	G	H	K
3	SWE- 3-0	25	8	24	15	2.5	12	18	14
4	SWE- 4-0	28.3	8	24	15.3	3.5	14	21	14
6	SWE- 6-0	28.4	8	24	15.4	5	14	21	14
8	SWE- 8-0	28.8	9	24	16.8	6	15.87	21	14
10	SWE-10-0	31.7	10	27	18.7	8	19	23	17
12	SWE-12-0	34.8	12	30	22.8	10	23	24	19

※管外径5φも製作しております。


(INCHES)

1/8"	3.18	SWE- 01-0	25	8	24	15	2.5	12	18	14
1/4"	6.35	SWE- 02-0	28.4	8	24	15.4	5	14	21	14
5/16"	7.94	SWE-025-0	28.8	9	24	16.8	6	15.87	21	14
3/8"	9.53	SWE- 03-0	31.3	9.5	27	17.8	7	17.46	23	17
1/2"	12.7	SWE- 04-0	34.8	12	30	22.8	10	23	24	19

A.D:FINGER TIGHT±0.5mm (about)
※管外径3φも製作しております。

RA REDUCING ADAPTER

レジュースー



(METRIC)

(Unit:mm)

TUBE O.D.		PART. No.	A	C	D	E	F	G	H
T ₁	T ₂								
3	4	RA- 3*4 -0	41	16	15	2.5	12	12	34
3	6	RA- 3*6 -0	41	16	15	2.5	12	12	34
4	6	RA- 4*6 -0	44.3	18.3	15.3	3.5	14	14	37
4	8	RA- 4*8 -0	44.3	18.3	15.3	3.5	14	14	37
6	8	RA- 6*8 -0	44.4	18.4	15.4	5	14	14	37
6	10	RA- 6*10-0	49.4	18.4	15.4	5	14	14	42
8	10	RA- 8*10-0	49.8	18.8	16.8	6	14	15.87	42
8	12	RA- 8*12-0	53.8	18.8	16.8	6	14	15.87	46
10	12	RA-10*12-0	55.7	20.7	18.7	8	17	19	47

※管外径5φも製作しております。

(INCHES)

1/8"	3.18	1/4"	6.35	RA-01*02-0	41	16	15	2.5	12	12	12	34
1/4"	6.35	3/8"	9.35	RA-02*03-0	19.4	18.4	15.3	5	14	14	14	42
3/8"	9.53	1/2"	12.7	RA-03*04-0	55.3	20.3	17.8	7	14	17	17.46	47

A.C.D:FINGER TIGHT±0.5mm (about)
※管外径3φも製作しております。