

# LS-TC ロングシャンク T スロットカッター

SINCE 1935  
F.K.D.®

LS-TC T-Slot Cutters, Straight Tooth, Long Shank


材質=HSS-Co(SKH56)

「外径公差」

D≤16	-0.050~-0.16
16<D≤30	-0.065~-0.195
30<D≤45	-0.080~-0.24
45<D≤100	-0.100~-0.29

刃幅公差

0~+0.1



○シャンク部を長く設計してあります。MCなどに有効です。

Good for CNC and MC with long shank. Premium HSS Co8%.

●注文例=型番、刃径、刃幅、数量 「LS-TC 10x2」

※両サイド刃の長さはP157に掲載。

型番	刃径(D)	刃幅(ℓ)	首径(d1)	首長(ℓ1)	全長(L)	シャンク径(d)	刃数(NT)
LS-TC	10	2	4	15	130	10	8
LS-TC	10	2.5	4	15	130	10	8
LS-TC	10	3	4	15	130	10	8
LS-TC	10	3.5	4	15	130	10	8
LS-TC	10	4	4	15	130	10	8
LS-TC	10	4.5	4	15	130	10	8
LS-TC	10	5	4	15	130	10	8
LS-TC	10	6	4	15	130	10	8
LS-TC	10	7	4	15	130	10	8
LS-TC	10	8	4	15	130	10	8
LS-TC	10	10	4	15	130	10	8
LS-TC	12	2	5	15	130	10	8
LS-TC	12	2.5	5	15	130	10	8
LS-TC	12	3	5	15	130	10	8
LS-TC	12	3.5	5	15	130	10	8
LS-TC	12	4	5	15	130	10	8
LS-TC	12	4.5	5	15	130	10	8
LS-TC	12	5	5	15	130	10	8
LS-TC	12	6	5	15	130	10	8
LS-TC	12	7	5	15	130	10	8
LS-TC	12	8	5	15	130	10	8
LS-TC	15	2	6	20	135	12	8
LS-TC	15	2.5	6	20	135	12	8
LS-TC	15	3	6	20	135	12	8
LS-TC	15	3.5	6	20	135	12	8
LS-TC	15	4	6	20	135	12	8
LS-TC	15	4.5	6	20	135	12	8
LS-TC	15	5	6	20	135	12	8
LS-TC	15	6	6	20	135	12	8
LS-TC	15	7	6	20	135	12	8
LS-TC	15	8	6	20	135	12	8
LS-TC	15	9	6	20	135	12	8
LS-TC	15	10	6	20	135	12	8
LS-TC	15	12	6	20	135	12	8
LS-TC	20	2	9	22	150	16	10
LS-TC	20	2.5	9	22	150	16	10
LS-TC	20	3	9	22	150	16	10
LS-TC	20	3.5	9	22	150	16	10
LS-TC	20	4	9	22	150	16	10
LS-TC	20	4.5	9	22	150	16	10
LS-TC	20	5	9	22	150	16	10
LS-TC	20	6	9	22	150	16	10
LS-TC	20	7	9	22	150	16	10

型番	刃径(D)	刃幅(ℓ)	首径(d1)	首長(ℓ1)	全長(L)	シャンク径(d)	刃数(NT)
LS-TC	20	8	9	22	150	16	10
LS-TC	20	9	9	22	150	16	10
LS-TC	20	10	9	22	150	16	10
LS-TC	20	12	9	22	150	16	10
LS-TC	25	2	11	24	150	16	10
LS-TC	25	2.5	11	24	150	16	10
LS-TC	25	3	11	24	150	16	10
LS-TC	25	3.5	11	24	150	16	10
LS-TC	25	4	11	24	150	16	10
LS-TC	25	4.5	11	24	150	16	10
LS-TC	25	5	11	24	150	16	10
LS-TC	25	6	11	24	150	16	10
LS-TC	25	7	11	24	150	16	10
LS-TC	25	8	11	24	150	16	10
LS-TC	25	9	11	24	150	16	10
LS-TC	25	10	11	24	150	16	10
LS-TC	25	12	11	24	150	16	10
LS-TC	30	2	13	26	150	16	12
LS-TC	30	2.5	13	26	150	16	12
LS-TC	30	3	13	26	150	16	12
LS-TC	30	3.5	13	26	150	16	12
LS-TC	30	4	13	26	150	16	12
LS-TC	30	4.5	13	26	150	16	12
LS-TC	30	5	13	26	150	16	12
LS-TC	30	6	13	26	150	16	12
LS-TC	30	7	13	26	150	16	12
LS-TC	30	8	13	26	150	16	12
LS-TC	30	9	13	26	150	16	12
LS-TC	30	10	13	26	150	16	12
LS-TC	30	12	13	26	150	16	12
LS-TC	30	14	13	26	150	16	12
LS-TC	30	15	13	26	150	16	12
LS-TC	35	2	15	28	150	16	12
LS-TC	35	2.5	15	28	150	16	12
LS-TC	35	3	15	28	150	16	12
LS-TC	35	3.5	15	28	150	16	12
LS-TC	35	4	15	28	150	16	12
LS-TC	35	4.5	15	28	150	16	12
LS-TC	35	5	15	28	150	16	12
LS-TC	35	6	15	28	150	16	12
LS-TC	35	7	15	28	150	16	12
LS-TC	35	8	15	28	150	16	12
LS-TC	35	9	15	28	150	16	12

柄付カッター