

# LS-STC ロングシャンク千鳥刃Tスロットカッター

SINCE 1935  
F.K.D.®

LS-STC T-Slot Cutters, Staggered Tooth, Long Shank

材質=HSS-Co(SKH56)

「外径公差」


D≤16 -0.050~-0.16  
16<D≤30 -0.065~-0.195  
30<D≤45 -0.080~-0.24  
45<D≤100 -0.100~-0.29

刃幅公差

0~+0.1

左右振れ角=15° ℓ≤20

左右振れ角=12° ℓ≥21



○シャンク部を長く設計してあります。MCなどに有効です。

Good for CNC and MC with long shank. Premium HSS Co8%.

●注文例=型番、刃径、刃幅、数量 「LS-STC 10x3」 ※両サイド刃の長さはP157に掲載。

型番	刃径(D)	刃幅(ℓ)	首径(d1)	首長(ℓ1)	全長(L)	シャンク径(d)	刃数(NT)
LS-STC	10	3	4	15	130	10	6
LS-STC	10	4	4	15	130	10	6
LS-STC	10	5	4	15	130	10	6
LS-STC	10	6	4	15	130	10	6
LS-STC	10	7	4	15	130	10	6
LS-STC	10	8	4	15	130	10	6
LS-STC	12	3	5	15	130	10	6
LS-STC	12	4	5	15	130	10	6
LS-STC	12	5	5	15	130	10	6
LS-STC	12	6	5	15	130	10	6
LS-STC	12	7	5	15	130	10	6
LS-STC	12	8	5	15	130	10	6
LS-STC	15	3	6	20	135	12	6
LS-STC	15	4	6	20	135	12	6
LS-STC	15	5	6	20	135	12	6
LS-STC	15	6	6	20	135	12	6
LS-STC	15	7	6	20	135	12	6
LS-STC	15	8	6	20	135	12	6
LS-STC	15	9	6	20	135	12	6
LS-STC	15	10	6	20	135	12	6
LS-STC	15	11	6	20	135	12	6
LS-STC	15	12	6	20	135	12	6
LS-STC	16	3	7	20	135	12	6
LS-STC	16	4	7	20	135	12	6
LS-STC	16	5	7	20	135	12	6
LS-STC	16	6	7	20	135	12	6
LS-STC	16	7	7	20	135	12	6
LS-STC	16	8	7	20	135	12	6
LS-STC	16	9	7	20	135	12	6
LS-STC	16	10	7	20	135	12	6
LS-STC	16	11	7	20	135	12	6
LS-STC	16	12	7	20	135	12	6
LS-STC	18	3	8	20	150	12	6
LS-STC	18	4	8	20	150	12	6
LS-STC	18	5	8	20	150	12	6
LS-STC	18	6	8	20	150	12	6
LS-STC	18	7	8	20	150	12	6
LS-STC	18	8	8	20	150	12	6
LS-STC	18	9	8	20	150	12	6
LS-STC	18	10	8	20	150	12	6
LS-STC	18	11	8	20	150	12	6
LS-STC	18	12	8	20	150	12	6
LS-STC	18	13	8	20	150	12	6
LS-STC	18	14	8	20	150	12	6

型番	刃径(D)	刃幅(ℓ)	首径(d1)	首長(ℓ1)	全長(L)	シャンク径(d)	刃数(NT)
LS-STC	18	15	8	20	150	12	6
LS-STC	19	3	8	22	150	12	6
LS-STC	19	4	8	22	150	12	6
LS-STC	19	5	8	22	150	12	6
LS-STC	19	6	8	22	150	12	6
LS-STC	19	7	8	22	150	12	6
LS-STC	19	8	8	22	150	12	6
LS-STC	19	9	8	22	150	12	6
LS-STC	19	10	8	22	150	12	6
LS-STC	19	11	8	22	150	12	6
LS-STC	19	12	8	22	150	12	6
LS-STC	20	3	9	22	150	16	6
LS-STC	20	4	9	22	150	16	6
LS-STC	20	5	9	22	150	16	6
LS-STC	20	6	9	22	150	16	6
LS-STC	20	7	9	22	150	16	6
LS-STC	20	8	9	22	150	16	6
LS-STC	20	9	9	22	150	16	6
LS-STC	20	10	9	22	150	16	6
LS-STC	20	11	9	22	150	16	6
LS-STC	20	12	9	22	150	16	6
LS-STC	22	3	9.5	22	150	16	6
LS-STC	22	4	9.5	22	150	16	6
LS-STC	22	5	9.5	22	150	16	6
LS-STC	22	6	9.5	22	150	16	6
LS-STC	22	7	9.5	22	150	16	6
LS-STC	22	8	9.5	22	150	16	6
LS-STC	22	9	9.5	22	150	16	6
LS-STC	22	10	9.5	22	150	16	6
LS-STC	22	11	9.5	22	150	16	6
LS-STC	22	12	9.5	22	150	16	6
LS-STC	24	3	11	24	150	16	8
LS-STC	24	4	11	24	150	16	8
LS-STC	24	5	11	24	150	16	8
LS-STC	24	6	11	24	150	16	8
LS-STC	24	7	11	24	150	16	8
LS-STC	24	8	11	24	150	16	8
LS-STC	24	9	11	24	150	16	8
LS-STC	24	10	11	24	150	16	8
LS-STC	24	11	11	24	150	16	8
LS-STC	24	12	11	24	150	16	8
LS-STC	25	3	11	24	150	16	8
LS-STC	25	4	11	24	150	16	8
LS-STC	25	5	11	24	150	16	8

柄付カッター