







# こて先・ノズル一覧

## 900Sシリーズ 900S (製品P.17)、900S-ESD (製品P.16) 用

※ こて先外径φ5.8mm

























### 標準タイプ

|  |  |   |  |
|--|--|---|--|
| <b>900S-T-B B型</b><br><br><b>945円 (900円 税別)</b>       | <b>900S-T-1C 1C型</b><br><br><b>1,155円 (1,100円 税別)</b> | <b>900S-T-2C 2C型</b><br><br><b>945円 (900円 税別)</b> | <b>900S-T-1.2D 1.2D型</b><br><br><b>945円 (900円 税別)</b> |
| <b>900S-T-1.6D 1.6D型</b><br><br><b>945円 (900円 税別)</b> | <b>900S-T-I I型</b><br><br><b>945円 (900円 税別)</b>       |   |  |





## 900Mシリーズ 900M-ESD (製品P.17)、907-ESD (製品P.16)、933 (製品P.25) 用

※ こて先外径φ6.5mm

### 標準タイプ

|   |  |   |  |
|---|--|---|--|
| <b>900M-T-B / 900M-T-BF2** B型</b><br><br><b>662円 (630円 税別)</b> | <b>900M-T-0.5C 0.5C型</b><br><br><b>966円 (920円 税別)</b>           | <b>900M-T-0.8C 0.8C型</b><br><br><b>966円 (920円 税別)</b>           | <b>900M-T-1C / 900M-T-1CF* 1C型</b><br><br><b>966円 (920円 税別)</b> |
| <b>900M-T-1.5CF* 1.5C型</b><br><br><b>966円 (920円 税別)</b>        | <b>900M-T-2C / 900M-T-2CF* 2C型</b><br><br><b>662円 (630円 税別)</b> | <b>900M-T-3C / 900M-T-3CF* 3C型</b><br><br><b>662円 (630円 税別)</b> | <b>900M-T-4C / 900M-T-4CF* 4C型</b><br><br><b>662円 (630円 税別)</b> |
| <b>900M-T-0.8D 0.8D型</b><br><br><b>662円 (630円 税別)</b>         | <b>900M-T-1.2D 1.2D型</b><br><br><b>662円 (630円 税別)</b>          | <b>900M-T-1.6D 1.6D型</b><br><br><b>662円 (630円 税別)</b>          | <b>900M-T-2.4D 2.4D型</b><br><br><b>662円 (630円 税別)</b>          |
| <b>900M-T-3.2D 3.2D型</b><br><br><b>662円 (630円 税別)</b>        | <b>900M-T-H H型</b><br><br><b>966円 (920円 税別)</b>               | <b>900M-T-1.8H 1.8H型</b><br><br><b>966円 (920円 税別)</b>         | <b>900M-T-I I型</b><br><br><b>662円 (630円 税別)</b>               |
| <b>900M-T-K K型</b><br><br><b>1,365円 (1,300円 税別)</b>          | <b>900M-T-LB LB型</b><br><br><b>966円 (920円 税別)</b>             | <b>900M-T-1.2LD 1.2LD型</b><br><br><b>914円 (870円 税別)</b>       | <b>900M-T-R R型</b><br><br><b>1,260円 (1,200円 税別)</b>           |
| <b>900M-T-RT RT型</b><br><br><b>1,260円 (1,200円 税別)</b>        | <b>900M-T-S4 S4型</b><br><br><b>662円 (630円 税別)</b>             | <b>900M-T-SB SB型</b><br><br><b>914円 (870円 税別)</b>             | <b>900M-T-SI SI型</b><br><br><b>767円 (730円 税別)</b>             |

### 長寿命タイプ











|   |   |  |   |
|---|---|--|---|
| <b>900M-T-BZ B型</b><br><br><b>662円 (630円 税別)</b> | <b>900M-T-2BCZ 2BC型</b><br><br><b>662円 (630円 税別)</b> | <b>900M-T-3BCZ 3BC型</b><br><br><b>662円 (630円 税別)</b> | <b>900M-T-KZ K型</b><br><br><b>1,365円 (1,300円 税別)</b> |
|---|---|--|---|

\* カット面のみはんだメッキをしております。 \*\* No.900M-T-BF2は、はんだメッキが2mmです。

## 900Lシリーズ 900L-ESD (製品P.17)、908-ESD (製品P.16)、934 (製品P.25) 用

※ こて先外径φ8.5mm

### 標準タイプ

|  |  |   |  |
|--|--|---|--|
| <b>900L-T-B B型</b><br><br><b>756円 (720円 税別)</b>                 | <b>900L-T-2B 2B型</b><br><br><b>756円 (720円 税別)</b>               | <b>900L-T-2C / 900L-T-2CF* 2C型</b><br><br><b>756円 (720円 税別)</b> | <b>900L-T-3C / 900L-T-3CF* 3C型</b><br><br><b>756円 (720円 税別)</b> |
| <b>900L-T-4C / 900L-T-4CF* 4C型</b><br><br><b>756円 (720円 税別)</b> | <b>900L-T-5C / 900L-T-5CF* 5C型</b><br><br><b>756円 (720円 税別)</b> | <b>900L-T-2.4D 2.4D型</b><br><br><b>756円 (720円 税別)</b>           | <b>900L-T-3.2D 3.2D型</b><br><br><b>756円 (720円 税別)</b>           |
| <b>900L-T-I I型</b><br><br><b>756円 (720円 税別)</b>                 | <b>900L-T-K K型</b><br><br><b>1,470円 (1,400円 税別)</b>             |   |  |

\* カット面のみはんだメッキをしております。