

商品選択表

▼キャスターをご注文の際は表中【商品記号】をお伝えください。

▼車輪をご注文の際は表中【車輪記号】をお伝えください。

商品記号		許容荷重 1個(daN)	使用車輪	車輪記号		車幅 mm	車輪 参照 ページ
品番・品種 - 車種	車輪径 (mm)			車輪品番・品種 - 車種	車輪径 (mm)		
420 FAS - R	100	120		425 S - R	100	32	319
	125	150			125	38	
	150	160			150	40	
420 FAS - WR	100	120		425 S - WR	100	34	319
	125	150			125	40	
	150	160			150	40	
420 FAS - RB	100	120		435 S - RB	100	32	320
	125	150			125	38	
	150	160			150	40	
420 FAS - WRB	100	120		435 S - WRB	100	34	320
	125	150			125	40	
	150	160			150	40	
420 FAS - CHR	100	120		434 S - CHR	100	32	321
	125	150			125	38	
	150	160			150	40	
420 FAS - XRZ	100	120		435 S - XRZ	100	32	322
	125	150			125	38	
	150	160			150	40	
420 FAS - N	100	120		429 S - N	100	32	325
	125	150			125	35	
	150	160			150	35	
420 FAS - NRB	100	120		429 S - NRB	100	29	326
	125	150			125	35	
	150	160			150	35	
420 FAS - UB	100	100		439 S - UB	100	32	330
	125	130			125	38	
	150	140			150	38	
420 FAS - URB	100	120		423 S - URB	100	32	332
	125	150			125	38	
	150	160			150	40	
420 FAS - C	100	120		426 S - C	100	30	336
	125	150			125	33	
	150	160			150	35	
420 FAS - MCB	100	120		499 S - MCB	100	33	337
	125	150			125	43	
	150	160			150	43	
420 FAS - PH	100	120		428 S - PH	100	32	338
	125	150			125	38	
	150	160			150	42	