



# コネクタ(めす)

FEMALE CONNECTOR



※印サイズの形状

単位：mm

継手の呼び	適用管外径 A		(Rc) T	E	六角対辺		I	ℓ	手締め L(約)	重量 (kg)
	呼び径	外径			H <sub>1</sub>	H				
KSA06-010E	6		1/8	4	17	14	7	25	35.5	0.038
KSA06-020E	6		1/4	4	19	14	7	30	40.5	0.048
KSA08-010E	8		1/8	6	17	17	7	25	35.5	0.045
KSA08-020E	8		1/4	6	19	17	7	30	40.5	0.056
KSA10-020E	10		1/4	8	19	19	7	30	41.5	0.062
KSA10-030E	10		3/8	8	24	19	7	32	43.5	0.085
KSA12-020E	12		1/4	10	19	22	7	30	41.5	0.070
KSA12-030E	12		3/8	10	24	22	7	32	43.5	0.093
KSA15-030E	15		3/8	12	24	27	7.5	34	46.5	0.122
KSA15-040E	15		1/2	12	30	27	7.5	39	51.5	0.173
KSA16-030E	16		3/8	13	27	30	7.5	34	46.5	0.164
KSA16-040E	16		1/2	13	30	30	7.5	39	51.5	0.195
KSA18-040E	18		1/2	14	30	32	8	39	51.5	0.201
KSA20-040E	20		1/2	17	30	36	8	39	51.5	0.231
KSA20-060E	20		3/4	17	36	36	8	41	53.5	0.279
KSA22-060E	22		3/4	18	36	36	9	41	53.5	0.261
KSA25-060E	25		3/4	20	36	41	10	41	54.5	0.307
KSA25-080E	25		1	20	46	41	10	45	58.5	0.442
KSA28-080E	28		1	22	46	46	10	47	61	0.498
KSA30-080E	30		1	25	46	46	10	47	61.5	0.489
KSA30-100E	30		1 1/4	25	55	46	10	51	65.5	0.632
KSA35-100E	35		1 1/4	28	55	55	11	51	68.5	0.737
※KSA38-120N	38		1 1/2	32	65	60	12	51	70.5	1.030
※KSA40-120N	40		1 1/2	32	65	60	12	55	74.5	1.061
※KSA42-120N	42		1 1/2	34	65	60	12	55	74.5	1.030
※KSA50-160N	50		2	40	80	75	12	60	81.5	1.770
※KSA11-020N	1/8	10.5	1/4	8	19	19	7	30	41.5	0.060
※KSA13-030N	1/4	13.8	3/8	11	24	24	7.5	34	46	0.106
※KSA17-040N	3/8	17.3	1/2	14	30	32	8	39	51.5	0.201
※KSA21-060N	1/2	21.7	3/4	18	36	36	9	41	53.5	0.264
※KSA27-080N	3/4	27.2	1	22	46	46	10	47	61	0.501
※KSA34-100N	1	34.0	1 1/4	28	55	55	11	51	68.5	1.162
※KSA43-120N	1 1/4	42.7	1 1/2	34	65	65	12	55	75.5	1.162
※KSA48-160N	1 1/2	48.6	2	40	80	75	12	60	81.5	1.787

注. 予告なしに、品質・性能・改善のため寸法を変更する事があります。