

内径 φB	幅 L	外径 φD	面取径 φD <sub>1</sub>	締付ネジ M	品番 □:材質記号	価格(円)						
						黒染め C	三価 クロムメッキ U	無電解 ニッケルメッキ M	ニッケル クロムメッキ N	SUS304 S	A2017 A	POM (白色) X
8	5	14	—	M3×3	SC 0805□	160	—	290	—	300	—	—
	6	16	13	M4×4	SC 0806□	160	—	290	—	300	180	—
	8	16	13	M4×4	SC 0808□	160	—	290	—	300	—	—
	8	18	—	M4×4	SC 0808□	—	—	—	—	—	—	220
10	10	18	13	M4×4	SC 0810□	160	220	290	240	300	—	—
	5	16	—	M3×3	SC 1005□	160	—	290	—	300	—	—
	6	18	16	M4×4	SC 1006□	160	—	290	—	300	220	—
	8	18	16	M4×4	SC 1008□	160	—	290	—	300	—	—
12	8	20	—	M4×4	SC 1008□	—	—	—	—	—	—	260
	10	20	16	M4×4	SC 1010□	160	220	290	240	300	—	—
	6	20	—	M4×4	SC 1206□	180	—	340	—	350	—	—
	8	22	20	M4×4	SC 1208□	180	—	340	—	350	270	—
12.7	8	22	—	M4×4	SC 1208□	—	—	—	—	—	—	260
	10	26	20	M5×6	SC 1210□	180	280	340	310	350	—	—
	12	26	20	M6×6	SC 1212□	180	—	340	—	350	—	—
	6	20	—	M4×4	SC 12.7-06□	200	—	350	—	360	—	—
13	8	22	—	M4×4	SC 12.7-08□	200	—	350	—	360	—	—
	10	26	20	M5×6	SC 12.7-10□	200	—	350	—	360	—	—
	12	26	20	M6×6	SC 12.7-12□	200	—	350	—	360	—	—
	6	20	—	M4×4	SC 1306□	200	—	350	—	360	—	—
14	8	22	20	M4×4	SC 1308□	200	—	350	—	360	280	—
	10	26	20	M5×6	SC 1310□	200	280	350	330	360	—	—
	12	26	20	M5×6	SC 1412□	230	310	410	330	420	—	—
15	6	24	—	M4×4	SC 1506□	230	—	410	—	420	—	—
	8	25	24	M5×6	SC 1508□	230	—	410	—	420	310	—
	10	25	24	M5×6	SC 1510□	230	—	410	—	420	—	—
	10	28	—	M5×6	SC 1510□	—	—	—	—	—	—	350
16	12	28	24	M5×6	SC 1512□	230	330	410	390	420	—	—
	6	24	—	M4×4	SC 1606□	240	—	430	—	440	—	—
	8	28	24	M5×6	SC 1608□	240	—	430	—	440	—	—
	10	28	24	M5×6	SC 1610□	240	—	430	—	440	320	—
17	10	30	—	M5×6	SC 1610□	—	—	—	—	—	—	390
	12	28	24	M5×6	SC 1612□	240	330	430	390	440	—	—
	10	30	26	M6×6	SC 1710□	280	—	480	—	500	—	—
	12	32	26	M6×6	SC 1712□	280	330	480	390	500	—	—
20	15	32	29	M6×6	SC 1815□	280	350	500	420	530	—	—
	7	30	—	M5×6	SC 2007□	280	—	520	—	530	—	—
	10	32	29	M6×6	SC 2010□	280	—	520	—	530	350	—
	12	32	29	M6×6	SC 2012□	280	—	520	—	530	—	—
22	12	34	—	M6×6	SC 2012□	—	—	—	—	—	—	420
	15	32	29	M6×6	SC 2015□	280	350	520	440	530	—	—
	18	38	34	M8×8	SC 2218□	360	420	600	500	660	—	—
	12	38	37	M6×6	SC 2512□	360	—	670	—	820	530	—
25	12	38	—	M6×6	SC 2512□	—	—	—	—	—	—	500
	15	38	37	M6×6	SC 2515□	360	—	670	—	820	—	—
	18	42	38	M8×8	SC 2518□	360	470	670	550	820	—	—
	12	38	—	M6×6	SC 25.4-12□	420	—	770	—	880	—	—
25.4	15	38	—	M6×6	SC 25.4-15□	420	—	770	—	880	—	—
	18	42	38	M8×8	SC 25.4-18□	420	—	770	—	880	—	—
	18	45	40	M8×8	SC 2818□	420	—	770	—	880	—	—
30	12	45	—	M6×6	SC 3012□	—	—	—	—	—	—	600
	14	45	42	M8×8	SC 3014□	420	—	820	—	930	540	—
	16	45	42	M8×8	SC 3016□	420	—	820	—	930	—	—
	18	49	42	M8×8	SC 3018□	420	—	820	—	930	—	—
32	20	49	42	M8×8	SC 3020□	420	600	820	710	930	—	—
	20	53	44	M8×8	SC 3220□	530	—	930	—	1,200	—	—
	15	50	47	M8×8	SC 3515□	530	—	990	—	1,370	820	—
	18	55	47	M8×8	SC 3518□	530	—	990	—	1,370	—	—
35	20	59	47	M8×8	SC 3520□	530	820	990	930	1,370	—	—
	22	64	50	M10×12	SC 3822□	900	—	1,200	—	1,750	—	—
40	18	60	55	M10×8	SC 4018□	900	—	1,260	—	1,910	1,150	—
	22	72	55	M10×12	SC 4022□	900	1,150	1,260	1,200	1,910	—	—
45	22	75	60	M10×12	SC 4522□	990	—	1,420	—	2,180	—	—
	20	70	65	M10×8	SC 5020□	1,020	—	1,530	—	2,290	1,370	—
50	25	79	65	M10×12	SC 5025□	1,020	—	1,530	—	2,290	—	—
	28	81	70	M12×12	SC 5528□	1,590	—	—	—	3,710	—	—
60	28	88	75	M12×12	SC 6028□	1,750	—	—	—	4,470	—	—
	28	94	85	M12×12	SC 6528□	2,290	—	—	—	—	—	—
70	32	113	90	M16×16	SC 7032□	3,380	—	—	—	—	—	—
	32	119	95	M16×16	SC 7532□	4,260	—	—	—	—	—	—
80	32	126	105	M16×16	SC 8032□	4,580	—	—	—	—	—	—

セットカラー

ノーマル

銅管用

六角  
シャフト用

角シャフト用

2穴付

3穴付

3ザグリ穴付

4穴付

2ネジ穴付

3ネジ穴付

ベアリング  
固定用

ロカット

内径ネジ

六角  
内径ネジ

キー逃がし  
溝付

ダンパー付

追加加工

オプション

技術資料

SCK

SC

SCS

SCSS

