

適合 ベアリング	内径 φB	ボス径 φD <sub>1</sub>	幅		外径 φD	締付ネジ M	品番 □:材質記号	価格(円)		
			L	L <sub>1</sub>				黒染め C	無電解 ニッケルメッキ M	SUS304 S
693ZZ 623ZZ	3	5	7.5	2.5	7	★M3×3	SC 0307□B	280	310	460
694ZZ 624ZZ	4	6	7.5	2.5	8	★M3×3	SC 0407□B	280	310	460
695ZZ 605ZZ 625ZZ	5	7.2	7.5	2.5	11	★M3×3	SC 0507□B	350	380	530
606ZZ	6	8.4	7.5	2.5	13	M3×3	SC 0607□B1	390	420	550
626ZZ		9.2	7.5	2.5	13	M3×3	SC 0607□B2	390	420	550
696ZZ		8	7.5	2.5	13	M3×3	SC 0607□B3	390	420	550
608ZZ	8	11.7	9.5	2.5	18	M4×4	SC 0809□B1	420	500	660
628ZZ		11.4	9.5	2.5	18	M4×4	SC 0809□B2	420	500	660
698ZZ		10.4	9.5	2.5	18	M4×4	SC 0809□B3	420	500	660
6000ZZ	10	14.2	11	3	20	M5×6	SC 1011□B1	460	550	770
6200ZZ		16.7	11	3	20	M5×6	SC 1011□B2	460	550	770
6900ZZ		13.2	11	3	20	M5×6	SC 1011□B3	460	550	770
6001ZZ	12	17.2	11	3	22	M5×6	SC 1211□B1	550	600	880
6201ZZ		17.7	11	3	22	M5×6	SC 1211□B2	550	600	880
6901ZZ		15.2	11	3	22	M5×6	SC 1211□B3	550	600	880
6002ZZ	15	20.2	11	3	25	M5×6	SC 1511□B1	600	680	930
6202ZZ		21.2	11	3	25	M5×6	SC 1511□B2	600	680	930
6902ZZ		18.7	11	3	25	M5×6	SC 1511□B3	600	680	930
6003ZZ	17	22.2	13	3	28	M6×6	SC 1713□B1	700	770	1,090
6203ZZ		24.2	13	3	28	M6×6	SC 1713□B2	700	770	1,090
6903ZZ		20.2	13	3	28	M6×6	SC 1713□B3	700	770	1,090
6004ZZ	20	25.2	13	3	35	M6×6	SC 2013□B1	750	820	1,200
6204ZZ		27.2	13	3	35	M6×6	SC 2013□B2	750	820	1,200
6904ZZ		24.7	13	3	35	M6×6	SC 2013□B3	750	820	1,200
6005ZZ	25	31.2	13.5	3.5	38	M6×6	SC 2513□B1	820	930	1,530
6205ZZ		33.2	13.5	3.5	38	M6×6	SC 2513□B2	820	930	1,530
6905ZZ		30.2	13.5	3.5	38	M6×6	SC 2513□B3	820	930	1,530
6006ZZ	30	38.2	15.5	3.5	45	M8×8	SC 3015□B1	930	1,090	1,800
6206ZZ		40.2	15.5	3.5	45	M8×8	SC 3015□B2	930	1,090	1,800
6906ZZ		35.2	15.5	3.5	45	M8×8	SC 3015□B3	930	1,090	1,800
6007ZZ	35	43.2	16.5	4.5	50	M8×8	SC 3516□B1	1,200	1,310	2,180
6207ZZ		46.2	16.5	4.5	50	M8×8	SC 3516□B2	1,200	1,310	2,180
6907ZZ		41.2	16.5	4.5	50	M8×8	SC 3516□B3	1,200	1,310	2,180
6008ZZ	40	48.2	18.5	4.5	60	M10×8	SC 4018□B1	1,640	1,800	2,840
6208ZZ		52.2	18.5	4.5	60	M10×8	SC 4018□B2	1,640	1,800	2,840
6908ZZ		46.2	18.5	4.5	60	M10×8	SC 4018□B3	1,640	1,800	2,840

★印は止めネジが一本となります。

ノーマル

鋼管用

六角  
シャフト用

角シャフト用

2穴付

3穴付

3ザグリ穴付

4穴付

2ネジ穴付

3ネジ穴付

ベアリング  
固定用

ロカット

内径ネジ

六角  
内径ネジ

キー逃がし  
溝付

ダンパー付

追加工

オプション

技術資料

SCK

SC

SCS

SCSS