

レール サイズ	対応メーカー・シリーズ			W	H	B	P	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社							品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	25	46	5	13	5.5	M5×12	LSG-01	350	LSG-01S	640
	LWH15	LS15AL	HSR15A	25	53	6	13	5.5	M5×12	LSG-02	410	LSG-02S	690
	—	LH15AN	—	25	59	6	13	5.5	M5×12	LSG-03	410	LSG-03S	690
20	—	—	SRS20M	32	50	5	18	5.5	M5×12	LSG-04	410	LSG-04S	690
	LWH20	LS20AL, LH20AN	HSR20A	32	68	8	18	6.6	M6×12	LSG-05	460	LSG-05S	810
25	—	—	SRS25M	32	60	10	18	6.6	M6×12	LSG-06	410	LSG-06S	760
	LWH25	LS25AL, LH25AL	HSR25A	32	71	10	18	6.6	M6×12	LSG-07	460	LSG-07S	810
30	LWH30	LS30AL, LH30AL	HSR30A	38	80	10	22	9.0	M8×16	LSG-08	530	LSG-08S	990
35	LWH35	LS35AL, LH35AL	HSR35A	45	88	10	25	9.0	M8×16	LSG-09	580	LSG-09S	1,100

リニアストッパー

セットベース



レール サイズ	対応メーカー・シリーズ			W	H	A	B	P	M(細目)	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社									品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	25	46	38.5	5	13	M6×P0.75	5.5	M5×12	LSGN-01	460	LSGN-01S	810
	LWH15	LS15AL	HSR15A	25	53	45.0	6	13	M6×P0.75	5.5	M5×12	LSGN-02	530	LSGN-02S	870
	—	LH15AN	—	25	59	51.5	6	13	M6×P0.75	5.5	M5×12	LSGN-03	530	LSGN-03S	870
20	—	—	SRS20M	32	50	42.5	5	18	M8×P1.0	5.5	M5×12	LSGN-04	530	LSGN-04S	870
	LWH20	LS20AL, LH20AN	HSR20A	32	68	60.5	8	18	M8×P1.0	6.6	M6×12	LSGN-05	580	LSGN-05S	990
25	—	—	SRS25M	32	60	52.5	10	18	M8×P1.0	6.6	M6×12	LSGN-06	530	LSGN-06S	920
	LWH25	LS25AL, LH25AL	HSR25A	32	71	63.5	10	18	M8×P1.0	6.6	M6×12	LSGN-07	580	LSGN-07S	990
30	LWH30	LS30AL, LH30AL	HSR30A	38	80	72.5	10	22	M8×P1.0	9.0	M8×16	LSGN-08	640	LSGN-08S	1,160
35	LWH35	LS35AL, LH35AL	HSR35A	45	88	80.5	10	25	M8×P1.0	9.0	M8×16	LSGN-09	690	LSGN-09S	1,280

レール サイズ	対応メーカー・シリーズ			W	H	A	B	P	M	D	付属品		鉄(黒染め)		ステンレス		
	IKO社	NSK社	THK社								ボルト	D1	L	品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	25	46	38.5	5	13	M4	5.5	M5×12	15	11	LSGU-01	810	LSGU-01S	1,160
	LWH15	LS15AL	HSR15A	25	53	45.5	6	13	M4	5.5	M5×12	15	11	LSGU-02	880	LSGU-02S	1,220
	—	LH15AN	—	25	59	51.5	6	13	M4	5.5	M5×12	15	11	LSGU-03	880	LSGU-03S	1,220
20	—	—	SRS20M	32	50	42.5	5	18	M4	5.5	M5×12	15	11	LSGU-04	880	LSGU-04S	1,220
	LWH20	LS20AL, LH20AN	HSR20A	32	68	58.0	8	18	M5	6.6	M6×12	20	13	LSGU-05	990	LSGU-05S	1,400
25	—	—	SRS25M	32	60	52.5	10	18	M4	6.6	M6×12	15	11	LSGU-06	880	LSGU-06S	1,270
	LWH25	LS25AL, LH25AL	HSR25A	32	71	61.0	10	18	M5	6.6	M6×12	20	13	LSGU-07	990	LSGU-07S	1,400
30	LWH30	LS30AL, LH30AL	HSR30A	38	80	67.5	10	22	M5	9.0	M8×16	25	13	LSGU-08	1,100	LSGU-08S	1,620
35	LWH35	LS35AL, LH35AL	HSR35A	45	88	75.5	10	25	M5	9.0	M8×16	25	13	LSGU-09	1,150	LSGU-09S	1,740

抜け止め用

コンパクト

ストッパーブロック

ストッパーボルト
ウレタンボルト

レール サイズ	対応メーカー・シリーズ			W	H	A	B	P	M(細目)	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社									品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	25	46	38.5	5	13	M6×P0.75	5.5	M5×12	LSGN-01-U	1,310	LSGN-01S-U	1,660
	LWH15	LS15AL	HSR15A	25	53	45.0	6	13	M6×P0.75	5.5	M5×12	LSGN-02-U	1,380	LSGN-02S-U	1,720
	—	LH15AN	—	25	59	51.5	6	13	M6×P0.75	5.5	M5×12	LSGN-03-U	1,380	LSGN-03S-U	1,720
20	—	—	SRS20M	32	50	42.5	5	18	M8×P1.0	5.5	M5×12	LSGN-04-U	1,440	LSGN-04S-U	1,780
	LWH20	LS20AL, LH20AN	HSR20A	32	68	60.5	8	18	M8×P1.0	6.6	M6×12	LSGN-05-U	1,490	LSGN-05S-U	1,900
25	—	—	SRS25M	32	60	52.5	10	18	M8×P1.0	6.6	M6×12	LSGN-06-U	1,440	LSGN-06S-U	1,830
	LWH25	LS25AL, LH25AL	HSR25A	32	71	63.5	10	18	M8×P1.0	6.6	M6×12	LSGN-07-U	1,490	LSGN-07S-U	1,900
30	LWH30	LS30AL, LH30AL	HSR30A	38	80	72.5	10	22	M8×P1.0	9.0	M8×16	LSGN-08-U	1,550	LSGN-08S-U	2,070
35	LWH35	LS35AL, LH35AL	HSR35A	45	88	80.5	10	25	M8×P1.0	9.0	M8×16	LSGN-09-U	1,600	LSGN-09S-U	2,190