

レール サイズ	対応メーカー・シリーズ			W	H	B	E	F	P	T	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社										品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	32	30	18	12	12	16	25	5.5	M5×12	LSD-01	1,330	LSD-01S	2,310
	LWH15	LS15AL	HSR15A	32	38	18	12	12	16	25	5.5	M5×12	LSD-02	1,330	LSD-02S	2,310
	—	LH15AN	—	32	45	18	12	12	16	25	5.5	M5×12	LSD-03	1,390	LSD-03S	2,430
20	LWH20	LS20AL, LH20AN	HSR20A	32	35	18	12	12	16	25	5.5	M5×12	LSD-04	1,330	LSD-04S	2,310
	—	—	SRS20M	32	40	23	12	12	18	32	6.6	M6×12	LSD-05	1,390	LSD-05S	2,840
25	LWH25	LS25AL, LH25AL	HSR25A	32	50	23	12	12	18	32	6.6	M6×12	LSD-06	1,510	LSD-06S	2,840
	—	—	SRS25M	32	40	23	12	12	18	32	6.6	M6×12	LSD-07	1,850	LSD-07S	3,700
30	LWH30	LS30AL, LH30AL	HSR30A	38	57	28	16	16	20	38	9.0	M8×16	LSD-07	1,850	LSD-07S	3,700
35	LWH35	LS35AL, LH35AL	HSR35A	45	63	31	16	16	25	45	9.0	M8×16	LSD-08	2,260	LSD-08S	4,920

レール サイズ	対応メーカー・シリーズ			W	H	A	B	E	F	P	T	M(細目)	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社												品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	32	30	23.5	18	12	12	16	25	M6×P0.75	5.5	M5×12	LSDN-01	1,450	LSDN-01S	2,540
	LWH15	LS15AL	HSR15A	32	38	31.5	18	12	12	16	25	M6×P0.75	5.5	M5×12	LSDN-02	1,450	LSDN-02S	2,540
	—	LH15AN	—	32	43	35.5	18	12	12	16	25	M6×P0.75	5.5	M5×12	LSDN-03	1,510	LSDN-03S	2,610
20	—	—	SRS20M	32	35	27.5	18	12	12	16	25	M8×P1.0	5.5	M5×12	LSDN-04	1,450	LSDN-04S	2,540
	LWH20	LS20AL	—	32	43	35.5	18	12	12	16	25	M8×P1.0	5.5	M5×12	LSDN-05	1,510	LSDN-05S	2,610
	—	LH20AN	HSR20A	32	45	37.5	18	12	12	16	25	M8×P1.0	5.5	M5×12	LSDN-06	1,510	LSDN-06S	2,610
25	—	—	SRS25M	32	40	32.5	23	12	12	18	32	M8×P1.0	6.6	M6×12	LSDN-07	1,510	LSDN-07S	2,890
	LWH25	LS25AL	—	32	50	40.5	23	12	12	18	32	M8×P1.0	6.6	M6×12	LSDN-08	1,620	LSDN-08S	2,890
	—	LH25AL	HSR25A	32	50	43.5	23	12	12	18	32	M8×P1.0	6.6	M6×12	LSDN-09	1,620	LSDN-09S	2,890
30	LWH30	LS30AL, LH30AL	HSR30A	38	57	49.5	28	16	16	20	38	M8×P1.0	9.0	M8×16	LSDN-10	1,970	LSDN-10S	3,870
35	LWH35	LS35AL, LH35AL	HSR35A	45	63	55.5	31	16	16	25	45	M8×P1.0	9.0	M8×16	LSDN-11	2,380	LSDN-11S	5,080

レール サイズ	対応メーカー・シリーズ			W	H	A	B	E	F	P	P1	e	T	M(細目)	D	d	付属品 ボルト ワッシャー	鉄(黒染め)		ステンレス		
	IKO社	NSK社	THK社															品番	価格(円)	品番	価格(円)	
15	—	—	SRS15M	32	30	23.5	18	12	12	16	16	6	25	M6×P0.75	5.5	4X6	M5×12	4X10	LSDN-01N	1,790	LSDN-01SN	3,000
	LWH15	LS15AL	HSR15A	32	38	31.5	18	12	12	16	16	6	25	M6×P0.75	5.5	4X6	M5×12	4X10	LSDN-02N	1,790	LSDN-02SN	3,000
	—	LH15AN	—	32	43	35.5	18	12	12	16	16	6	25	M6×P0.75	5.5	4X6	M5×12	4X10	LSDN-03N	1,850	LSDN-03SN	3,070
20	—	—	SRS20M	32	35	27.5	18	12	12	16	16	6	25	M8×P1.0	5.5	4X6	M5×12	4X10	LSDN-04N	1,790	LSDN-04SN	3,000
	LWH20	LS20AL	—	32	43	35.5	18	12	12	16	16	6	25	M8×P1.0	5.5	4X6	M5×12	4X10	LSDN-05N	1,850	LSDN-05SN	3,070
	—	LH20AN	HSR20A	32	45	37.5	18	12	12	16	16	6	25	M8×P1.0	5.5	4X6	M5×12	4X10	LSDN-06N	1,850	LSDN-06SN	3,070
25	—	—	SRS25M	32	40	32.5	23	12	12	18	18	6	32	M8×P1.0	6.6	4X6	M6×12	4X10	LSDN-07N	1,850	LSDN-07SN	3,360
	LWH25	LS25AL	—	32	50	40.5	23	12	12	18	18	6	32	M8×P1.0	6.6	4X6	M6×12	4X10	LSDN-08N	1,970	LSDN-08SN	3,360
	—	LH25AL	HSR25A	32	50	43.5	23	12	12	18	18	6	32	M8×P1.0	6.6	4X6	M6×12	4X10	LSDN-09N	1,970	LSDN-09SN	3,360
30	LWH30	LS30AL, LH30AL	HSR30A	38	57	49.5	28	16	16	20	8	38	M8×P1.0	9.0	5X8	M8×16	5X12	LSDN-10N	2,310	LSDN-10SN	4,330	
35	LWH35	LS35AL, LH35AL	HSR35A	45	63	55.5	31	16	16	25	8	45	M8×P1.0	9.0	5X8	M8×16	5X12	LSDN-11N	2,720	LSDN-11SN	5,540	

レール サイズ	対応メーカー・シリーズ			W	H	A	B	E	F	P	T	M	D	付属品 ボルト	D1	L	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社														品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	32	30	22.5	18	12	12	16	25	M4	5.5	M5×12	15	11	LSDU-01	1,800	LSDU-01S	2,890
	LWH15	LS15AL	HSR15A	32	38	30.5	18	12	12	16	25	M4	5.5	M5×12	15	11	LSDU-02	1,800	LSDU-02S	2,890
	—	LH15AN	—	32	45	35.0	18	12	12	16	25	M5	5.5	M5×12	20	13	LSDU-03	1,920	LSDU-03S	3,020
20	—	—	SRS20M	32	30	22.5	18	12	12	16	25	M4	5.5	M5×12	15	11	LSDU-01	1,800	LSDU-01S	2,890
	LWH20	LS20AL, LS20AN	HSR20A	32	45	35.0	18	12	12	16	25	M5	5.5	M5×12	20	13	LSDU-03	1,920	LSDU-03S	3,020
25	—	—	SRS25M	32	38	30.5	18	12	12	16	25	M4	5.5	M5×12	15	11	LSDU-02	1,800	LSDU-02S	2,890
	LWH25	LS25AL, LH25AL	HSR25A	32	50	40.0	23	12	12	18	32	M5	6.6	M6×12	20	13	LSDU-04	2,030	LSDU-04S	3,300
30	LWH30	LS30AL, LH30AL	HSR30A	38	57	44.5	28	16	16	20	38	M5	9.0	M8×16	25	13	LSDU-05	2,430	LSDU-05S	4,330
35	LWH35	LS35AL, LH35AL	HSR35A	45	63	50.5	31	16	16	25	45	M5	9.0	M8×16	25	13	LSDU-06	2,840	LSDU-06S	5,540

レール サイズ	対応メーカー・シリーズ			W	H	A	B	E	F	P	T	M(細目)	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社												品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	32	30	23.5	18	12	12	16	25	M6×P0.75	5.5	M5×12	LSDN-01-U	2,300	LSDN-01S-U	3,390
	LWH15	LS15AL	HSR15A	32	38	31.5	18	12	12	16	25	M6×P0.75	5.5	M5×12	LSDN-02-U	2,300	LSDN-02S-U	3,390
	—	LH15AN	—	32	43	35.5	18	12	12	16	25	M6×P0.75	5.5	M5×12	LSDN-03-U	2,360	LSDN-03S-U	3,460
20	—	—	SRS20M	32	35	27.5	18	12	12	16	25	M8×P1.0	5.5	M5×12	LSDN-04-U	2,360	LSDN-04S-U	3,450
	LWH20	LS20AL	—	32	43	35.5	18	12	12	16	25	M8×P1.0	5.5	M5×12	LSDN-05-U	2,420	LSDN-05S-U	3,520
	—	LH20AN	HSR20A	32	45	37.5	18	12	12	16	25	M8×P1.0	5.5	M5×12	LSDN-06-U	2,420	LSDN-06S-U	3,520
25	—	—	SRS25M	32	40	32.5	23	12	12	18	32	M8×P1.0	6.6	M6×12	LSDN-07-U	2,420	LSDN-07S-U	3,800
	LWH25	LS25AL	—	32	50	40.5	23	12	12	18	32	M8×P1.0	6.6	M6×12	LSDN-08-U	2,530	LSDN-08S-U	3,800
30	LWH30	LS30AL, LH30AL	HSR30A	38	57	49.5	28	16	16	20	38	M8×P1.0	9.0	M8×16	LSDN-09-U	2,530	LSDN-09S-U	3,800
	—	LH25AL	HSR25A	32	50	43.5	23	12	12	18	32	M8×P1.0	6.6	M6×12	LSDN-10-U	2,880	LSDN-10S-U	4,780
35	LWH35	LS35AL, LH35AL	HSR35A	45	63	55.5	31	16	16	25	45	M8×P1.0	9.0	M8×16	LSDN-11-U	3,290	LSDN-11S-U	5,990



抜け止め用

コンパクト

ストッパーブロック

ストッパーボルト  
ウレタンボルト