

レール サイズ	対応メーカー・シリーズ			W	H	B	J	P	T	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社									品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	50	30	12	18	35	12	5.5	M5×16	LSC-01	1,450	LSC-01S	2,080
	LWH15	LS15AL	HSR15A	50	38	12	18	35	12	5.5	M5×16	LSC-02	1,450	LSC-02S	2,080
	—	LH15AN	—	50	43	12	18	35	12	5.5	M5×16	LSC-03	1,510	LSC-03S	2,200
20	—	—	SRS20M	50	38	12	18	35	12	5.5	M5×16	LSC-02	1,450	LSC-02S	2,080
	LWH20	LS20AL, LH20AN	HSR20A	50	45	12	20	35	12	5.5	M5×16	LSC-04	1,560	LSC-04S	2,200
25	—	—	SRS25M	50	40	16	20	35	16	6.6	M6×20	LSC-05	1,620	LSC-05S	2,430
	LWH25	LS25AL, LH25AL	HSR25A	50	51	16	20	35	16	6.6	M6×20	LSC-06	1,680	LSC-06S	2,430
30	LWH30	LS30AL, LH30AL	HSR30A	65	57	16	24	45	16	9.0	M8×20	LSC-07	1,790	LSC-07S	2,770
35	LWH35	LS35AL, LH35AL	HSR35A	65	63	16	24	45	16	9.0	M8×20	LSC-08	1,850	LSC-08S	2,950

レール サイズ	対応メーカー・シリーズ			W	H	A	B	J	P	T	M(細目)	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社											品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	50	30	23.5	12	18	35	12	M6×P0.75	5.5	M5×16	LSCN-01	1,560	LSCN-01S	2,150
	LWH15	LS15AL	HSR15A	50	38	31.5	12	18	35	12	M6×P0.75	5.5	M5×16	LSCN-02	1,560	LSCN-02S	2,260
	—	LH15AN	—	50	43	35.5	12	18	35	12	M6×P0.75	5.5	M5×16	LSCN-03	1,620	LSCN-03S	2,380
20	—	—	SRS20M	50	35	27.5	12	20	35	12	M8×P1.0	5.5	M5×16	LSCN-04	1,560	LSCN-04S	2,260
	—	LS20AL	—	50	43	35.5	12	20	35	12	M8×P1.0	5.5	M5×16	LSCN-05	1,620	LSCN-05S	2,380
	LWH20	LH20AN	HSR20A	50	45	37.5	12	20	35	12	M8×P1.0	5.5	M5×16	LSCN-06	1,680	LSCN-06S	2,380
25	—	—	SRS25M	50	40	32.5	16	20	35	16	M8×P1.0	6.6	M6×20	LSCN-07	1,740	LSCN-07S	2,610
	—	LS25AL	—	50	48	40.5	16	20	35	16	M8×P1.0	6.6	M6×20	LSCN-08	1,790	LSCN-08S	2,610
	LWH25	LH25AL	HSR25A	50	51	43.5	16	20	35	16	M8×P1.0	6.6	M6×20	LSCN-09	1,790	LSCN-09S	2,610
30	LWH30	LS30AL, LH30AL	HSR30A	65	57	49.5	16	24	45	16	M8×P1.0	9.0	M8×20	LSCN-10	1,910	LSCN-10S	2,950
35	LWH35	LS35AL, LH35AL	HSR35A	65	63	55.5	16	24	45	16	M8×P1.0	9.0	M8×20	LSCN-11	1,970	LSCN-11S	3,120

レール サイズ	対応メーカー・シリーズ			W	H	A	B	J	P	P1	T	M(細目)	D	d	付属品 ボルト / ナット	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社													品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	50	30	23.5	12	18	35	18	12	M6×P0.75	5.5	4X6	M5×16 4×10	LSCN-01N	1,910	LSCN-01SN	2,720
	LWH15	LS15AL	HSR15A	50	38	31.5	12	18	35	18	12	M6×P0.75	5.5	4X6	M5×16 4×10	LSCN-02N	1,910	LSCN-02SN	2,720
	—	LH15AN	—	50	43	35.5	12	18	35	18	12	M6×P0.75	5.5	4X6	M5×16 4×10	LSCN-03N	1,970	LSCN-03SN	2,840
20	—	—	SRS20M	50	35	27.5	12	20	35	18	12	M8×P1.0	5.5	4X6	M5×16 4×10	LSCN-04N	1,910	LSCN-04SN	2,720
	—	LS20AL	—	50	43	35.5	12	20	35	18	12	M8×P1.0	5.5	4X6	M5×16 4×10	LSCN-05N	1,970	LSCN-05SN	2,840
	LWH20	LH20AN	HSR20A	50	45	37.5	12	20	35	18	12	M8×P1.0	5.5	4X6	M5×16 4×10	LSCN-06N	2,020	LSCN-06SN	2,840
25	—	—	SRS25M	50	40	32.5	16	20	35	18	16	M8×P1.0	6.6	4X6	M6×20 4×10	LSCN-07N	2,080	LSCN-07SN	3,070
	—	LS25AL	—	50	48	40.5	16	20	35	18	16	M8×P1.0	6.6	4X6	M6×20 4×10	LSCN-08N	2,150	LSCN-08SN	3,070
	LWH25	LH25AL	HSR25A	50	51	43.5	16	20	35	18	16	M8×P1.0	6.6	4X6	M6×20 4×10	LSCN-09N	2,150	LSCN-09SN	3,070
30	LWH30	LS30AL, LH30AL	HSR30A	65	57	49.5	16	24	45	20	16	M8×P1.0	9.0	5X8	M8×20 5×12	LSCN-10N	2,260	LSCN-10SN	3,410
35	LWH35	LS35AL, LH35AL	HSR35A	65	63	55.5	16	24	45	20	16	M8×P1.0	9.0	5X8	M8×20 5×12	LSCN-11N	2,310	LSCN-11SN	3,590

レール サイズ	対応メーカー・シリーズ			W	H	A	B	J	P	T	M	D	付属品 ボルト	D1	L	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社													品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	50	30	22.5	12	18	35	12	M4	5.5	M5×16	15	11	LSCU-01	1,910	LSCU-01S	2,500
	LWH15	LS15AL	HSR15A	50	38	30.5	12	18	35	12	M4	5.5	M5×16	15	11	LSCU-02	1,910	LSCU-02S	2,610
	—	LH15AN	—	50	43	35.5	12	18	35	12	M4	5.5	M5×16	15	11	LSCU-03	1,970	LSCU-03S	2,730
20	—	—	SRS20M	50	38	30.5	12	18	35	12	M4	5.5	M5×16	15	11	LSCU-02	1,910	LSCU-02S	2,610
	LWH20	LS20AL, LH20AN	HSR20A	50	45	35.0	12	20	35	12	M5	5.5	M5×16	20	13	LSCU-04	2,090	LSCU-04S	2,790
25	—	—	SRS25M	50	40	30.0	16	20	35	16	M5	6.6	M6×20	20	13	LSCU-05	2,150	LSCU-05S	3,020
	LWH25	LS25AL, LH25AL	HSR25A	50	51	41.0	16	20	35	16	M5	6.6	M6×20	20	13	LSCU-06	2,200	LSCU-06S	3,020
30	LWH30	LS30AL, LH30AL	HSR30A	65	57	44.5	16	24	45	16	M5	9.0	M8×20	25	13	LSCU-07	2,370	LSCU-07S	3,410
35	LWH35	LS35AL, LH35AL	HSR35A	65	63	50.5	16	24	45	16	M5	9.0	M8×20	25	13	LSCU-08	2,430	LSCU-08S	3,580

レール サイズ	対応メーカー・シリーズ			W	H	A	B	J	P	T	M(細目)	D	付属品 ボルト	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社											品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	50	30	23.5	12	18	35	12	M6×P0.75	5.5	M5×16	LSCN-01-U	2,410	LSCN-01S-U	3,000
	LWH15	LS15AL	HSR15A	50	38	31.5	12	18	35	12	M6×P0.75	5.5	M5×16	LSCN-02-U	2,410	LSCN-02S-U	3,110
	—	LH15AN	—	50	43	35.5	12	18	35	12	M6×P0.75	5.5	M5×16	LSCN-03-U	2,470	LSCN-03S-U	3,230
20	—	—	SRS20M	50	35	27.5	12	20	35	12	M8×P1.0	5.5	M5×16	LSCN-04-U	2,470	LSCN-04S-U	3,170
	—	LS20AL	—	50	43	35.5	12	20	35	12	M8×P1.0	5.5	M5×16	LSCN-05-U	2,530	LSCN-05S-U	3,290
	LWH20	LH20AN	HSR20A	50	45	37.5	12	20	35	12	M8×P1.0	5.5	M5×16	LSCN-06-U	2,590	LSCN-06S-U	3,290
25	—	—	SRS25M	50	40	32.5	16	20	35	16	M8×P1.0	6.6	M6×20	LSCN-07-U	2,650	LSCN-07S-U	3,520
	—	LS25AL	—	50	48	40.5	16	20	35	16	M8×P1.0	6.6	M6×20	LSCN-08-U	2,700	LSCN-08S-U	3,520
LWH25	LH25AL	HSR25A	50	51	43.5	16	20	35	16	M8×P1.0	6.6	M6×20	LSCN-09-U	2,700	LSCN-09S-U	3,520	
30	LWH30	LS30AL, LH30AL	HSR30A	65	57	49.5	16	24	45	16	M8×P1.0	9.0	M8×20	LSCN-10-U	2,820	LSCN-10S-U	3,860
35	LWH35	LS35AL, LH35AL	HSR35A	65	63	55.5	16	24	45	16	M8×P1.0	9.0	M8×20	LSCN-11-U	2,880	LSCN-11S-U	4,030

リニアストッパー

セットベース



抜け止め用

コンパクト

ストッパーブロック

ストッパーボルト
ウレタンボルト