

## リニアストッパー

## セットベース



## 抜け止め用

## コンパクト

## ストッパーブロック

ストッパーボルト  
ウレタンボルト

| レール<br>サイズ | 対応メーカー・シリーズ |                |        | W  | H  | E  | S1   | S2 | T  | D   | 付属品<br>ボルト | 鉄(黒染め) |       | ステンレス   |       |
|------------|-------------|----------------|--------|----|----|----|------|----|----|-----|------------|--------|-------|---------|-------|
|            | IKO社        | NSK社           | THK社   |    |    |    |      |    |    |     |            | 品番     | 価格(円) | 品番      | 価格(円) |
| 15         | —           | —              | SRS15M | 32 | 30 | 9  | 15   | 11 | 12 | 5.5 | M5×35      | LSF-01 | 1,100 | LSF-01S | 1,510 |
|            | LWH15       | LS15AL         | HSR15A | 32 | 38 | 9  | 15   | 16 | 12 | 5.5 | M5×40      | LSF-02 | 1,100 | LSF-02S | 1,560 |
|            | —           | LH15AN         | —      | 32 | 43 | 9  | 15   | 16 | 12 | 5.5 | M5×45      | LSF-03 | 1,160 | LSF-03S | 1,620 |
| 20         | —           | —              | SRS20M | 32 | 35 | 9  | 17.5 | 12 | 12 | 5.5 | M5×40      | LSF-04 | 1,100 | LSF-04S | 1,510 |
|            | —           | LS20AL         | —      | 32 | 43 | 9  | 17.5 | 17 | 12 | 5.5 | M5×45      | LSF-05 | 1,160 | LSF-05S | 1,620 |
|            | LWH20       | LH20AN         | HSR20A | 32 | 45 | 9  | 17.5 | 19 | 12 | 5.5 | M5×50      | LSF-06 | 1,160 | LSF-06S | 1,740 |
| 25         | —           | —              | SRS25M | 32 | 40 | 7  | 19   | 16 | 16 | 6.6 | M6×45      | LSF-07 | 1,330 | LSF-07S | 1,740 |
|            | —           | LS25AL         | —      | 32 | 48 | 7  | 19   | 19 | 16 | 6.6 | M6×50      | LSF-08 | 1,330 | LSF-08S | 1,850 |
|            | LWH25       | LH25AL         | HSR25A | 32 | 50 | 7  | 19   | 23 | 16 | 6.6 | M6×55      | LSF-09 | 1,330 | LSF-09S | 1,850 |
| 30         | LWH30       | LS30AL, LH30AL | HSR30A | 40 | 57 | 10 | 22   | 27 | 16 | 9.0 | M8×60      | LSF-10 | 1,330 | LSF-10S | 2,080 |
| 35         | LWH35       | LS35AL, LH35AL | HSR35A | 50 | 65 | 10 | 30   | 30 | 16 | 9.0 | M8×70      | LSF-11 | 1,560 | LSF-11S | 2,260 |

| レール<br>サイズ | 対応メーカー・シリーズ |                |        | W  | H  | A    | E  | F    | S1   | S2 | P  | T  | M(細目)    | D   | 付属品<br>ボルト | 鉄(黒染め)  |       | ステンレス    |       |
|------------|-------------|----------------|--------|----|----|------|----|------|------|----|----|----|----------|-----|------------|---------|-------|----------|-------|
|            | IKO社        | NSK社           | THK社   |    |    |      |    |      |      |    |    |    |          |     |            | 品番      | 価格(円) | 品番       | 価格(円) |
| 15         | —           | —              | SRS15M | 44 | 30 | 23.5 | 7  | 37   | 15   | 11 | 16 | 12 | M6×P0.75 | 5.5 | M5×35      | LSFN-01 | 1,220 | LSFN-01S | 2,080 |
|            | LWH15       | LS15AL, LH15AN | HSR15A | 44 | 38 | 31.5 | 7  | 37   | 15   | 16 | 16 | 12 | M6×P0.75 | 5.5 | M5×40      | LSFN-02 | 1,280 | LSFN-02S | 2,310 |
| 20         | —           | —              | SRS20M | 44 | 35 | 27.5 | 7  | 37   | 17.5 | 12 | 12 | 12 | M8×P1.0  | 5.5 | M5×40      | LSFN-03 | 1,280 | LSFN-03S | 2,310 |
|            | LWH20       | LS20AL, LH20AN | HSR20A | 44 | 50 | 37.5 | 7  | 37   | 17.5 | 19 | 12 | 12 | M8×P1.0  | 5.5 | M5×55      | LSFN-04 | 1,330 | LSFN-04S | 2,540 |
| 25         | —           | —              | SRS25M | 44 | 38 | 31.5 | 7  | 37   | 15   | 16 | 16 | 12 | M6×P0.75 | 5.5 | M5×40      | LSFN-02 | 1,280 | LSFN-02S | 2,310 |
|            | LWH25       | LS25AL, LH25AL | HSR25A | 44 | 50 | 43.5 | 7  | 37   | 19   | 23 | 12 | 16 | M8×P1.0  | 6.6 | M6×55      | LSFN-05 | 1,450 | LSFN-05S | 2,770 |
| 30         | LWH30       | LS30AL, LH30AL | HSR30A | 65 | 65 | 49.5 | 10 | 54.5 | 25   | 27 | 20 | 16 | M8×P1.0  | 9.0 | M8×70      | LSFN-06 | 1,740 | LSFN-06S | 3,070 |
| 35         | LWH35       | LS35AL, LH35AL | HSR35A | 65 | 65 | 55.5 | 10 | 54.5 | 28   | 30 | 20 | 16 | M8×P1.0  | 9.0 | M8×70      | LSFN-07 | 1,740 | LSFN-07S | 3,070 |

| レール<br>サイズ | 対応メーカー・シリーズ |                |        | W  | H  | A    | E  | F    | S1   | S2 | P  | T  | M  | D   | 付属品<br>ボルト | D1 | L  | 鉄(黒染め)  |       | ステンレス    |       |
|------------|-------------|----------------|--------|----|----|------|----|------|------|----|----|----|----|-----|------------|----|----|---------|-------|----------|-------|
|            | IKO社        | NSK社           | THK社   |    |    |      |    |      |      |    |    |    |    |     |            |    |    | 品番      | 価格(円) | 品番       | 価格(円) |
| 15         | —           | —              | SRS15M | 44 | 30 | 22.5 | 7  | 36.5 | 15   | 11 | 16 | 12 | M4 | 5.5 | M5×35      | 15 | 11 | LSFU-01 | 1,570 | LSFU-01S | 2,430 |
|            | LWH15       | LS15AL, LH15AN | HSR15A | 44 | 38 | 30.5 | 7  | 36.5 | 15   | 16 | 16 | 12 | M4 | 5.5 | M5×40      | 15 | 11 | LSFU-02 | 1,630 | LSFU-02S | 2,660 |
| 20         | —           | —              | SRS20M | 44 | 35 | 25.0 | 7  | 34.0 | 17.5 | 12 | 12 | 12 | M5 | 5.5 | M5×40      | 20 | 13 | LSFU-03 | 1,690 | LSFU-03S | 2,720 |
|            | LWH20       | LS20AL, LH20AN | HSR20A | 44 | 50 | 40.0 | 7  | 34.0 | 17.5 | 19 | 12 | 12 | M5 | 5.5 | M5×55      | 20 | 13 | LSFU-04 | 1,740 | LSFU-04S | 2,950 |
| 25         | —           | —              | SRS25M | 44 | 38 | 30.5 | 7  | 36.5 | 15   | 16 | 16 | 12 | M4 | 5.5 | M5×40      | 15 | 11 | LSFU-02 | 1,630 | LSFU-02S | 2,660 |
|            | LWH25       | LS25AL, LH25AL | HSR25A | 44 | 50 | 40.0 | 7  | 34.0 | 19   | 23 | 12 | 16 | M5 | 6.6 | M6×55      | 20 | 13 | LSFU-05 | 1,860 | LSFU-05S | 3,180 |
| 30         | LWH30       | LS30AL, LH30AL | HSR30A | 65 | 65 | 52.5 | 10 | 52.5 | 25   | 27 | 20 | 16 | M5 | 9.0 | M8×70      | 25 | 13 | LSFU-06 | 2,200 | LSFU-06S | 3,530 |
| 35         | LWH35       | LS35AL, LH35AL | HSR35A | 65 | 65 | 52.5 | 10 | 52.5 | 28   | 30 | 20 | 16 | M5 | 9.0 | M8×70      | 25 | 13 | LSFU-07 | 2,200 | LSFU-07S | 3,530 |

| レール<br>サイズ | 対応メーカー・シリーズ |                |        | W  | H  | A    | E  | F    | S1   | S2 | P  | T  | M(細目)    | D   | 付属品<br>ボルト | 鉄(黒染め)    |       | ステンレス      |       |
|------------|-------------|----------------|--------|----|----|------|----|------|------|----|----|----|----------|-----|------------|-----------|-------|------------|-------|
|            | IKO社        | NSK社           | THK社   |    |    |      |    |      |      |    |    |    |          |     |            | 品番        | 価格(円) | 品番         | 価格(円) |
| 15         | —           | —              | SRS15M | 44 | 30 | 23.5 | 7  | 37.0 | 15   | 11 | 16 | 12 | M6×P0.75 | 5.5 | M5×35      | LSFN-01-U | 2,070 | LSFN-01S-U | 2,930 |
|            | LWH15       | LS15AL, LH15AN | HSR15A | 44 | 38 | 31.5 | 7  | 37.0 | 15   | 16 | 16 | 12 | M6×P0.75 | 5.5 | M5×40      | LSFN-02-U | 2,130 | LSFN-02S-U | 3,160 |
| 20         | —           | —              | SRS20M | 44 | 35 | 27.5 | 7  | 37.0 | 17.5 | 12 | 12 | 12 | M8×P1.0  | 5.5 | M5×40      | LSFN-03-U | 2,190 | LSFN-03S-U | 3,220 |
|            | LWH20       | LS20AL, LH20AN | HSR20A | 44 | 50 | 37.5 | 7  | 37.0 | 17.5 | 19 | 12 | 12 | M8×P1.0  | 5.5 | M5×55      | LSFN-04-U | 2,240 | LSFN-04S-U | 3,450 |
| 25         | —           | —              | SRS25M | 44 | 38 | 31.5 | 7  | 37.0 | 15   | 16 | 16 | 12 | M6×P0.75 | 5.5 | M5×40      | LSFN-02-U | 2,130 | LSFN-02S-U | 3,160 |
|            | LWH25       | LS25AL, LH25AL | HSR25A | 44 | 50 | 43.5 | 7  | 37.0 | 19   | 23 | 12 | 16 | M8×P1.0  | 6.6 | M6×55      | LSFN-05-U | 2,360 | LSFN-05S-U | 3,680 |
| 30         | LWH30       | LS30AL, LH30AL | HSR30A | 65 | 65 | 49.5 | 10 | 54.5 | 25   | 27 | 20 | 16 | M8×P1.0  | 9.0 | M8×70      | LSFN-06-U | 2,650 | LSFN-06S-U | 3,980 |
| 35         | LWH35       | LS35AL, LH35AL | HSR35A | 65 | 65 | 55.5 | 10 | 54.5 | 28   | 30 | 20 | 16 | M8×P1.0  | 9.0 | M8×70      | LSFN-07-U | 2,650 | LSFN-07S-U | 3,980 |