

レール サイズ	対応メーカー・シリーズ			W	H	A	P	P1	T	M(細目)	M1	付属品 ノックピン	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社										品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	40	15	8.5	30	15	12	M6×P0.75	M5X10	4×10	LSV-01N	920	LSV-01SN	1,220
	LWH15	LS15AL	HSR15A	40	22	15.0	30	15	12	M6×P0.75	M5X10	4×10	LSV-02N	1,100	LSV-02SN	1,390
	—	LH15AN	—	40	26	19.0	30	15	12	M6×P0.75	M5X10	4×10	LSV-03N	1,100	LSV-03SN	1,390
20	LWH20	LS20AL、LH20AN	HSR20A	40	18	10.0	30	15	12	M8×P1.0	M5X10	4×10	LSV-04N	920	LSV-04SN	1,220
	—	—	SRS25M	40	23	15.0	30	15	16	M8×P1.0	M6X12	4×10	LSV-05N	1,220	LSV-05SN	1,560
25	—	LS25AL	—	40	31	23.0	30	15	16	M8×P1.0	M6X12	4×10	LSV-06N	1,220	LSV-06SN	1,560
	LWH25	LH25AL	HSR25A	40	34	26.0	30	15	16	M8×P1.0	M6X12	4×10	LSV-07N	1,220	LSV-07SN	1,560
30	LWH30	LS30AL、LH30AL	HSR30A	50	40	32.0	35	15	16	M8×P1.0	M8X16	4×10	LSV-08N	1,450	LSV-08SN	2,020
35	LWH35	LS35AL、LH35AL	HSR35A	50	46	38.0	35	15	16	M8×P1.0	M8X16	4×10	LSV-09N	1,450	LSV-09SN	2,020

リニアストッパー

セットベース



レール サイズ	対応メーカー・シリーズ			W	H	A	P	T	M1	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社							品番	価格(円)	品番	価格(円)
15	—	—	SRS15M	40	15	7.5	30	12	M5X10	LSVU-01	920	LSVU-01S	1,100
	LWH15	LS15AL	HSR15A	40	22	14.5	30	12	M5X10	LSVU-02	1,100	LSVU-02S	1,280
	—	LH15AN	—	40	26	18.5	30	12	M5X10	LSVU-03	1,100	LSVU-03S	1,280
20	LWH20	LS20AL、LH20AN	HSR20A	40	18	10.5	30	12	M5X10	LSVU-04	920	LSVU-04S	1,100
	—	—	SRS25M	40	23	15.5	30	16	M6X12	LSVU-05	1,220	LSVU-05S	1,450
25	—	LS25AL	—	40	31	23.5	30	16	M6X12	LSVU-06	1,220	LSVU-06S	1,450
	LWH25	LH25AL	HSR25A	40	34	26.5	30	16	M6X12	LSVU-07	1,220	LSVU-07S	1,450
30	LWH30	LS30AL、LH30AL	HSR30A	50	40	32.5	35	16	M8X16	LSVU-08	1,450	LSVU-08S	1,910
35	LWH35	LS35AL、LH35AL	HSR35A	50	46	38.5	35	16	M8X16	LSVU-09	1,450	LSVU-09S	1,910

抜け止め用

コンパクト

ストッパーブロック

ストッパーボルト
ウレタンボルト

レール サイズ	対応メーカー・シリーズ			W	H	A	P	P1	T	M(細目)	M1	付属品 ノックピン	鉄(黒染め)		ステンレス	
	IKO社	NSK社	THK社										品番	価格(円)	品番	価格(円)
15	LWH15	LS15AL	HSR15A	40	22	15	30	15	12	M6×P0.75	M5X10	4×10	LSV-01N-U	1,950	LSV-01SN-U	2,240
	—	LH15AN	—	40	26	19	30	15	12	M6×P0.75	M5X10	4×10	LSV-02N-U	1,950	LSV-02SN-U	2,240
20	LWH20	LS20AL、LH20AN	HSR20A	40	18	10	30	15	12	M8×P1.0	M5X10	4×10	LSV-03N-U	1,830	LSV-03SN-U	2,130
	—	—	SRS25M	40	23	15	30	15	16	M8×P1.0	M6X12	4×10	LSV-04N-U	2,130	LSV-04SN-U	2,470
25	—	LS25AL	—	40	31	23	30	15	16	M8×P1.0	M6X12	4×10	LSV-05N-U	2,130	LSV-05SN-U	2,470
	LWH25	LH25AL	HSR25A	40	34	26	30	15	16	M8×P1.0	M6X12	4×10	LSV-06N-U	2,130	LSV-06SN-U	2,470
30	LWH30	LS30AL、LH30AL	HSR30A	50	40	32	35	15	16	M8×P1.0	M8X16	4×10	LSV-07N-U	2,360	LSV-07SN-U	2,930
35	LWH35	LS35AL、LH35AL	HSR35A	50	46	38	35	15	16	M8×P1.0	M8X16	4×10	LSV-08N-U	2,360	LSV-08SN-U	2,930