



| 部品番号<br>PART NO. | 適用チューブ<br>外径<br>TUBE O.D.<br>TO BE USED<br>(mm) | T<br>(R·M) | φD<br>(mm) | S<br>六角<br>対辺<br>HEX<br>(mm) | L <sub>1</sub><br>(mm) | L <sub>2</sub><br>(mm) | L <sub>3</sub><br>(mm) | IN<br>(mm) | 重量<br>WEIGHT<br>(g) | 最小内径<br>ORIFICE<br>(mm) | 有効断面積<br>EFFECTIVE<br>SECTIONAL AREA<br>(mm <sup>2</sup> ) |                                  |
|------------------|---|------------|------------|------------------------------|------------------------|------------------------|------------------------|------------|---------------------|-------------------------|--|----------------------------------|
|                  |   |            |            |                              |                        |                        |                        |            |                     |                         | ナイロンチューブ<br>NYLON<br>TUBE                                  | ウレタンチューブ<br>POLYURETHANE<br>TUBE |
| PTAM- 4-M5-PM    | 4   | M5         | 10.5       | 12                           | 17                     | 23                     | 5                      | 13         | 10                  | 2.5                     | 2.6  | 2.6                              |
| PTAM- 4-PT1/8-PM | 4   | 1/8        | 10.5       | 12                           | 17                     | 26                     | 8                      | 13         | 13                  | 3                       | 2.9  | 2.9                              |
| PTAM- 4-PT1/4-PM | 4   | 1/4        | 10.5       | 14                           | 17                     | 29                     | 11                     | 13         | 16                  | 3                       | 2.9  | 2.9                              |
| PTAM- 6-M5-PM    | 6   | M5         | 12.5       | 12                           | 18                     | 24                     | 5                      | 14         | 12                  | 2.5                     | 3.4  | 3.4                              |
| PTAM- 6-PT1/8-PM | 6   | 1/8        | 12.5       | 12                           | 18                     | 27                     | 8                      | 14         | 15                  | 4                       | 6.8  | 6.8                              |
| PTAM- 6-PT1/4-PM | 6   | 1/4        | 12.5       | 14                           | 18                     | 30                     | 11                     | 14         | 19                  | 4                       | 6.8  | 6.8                              |
| PTAM- 6-PT3/8-PM | 6   | 3/8        | 12.5       | 17                           | 18                     | 31                     | 12                     | 14         | 29                  | 4                       | 6.8  | 6.8                              |
| PTAM- 8-PT1/8-PM | 8   | 1/8        | 14.5       | 17                           | 19                     | 28                     | 8                      | 15         | 17                  | 6                       | 20.3   | 11.6                             |
| PTAM- 8-PT1/4-PM | 8   | 1/4        | 14.5       | 17                           | 19                     | 31                     | 11                     | 15         | 24                  | 6                       | 20.3   | 11.6                             |
| PTAM- 8-PT3/8-PM | 8   | 3/8        | 14.5       | 17                           | 19                     | 32                     | 12                     | 15         | 28                  | 6                       | 20.3   | 11.6                             |
| PTAM-10-PT1/8-PM | 10  | 1/8        | 19         | 19                           | 25                     | 34                     | 9                      | 19         | 36                  | 6                       | 27.0   | 18.0                             |
| PTAM-10-PT1/4-PM | 10  | 1/4        | 19         | 19                           | 25                     | 37                     | 12                     | 19         | 38                  | 8                       | 27.0   | 18.0                             |
| PTAM-10-PT3/8-PM | 10  | 3/8        | 19         | 19                           | 25                     | 37                     | 12                     | 19         | 44                  | 8                       | 36.0   | 28.0                             |
| PTAM-10-PT1/2-PM | 10  | 1/2        | 19         | 22                           | 25                     | 41                     | 16                     | 19         | 73                  | 8                       | 36.0   | 28.0                             |
| PTAM-12-PT1/8-PM | 12  | 1/8        | 22         | 22                           | 29                     | 37                     | 9                      | 21         | 43                  | 6                       | 28.0   | 20.0                             |
| PTAM-12-PT1/4-PM | 12  | 1/4        | 22         | 22                           | 29                     | 40                     | 12                     | 21         | 52                  | 8                       | 45.0   | 39.5                             |
| PTAM-12-PT3/8-PM | 12  | 3/8        | 22         | 22                           | 29                     | 40                     | 12                     | 21         | 62                  | 10                      | 51.0   | 47.0                             |
| PTAM-12-PT1/2-PM | 12  | 1/2        | 22         | 22                           | 29                     | 44                     | 16                     | 21         | 77                  | 10                      | 55.0   | 47.0                             |

※R (PT) ネジには、ネジサイズが一目で判別できるR (PT) ネジ別の色シールがついています。PAT.NO.1820889  
 The R (PT) screws have different color seals so that they can be distinguished at a glance.  
 ●R<sup>1</sup>/<sub>8</sub>: 白 white ●R<sup>1</sup>/<sub>4</sub>: 青 blue ●R<sup>3</sup>/<sub>8</sub>: 黄 yellow ●R<sup>1</sup>/<sub>2</sub>: 灰 gray