


## Fシリーズ



Fシリーズは**カタログ記号+F+穴径+A**にてご注文ください。

\* 寸法表の背景色はFシリーズの形状図を表しております。

| 軸穴径 A            |           | F シリーズラインナップ |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
|------------------|-----------|--------------|------|-------|-----|------|------|------|------|-------|------|------|------|------|------|------|
| カタログ記号           |           | 10           | 12   | 14    | 15  | 16   | 17   | 18   | 19   | 20    | 22   | 25   | 28   | 30   | 32   | 35   |
| SS1.5-26 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-27 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-28 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-29 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-30 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-32 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-34 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-35 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-36 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-38 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-40 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-42 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-44 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-45 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-46 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-48 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-50 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-52 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-54 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-55 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-56 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-58 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-60 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-62 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-64 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-65 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-66 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-68 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-70 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-72 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-75 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-76 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-80 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-84 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-85 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-88 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-90 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-95 F 穴径 A  |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-100 F 穴径 A |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-120 F 穴径 A |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| SS1.5-150 F 穴径 A |           |              |      |       |     |      |      |      |      |       |      |      |      |      |      |      |
| 軸穴径 A            |           | 10           | 12   | 14    | 15  | 16   | 17   | 18   | 19   | 20    | 22   | 25   | 28   | 30   | 32   | 35   |
| 参考滑り出しトルク N・m    |           | 18           | 23   | 37    | 39  | 42   | 45   | 48   | 49   | 97    | 110  | 124  | 141  | 149  | 163  | 173  |
| 参考スラスト荷重 kN      |           | 3.59         | 3.76 | 5.21  | 5.1 | 5.17 | 5.23 | 5.28 | 5.12 | 9.68  | 9.98 | 9.90 | 10.0 | 9.89 | 10.1 | 9.88 |
| ブッシュ             | L         | 10           |      | 12    |     |      |      |      |      | 14    |      |      |      |      |      |      |
|                  | K         | 29           | 31   | 36    | 37  | 38   | 39   | 40   | 42   | 46    | 47   | 51   | 53   | 56   | 58   | 61   |
| 隙間               | J         | 2            |      |       |     |      |      |      |      | 3     |      |      |      |      |      |      |
| 全長               | G         | 35           |      | 37    |     |      |      |      |      | 39    |      |      |      |      |      |      |
| 六角穴付ボルト          | 本数        | 3            |      |       |     |      |      |      |      | 4     |      |      |      |      |      |      |
|                  | サイズ       | M4×12        |      | M4×15 |     |      |      |      |      | M5×18 |      |      |      |      |      |      |
|                  | 締付トルク N・m | 3.9          |      |       |     |      |      | 7.8  |      |       |      |      |      |      |      |      |
| ブッシュ質量 (g)       |           | 20           | 22   | 38    | 40  | 41   | 43   | 45   | 49   | 71    | 71   | 81   | 84   | 93   | 97   | 106  |

