



Fシリーズは**カタログ記号+F+穴径**にてご注文ください。

\*寸法表の背景色はFシリーズの形状図を表しております。

軸穴径 A		Fシリーズラインナップ												
カタログ記号		15	16	17	18	19	20	22	25	28	30	32	35	40
SSA3-20 F 穴径														
SSA3-24 F 穴径														
SSA3-25 F 穴径														
SSA3-28 F 穴径														
SSA3-30 F 穴径														
SSA3-32 F 穴径														
SSA3-35 F 穴径														
SSA3-36 F 穴径														
SSA3-40 F 穴径														
SSA3-45 F 穴径														
SSA3-48 F 穴径														
SSA3-50 F 穴径														
SSA3-55 F 穴径														
SSA3-56 F 穴径														
SSA3-60 F 穴径														
SSA3-70 F 穴径														
SSA3-80 F 穴径														
軸穴径 A		15	16	17	18	19	20	22	25	28	30	32	35	40
参考滑り出しトルク N・m		39	42	45	48	49	97	110	124	141	149	163	173	725
参考スラスト荷重 kN		5.10	5.17	5.23	5.28	5.12	9.68	9.98	9.90	10.0	9.89	10.1	9.88	12.3
プッシュ	L	12						14						19
	K	37	38	39	40	42	46	47	51	53	56	58	61	71
隙間	J	3												
全長	G	42						44						49
六角穴付 ボルト	本数	4												
	サイズ	M4×15						M5×18						M6×25
	締付トルク N・m	3.9						7.8						13.7
プッシュ質量 (g)		40	41	43	45	49	71	71	81	84	93	97	106	237

