



L, L3, L4 maxについては、超硬ソリッドドリルの折込表をご覧ください。

■ B041A/B042A • ~3 x D/~5 x D



- 第1選択
- 第2選択

		D1 径		L5	LS	D
ショート・KC7325	ロング・KC7325	mm	インチ			
B041A01000CPG	B042A01000CPG	1,000	.0394	0,1	28	4
B041A01016CPG	B042A01016CPG	1,016	.0400	0,1	28	4
B041A01041CPG	B042A01041CPG	1,041	.0410	0,2	28	4
B041A01067CPG	B042A01067CPG	1,067	.0420	0,2	28	4
B041A01092CPG	B042A01092CPG *	1,092	.0430	0,2	28	4
B041A01100CPG	B042A01100CPG	1,100	.0433	0,2	28	4
B041A01181CPG	B042A01181CPG	1,181	.0465	0,2	28	4
B041A01191CPG	B042A01191CPG	1,191	.0469	0,2	28	4
B041A01200CPG	B042A01200CPG	1,200	.0472	0,2	28	4
B041A01300CPG	B042A01300CPG	1,300	.0512	0,2	28	4
B041A01321CPG	B042A01321CPG	1,321	.0520	0,2	28	4
B041A01397CPG	B042A01397CPG	1,397	.0550	0,2	28	4
B041A01400CPG	B042A01400CPG	1,400	.0551	0,2	28	4
B041A01500CPG	B042A01500CPG	1,500	.0591	0,2	28	4
B041A01600CPG	B042A01600CPG	1,600	.0630	0,2	28	4
B041A01700CPG	B042A01700CPG	1,700	.0669	0,3	28	4
B041A01800CPG	B042A01800CPG	1,800	.0709	0,3	28	4
B041A01900CPG	B042A01900CPG	1,900	.0748	0,3	28	4
B041A01984CPG	B042A01984CPG	1,984	.0781	0,3	28	4
B041A02000CPG	B042A02000CPG	2,000	.0787	0,3	28	4
B041A02100CPG	B042A02100CPG	2,100	.0827	0,3	28	4
B041A02200CPG	B042A02200CPG	2,200	.0866	0,3	28	4
B041A02300CPG	B042A02300CPG	2,300	.0906	0,4	28	4
B041A02383CPG	B042A02383CPG	2,383	.0938	0,4	28	4
B041A02400CPG	B042A02400CPG	2,400	.0945	0,4	28	4
B041A02439CPG	B042A02439CPG	2,439	.0960	0,4	28	4
B041A02489CPG	B042A02489CPG	2,489	.0980	0,4	28	4
B041A02500CPG	B042A02500CPG	2,500	.0984	0,4	28	4
B041A02578CPG	B042A02578CPG	2,578	.1015	0,4	28	4
B041A02600CPG	B042A02600CPG	2,600	.1024	0,4	28	4
B041A02642CPG	B042A02642CPG	2,642	.1040	0,4	28	4
B041A02700CPG	B042A02700CPG	2,700	.1063	0,4	28	4

(続く)