



L, L3, L4 maxについては、超硬ソリッドドリルの折込表をご覧ください。



■ B051A/B052A/B053A • ~3 x D/~5 x D/~8 x D



- 第1選択
- 第2選択

			D1 径		L5	LS	D
ショート・KC7325	ロング・KC7325	エキストラロング・KC7325	mm	インチ			
—	—	B053A01000CPG	1,000	.0394	0,1	28	4
—	—	B053A01016CPG	1,016	.0400	0,1	28	4
—	—	B053A01067CPG	1,067	.0420	0,2	28	4
—	—	B053A01100CPG	1,100	.0433	0,2	28	4
—	—	B053A01181CPG	1,181	.0465	0,2	28	4
—	—	B053A01191CPG	1,191	.0469	0,2	28	4
—	—	B053A01200CPG	1,200	.0472	0,2	28	4
—	—	B053A01300CPG	1,300	.0512	0,2	28	4
—	—	B053A01321CPG	1,321	.0520	0,2	28	4
—	—	B053A01397CPG	1,397	.0550	0,2	28	4
—	—	B053A01400CPG	1,400	.0551	0,2	28	4
B051A01500CPG	B052A01500CPG	B053A01500CPG	1,500	.0591	0,2	28	4
B051A01600CPG	B052A01600CPG	B053A01600CPG	1,600	.0630	0,2	28	4
B051A01700CPG	B052A01700CPG	B053A01700CPG	1,700	.0669	0,3	28	4
B051A01800CPG	B052A01800CPG	B053A01800CPG	1,800	.0709	0,3	28	4
B051A01900CPG	B052A01900CPG	B053A01900CPG	1,900	.0748	0,3	28	4
B051A01984CPG	B052A01984CPG	B053A01984CPG	1,984	.0781	0,3	28	4
B051A02000CPG	B052A02000CPG	B053A02000CPG	2,000	.0787	0,3	28	4
B051A02100CPG	B052A02100CPG	B053A02100CPG	2,100	.0827	0,3	28	4
B051A02200CPG	B052A02200CPG	B053A02200CPG	2,200	.0866	0,3	28	4
B051A02300CPG	B052A02300CPG	B053A02300CPG	2,300	.0906	0,4	28	4
B051A02383CPG	B052A02383CPG	B053A02383CPG	2,383	.0938	0,4	28	4
B051A02400CPG	B052A02400CPG	B053A02400CPG	2,400	.0945	0,4	28	4
B051A02439CPG	B052A02439CPG	B053A02439CPG	2,439	.0960	0,4	28	4
B051A02489CPG	B052A02489CPG	B053A02489CPG	2,489	.0980	0,4	28	4
B051A02500CPG	B052A02500CPG	B053A02500CPG	2,500	.0984	0,4	28	4
B051A02578CPG	B052A02578CPG	B053A02578CPG	2,578	.1015	0,4	28	4
B051A02600CPG	B052A02600CPG	B053A02600CPG	2,600	.1024	0,4	28	4
B051A02642CPG	B052A02642CPG	B053A02642CPG	2,642	.1040	0,4	28	4
B051A02700CPG	B052A02700CPG	B053A02700CPG	2,700	.1063	0,4	28	4
B051A02705CPG	B052A02705CPG	B053A02705CPG	2,705	.1065	0,4	28	4
B051A02779CPG	B052A02779CPG	B053A02779CPG	2,779	.1094	0,4	28	4
B051A02800CPG	B052A02800CPG	B053A02800CPG	2,800	.1102	0,5	28	4
B051A02820CPG	B052A02820CPG	B053A02820CPG	2,820	.1110	0,5	28	4
B051A02870CPG	B052A02870CPG	B053A02870CPG	2,870	.1130	0,5	28	4
B051A02900CPG	B052A02900CPG	B053A02900CPG	2,900	.1142	0,5	28	4

(続く)