

Kシリーズ 引張コイルばね

材質 SUS304WPB

製品コード	旧型番	外径 mm	線径 mm	自由長さ mm	許容荷重 N	許容荷重時 長さ mm	総巻数	初張力 N	ばね定数 N/mm	バック内 個数
2001	KE020-020-0068	2.0	0.20	6.8	0.882	11.6	15.5	0.1764	0.1470	20
2002	KE020-020-0086			8.6	0.882	16.1	24.5	0.1764	0.0941	20
2003	KE020-020-0116			11.6	0.882	23.6	39.5	0.1764	0.0588	20
2004	KE020-020-0162			16.2	0.882	34.7	62.5	0.1764	0.0382	20
2005	KE025-020-0079	2.0	0.20	7.9	0.686	16.1	15.5	0.1078	0.0706	20
2006	KE025-020-0097			9.7	0.686	22.5	24.5	0.1078	0.0451	20
2007	KE025-020-0127			12.7	0.686	33.1	39.5	0.1078	0.0284	20
2008	KE025-020-0173			17.3	0.686	50.2	62.5	0.1078	0.0176	20
2009	KE025-023-0083	2.5	0.23	8.3	1.029	14.8	15.5	0.1960	0.1284	20
2010	KE025-023-0104			10.4	1.029	20.5	24.5	0.1960	0.0823	20
2011	KE025-023-0138			13.8	1.029	29.9	39.5	0.1960	0.0519	20
2012	KE025-023-0191			19.1	1.029	44.9	62.5	0.1960	0.0323	20
2013	KE025-026-0086	2.5	0.26	8.6	1.519	14.0	15.5	0.3332	0.2176	20
2014	KE025-026-0110			11.0	1.519	19.5	24.5	0.3332	0.1401	20
2015	KE025-026-0149			14.9	1.519	28.5	39.5	0.3332	0.0872	20
2016	KE025-026-0209			20.9	1.519	42.1	62.5	0.3332	0.0559	20
2017	KE025-029-0090	2.5	0.29	9.0	2.156	13.7	15.5	0.5194	0.3518	20
2018	KE025-029-0116			11.6	2.156	18.9	24.5	0.5194	0.2244	20
2019	KE025-029-0160			16.0	2.156	27.6	39.5	0.5194	0.1411	20
2020	KE025-029-0226			22.6	2.156	40.9	62.5	0.5194	0.0892	20
2021	KE032-020-0095	3.2	0.20	9.5	0.539	24.8	15.5	0.0588	0.0314	20
2022	KE032-020-0113			11.3	0.539	34.6	24.5	0.0588	0.0206	20
2023	KE032-020-0143			14.3	0.539	52.1	39.5	0.0588	0.0127	20
2024	KE032-020-0189			18.9	0.539	80.5	62.5	0.0588	0.0078	20
2025	KE032-023-0098	3.2	0.23	9.8	0.784	21.7	15.5	0.1078	0.0568	20
2026	KE032-023-0119			11.9	0.784	30.1	24.5	0.1078	0.0372	20
2027	KE032-023-0153			15.3	0.784	44.1	39.5	0.1078	0.0235	20
2028	KE032-023-0206			20.6	0.784	66.6	62.5	0.1078	0.0147	20
2029	KE032-026-0102	3.2	0.26	10.2	1.176	20.5	15.5	0.1862	0.0960	20
2030	KE032-026-0125			12.5	1.176	28.5	24.5	0.1862	0.0617	20
2031	KE032-026-0164			16.4	1.176	42.3	39.5	0.1862	0.0382	20
2032	KE032-026-0224			22.4	1.176	62.8	62.5	0.1862	0.0245	20
2033	KE032-029-0105	3.2	0.29	10.5	1.617	19.0	15.5	0.3038	0.1539	20
2034	KE032-029-0132			13.2	1.617	26.5	24.5	0.3038	0.0990	20
2035	KE032-029-0175			17.5	1.617	38.8	39.5	0.3038	0.0617	20
2036	KE032-029-0242			24.2	1.617	57.7	62.5	0.3038	0.0392	10
2037	KE032-032-0109	3.2	0.32	10.9	2.205	18.3	15.5	0.4704	0.2352	20
2038	KE032-032-0138			13.8	2.205	25.3	24.5	0.4704	0.1509	20
2039	KE032-032-0186			18.6	2.205	37.0	39.5	0.4704	0.0941	20
2040	KE032-032-0260			26.0	2.205	55.0	62.5	0.4704	0.0598	10
2041	KE032-035-0113	3.2	0.35	11.3	2.891	17.7	15.5	0.6762	0.3469	20
2042	KE032-035-0144			14.4	2.891	24.4	24.5	0.6762	0.2225	20
2043	KE032-035-0197			19.7	2.891	35.6	39.5	0.6762	0.1392	20
2044	KE032-035-0277			27.7	2.891	52.8	62.5	0.6762	0.0882	10
2045	KE040-023-0116	4.0	0.23	11.6	0.637	32.3	15.5	0.0490	0.0284	20
2046	KE040-023-0137			13.7	0.637	47.1	24.5	0.0490	0.0176	20
2047	KE040-023-0171			17.1	0.637	71.5	39.5	0.0490	0.0108	20
2048	KE040-023-0224			22.4	0.637	107.6	62.5	0.0490	0.0069	10
2049	KE040-026-0119	4.0	0.26	11.9	0.931	29.6	15.5	0.0980	0.0470	20
2050	KE040-026-0143			14.3	0.931	41.7	24.5	0.0980	0.0304	20
2051	KE040-026-0182			18.2	0.931	63.0	39.5	0.0980	0.0186	20
2052	KE040-026-0242			24.2	0.931	94.8	62.5	0.0980	0.0118	10
2053	KE040-029-0123	4.0	0.29	12.3	1.274	27.0	15.5	0.1764	0.0745	20
2054	KE040-029-0149			14.9	1.274	38.3	24.5	0.1764	0.0470	20
2055	KE040-029-0193			19.3	1.274	55.4	39.5	0.1764	0.0304	20

スーパースプリング

圧縮コイルばね
Kシリーズ

引張コイルばね
Kシリーズ

圧縮コイルばね
Sシリーズ

圧縮コイルばね
Dシリーズ

引張コイルばね
Dシリーズ

圧縮コイルばね
DSシリーズ

引張コイルばね
DSシリーズ

長巻きばね

参考資料