

             								mm								mm								mm							
■ヘキサゴンビット〈スタッピ〉								■ヘキサゴンビット〈ショート〉								■ヘキサゴンビット〈ショート〉															
交換ビット 品番	適用品番	S ₁	S ₂	L	タイプ	小売参考 価格		交換ビット 品番	適用品番	S ₁	S ₂	L	タイプ	小売参考 価格		交換ビット 品番	適用品番	S ₁	S ₂	L	タイプ	小売参考 価格									
	9.5 sq.								9.5 sq.								9.5 sq.														
T-03SS	BT3-03SS	3	6.3	14	A	¥ 670		T-03S	BT3-03S	3	6.3	28	A	¥ 340		T-1/8S	BT3-1/8S	3.1	6.3	28	A	¥ 500									
T-04SS	BT3-04SS	4	6.3	14	A	¥ 670		T-04S	BT3-04S	4	6.3	28	A	¥ 340		T-9/64S	BT3-9/64S	3.6	6.3	28	A	¥ 500									
T-05SS	BT3-05SS	5	6.3	15	A	¥ 670		T-05S	BT3-05S	5	6.3	30	A	¥ 340		T-5/32S	BT3-5/32S	3.9	6.3	28	A	¥ 500									
T-06SS	BT3-06SS	6	6.3	15.5	A	¥ 670		T-06S	BT3-06S	6	6.3	30	A	¥ 340		T-3/16S	BT3-3/16S	4.7	6.3	28	A	¥ 500									
T-07SS	BT3-07SS	7	8	16	B	¥ 670		T-07S	BT3-07S	7	8	30	B	¥ 340		T-7/32S	BT3-7/32S	5.5	6.3	30	A	¥ 500									
T-08SS	BT3-08SS	8	8	17	B	¥ 670		T-08S	BT3-08S	8	8	30	B	¥ 340		T-1/4S	BT3-1/4S	6.3	6.3	30	A	¥ 500									
T-09SS	BT3-09SS	9	10	19.5	B	¥ 720		T-09S	BT3-09S	9	10	32	B	¥ 390		T-5/16S	BT3-5/16S	7.9	8	30	B	¥ 500									
T-10SS	BT3-10SS	10	10	19.5	B	¥ 720		T-10S	BT3-10S	10	10	32	B	¥ 390		T-3/8S	BT3-3/8S	9.5	10	32	B	¥ 560									
T-12SS	BT3-12SS	12	12	22	B	¥ 810		T-12S	BT3-12S	12	12	34	B	¥ 480		T-7/16S	BT3-7/16S	11.1	12	34	B	¥ 680									

																	
■ヘキサゴンビット (スタンダード)									■ヘキサゴンビット (スタンダード)								
				mm									in				
交換ビット 品番	適用品番			S ₁	S ₂	L	タイプ	小売参考 価格	交換ビット 品番	適用品番			S ₁	S ₂	L	タイプ	小売参考 価格
																	
T-03	BT2-03	BT3-03		3	6.3	41	A	¥ 450	T-1/8	BT2-1/8	BT3-1/8		3.1	6.3	41	A	¥ 610
T-04	BT2-04	BT3-04		4	6.3	41	A	¥ 450	T-9/64	BT2-9/64	BT3-9/64		3.6	6.3	41	A	¥ 610
T-05	BT2-05	BT3-05	BT4-05	5	6.3	46	A	¥ 450	T-5/32	BT2-5/32	BT3-5/32		3.9	6.3	41	A	¥ 610
T-06	BT2-06	BT3-06	BT4-06	6	6.3	46	A	¥ 450	T-3/16	BT2-3/16	BT3-3/16	BT4-3/16	4.7	6.3	41	A	¥ 610
T-07		BT3-07	BT4-07	7	8	51	B	¥ 450	T-7/32	BT2-7/32	BT3-7/32	BT4-7/32	5.5	6.3	46	A	¥ 610
T-08		BT3-08	BT4-08	8	8	51	B	¥ 450	T-1/4	BT2-1/4	BT3-1/4	BT4-1/4	6.3	6.3	46	A	¥ 610
T-09		BT3-09	BT4-09	9	10	53	B	¥ 490	T-5/16		BT3-5/16	BT4-5/16	8	8	51	B	¥ 610
T-10		BT3-10	BT4-10	10	10	53	B	¥ 490	T-3/8		BT3-3/8	BT4-3/8	9.5	10	53	B	¥ 680
T-12		BT3-12	BT4-12	12	12	56	B	¥ 590	T-7/16		BT3-7/16	BT4-7/16	11.1	12	56	B	¥ 790
T-14			BT4-14	14	14	61	B	¥ 660	T-1/2			BT4-1/2	12.7	14	61	B	¥ 890
T-17			BT4-17	17	17	66	B	¥ 700	T-9/16			BT4-9/16	14.2	17	66	B	¥ 930
									T-5/8			BT4-5/8	15.8	17	66	B	¥ 930

mm

■ヘキサゴンビット (ロング)

交換ビット 品番	適用品番			S ₁	S ₂	L	タイプ	小売参考 価格
	6.3 sq.	9.5 sq.	12.7 sq.					
T-03L	BT2-03L	BT3-03L		3	6.3	108	A	¥ 670
T-04L	BT2-04L	BT3-04L		4	6.3	108	A	¥ 670
T-05L	BT2-05L	BT3-05L	BT4-05L	5	6.3	108	A	¥ 670
T-06L	BT2-06L	BT3-06L	BT4-06L	6	6.3	108	A	¥ 670
T-07L		BT3-07L	BT4-07L	7	8	108	B	¥ 670
T-08L		BT3-08L	BT4-08L	8	8	108	B	¥ 670
T-09L		BT3-09L	BT4-09L	9	10	108	B	¥ 720
T-10L		BT3-10L	BT4-10L	10	10	108	B	¥ 720
T-12L		BT3-12L	BT4-12L	12	12	108	B	¥ 810
T-14L			BT4-14L	14	14	108	B	¥ 880
T-17L			BT4-17L	17	17	108	B	¥ 920

mm

■ヘキサゴンビット (ロング)

交換ビット 品番	適用品番			S ₁	S ₂	L	タイプ	小売参考 価格
	6.3 sq.	9.5 sq.	12.7 sq.					
T-1/8L	BT2-1/8L	BT3-1/8L		3.1	6.3	108	A	¥ 830
T-9/64L	BT2-9/64L	BT3-9/64L		3.6	6.3	108	A	¥ 830
T-5/32L	BT2-5/32L	BT3-5/32L		3.9	6.3	108	A	¥ 830
T-3/16L	BT2-3/16L	BT3-3/16L	BT4-3/16L	4.7	6.3	108	A	¥ 830
T-7/32L	BT2-7/32L	BT3-7/32L	BT4-7/32L	5.5	6.3	108	A	¥ 830
T-1/4L	BT2-1/4L	BT3-1/4L	BT4-1/4L	6.3	6.3	108	A	¥ 830
T-5/16L		BT3-5/16L	BT4-5/16L	8	8	108	B	¥ 830
T-3/8L		BT3-3/8L	BT4-3/8L	9.5	10	108	B	¥ 890
T-7/16L		BT3-7/16L	BT4-7/16L	11.1	12	108	B	¥ 1,010
T-1/2L			BT4-1/2L	12.7	14	108	B	¥ 1,120
T-9/16L			BT4-9/16L	14.2	17	108	B	¥ 1,160
T-5/8L			BT4-5/8L	15.8	17	108	B	¥ 1,160



■ロングボールポイントヘキサゴンビット



mm

交換ビット 品番	適用品番			S ₁	S ₂	L	タイプ	小売参考 価格
	6.3 sq.	9.5 sq.	12.7 sq.					
T-03BPL	BT2-03BPL	BT3-03BPL		3	6.3	108	A	¥ 1,000
T-04BPL	BT2-04BPL	BT3-04BPL		4	6.3	108	A	¥ 1,000
T-05BPL	BT2-05BPL	BT3-05BPL	BT4-05BPL	5	6.3	108	A	¥ 1,000
T-06BPL	BT2-06BPL	BT3-06BPL	BT4-06BPL	6	6.3	108	A	¥ 1,000
T-07BPL		BT3-07BPL	BT4-07BPL	7	8	108	B	¥ 1,000
T-08BPL		BT3-08BPL	BT4-08BPL	8	8	108	B	¥ 1,000



インチ

■ロングボールポイントヘキサゴンビット



in

交換ビット 品番	適用品番			S ₁	S ₂	L	タイプ	小売参考 価格
	6.3 sq.	9.5 sq.	12.7 sq.					
T-1/8 BPL	BT2-1/8BPL	BT3-1/8BPL		3.1	6.3	108	A	¥ 1,160
T-9/64BPL	BT2-9/64BPL	BT3-9/64BPL		3.6	6.3	108	A	¥ 1,160
T-5/32BPL	BT2-5/32BPL	BT3-5/32BPL		3.9	6.3	108	A	¥ 1,160
T-3/16BPL	BT2-3/16BPL	BT3-3/16BPL	BT4-3/16BPL	4.7	6.3	108	A	¥ 1,160
T-7/32BPL	BT2-7/32BPL	BT3-7/32BPL	BT4-7/32BPL	5.5	6.3	108	A	¥ 1,160
T-1/4BPL	BT2-1/4BPL	BT3-1/4BPL	BT4-1/4BPL	6.3	6.3	108	A	¥ 1,160
T-5/16BPL		BT3-5/16BPL	BT4-5/16BPL	8	8	108	B	¥ 1,160

品名の下に製品の機能を表す機能マークを入れています。マークの意味は P.4~5をご参照ください。

めっきされた製品は手動用です。インパクトレンチ等の動力工具では使用しないでください。

このマークのついている製品は在庫を確認の上ご注文ください。

(マークの例: 9.5 インチ POWERFIT 36 39 リバース 六角 プラス)

表示価格は「小売参考価格」であり消費税は含まれておりません。