




# SUSFBN40B

## ●ご注文No.表記例

**SUSFBN 40B 20 D20**



- チェーン .....No.40
- チェーンピッチ .....(P) 12.70mm
- ローリンク内幅 .....(W) 7.95mm
- ローラ外径 .....(Dr) 7.92mm
- 歯幅 .....(T) 7.2 mm

TYPE	歯数	外径Do	ピッチ径Dp	ボス径BD	ボス長さBL	a	重量kg
<b>SUS FBN 40B</b>	10	46	41.10	★32	22	5	0.14
	11	51	45.08	★36	22	5	0.19
	12	55	49.07	★40	22	5	0.22
	13	59	53.07	37	22	6	0.23
	14	63	57.07	42	22	6	0.28
	15	67	61.08	46	22	6	0.34
	16	71	65.10	50	22	6	0.40
	17	76	69.12	54	22	6	0.46
	18	80	73.14	57	22	6	0.51
	19	84	77.16	62	22	6	0.59
	20	88	81.18	67	25	7	0.76
	21	92	85.21	71	25	7	0.85
	22	96	89.24	75	25	7	0.95
	23	100	93.27	77	25	7	1.00
	24	104	97.30	63	25	7	0.84
	25	108	101.33	63	25	7	0.88
	26	112	105.36	63	25	7	0.92
	28	120	113.43	63	25	7	1.00
	30	128	121.50	63	25	7	1.10
	32	137	129.57	68	28	10	1.30
35	149	141.68	68	28	10	1.40	
36	153	145.72	68	28	10	1.50	
40	169	161.87	68	28	10	1.70	