

ひし形35°・ネガ

(mm)

型番	IC	S	D1
VNGA 1604_	9.525	4.76	3.81

刃先仕様				K											適合ホルダ参照ページ								
記号	切れ刃状態	記入例			H																		
F	シャープエッジ	F	シャープエッジ																				
E	Rホーニング	E008	R0.08mmホーニング																				
T	チャンファ	T01215	0.12mm x 15° チャンファ																				
S	チャンファ+ホーニング	S01225	0.12mm x 25° チャンファ+ホーニング																				
形状		型番		刃先仕様	寸法 (mm)		使用 コーナ 数	MEGACOAT CBN					CBN										
					RE	LE		KBN05M	KBN10M	KBN25M	KBN35M	KBN60M	KBN70M	KBN510		KBN525	KBN475	KBN570					
		VNGA 160404S00545MEP 160408S00545MEP	S00545		0.4 0.8	2.0 1.8	2	●															
		VNGA 160404MEF 160408MEF	F		0.4 0.8	2.0 1.8	2									●	●						
		VNGA 160404ME4 160408ME4	S01225		0.4 0.8	2.0 1.8	4	●															
		VNGA 160401S01225ME 160402S01225ME 160404S01225ME 160408S01225ME	S01225		0.1 0.2 0.4 0.8	2.6 2.3 2.0 1.8	2	○	●	●	●			●	●	●	●						
		VNGA 160404T01215ME 160408T01215ME	T01215		0.4 0.8	2.0 1.8	2						●			●	●						
		VNGA 160404S01730MET 160408S01730MET	S01730		0.4 0.8	2.0 1.8	2	●		●	●				●								
		VNGA 160404S04030MEH 160408S04030MEH	S04030		0.4 0.8	2.0 1.8	2	●															
		VNGA 160401S01225SE 160402S01225SE 160404S01225SE	S01225		0.1 0.2 0.4	2.6 2.3 1.9	1		□					□	□								
		VNGA 160404S01730SET	S01730		0.4	1.9	1								□								

D18
D19
D20

- C B.Nダイヤモンド
- CBN
- ダイヤモンド
- ネガ
- C
- D
- S
- T
- V
- W
- ソリッド
- 溝入れ

CBN・ダイヤモンドの販売個数は、1ケース1個入りです

●：標準在庫（1個入りのみ在庫） ○：準標準在庫（在庫をご確認ください） □：次期カタログより抹消予定