

三角形60°・ポジ

型番	IC	S	(mm)		型番	IC	S	D1
			RE	LE				
TPGB 0802_	4.76	2.38	2.5	3.0	TPGB 1103_	6.35	3.18	3.5
			0902_	5.56	1603_	9.525		4.5
					TPGW 1604_	9.525	4.76	4.4

記号	切れ刃状態	記入例	形状	型番	刃先仕様	寸法 (mm)		使用コーナ数	MEGACOAT CBN							適合ホルダ参照ページ			
						RE	LE		KBN05M	KBN10M	KBN25M	KBN35M	KBN60M	KBN70M	KBN510		KBN525	KBN475	KBN570
F	シャープエッジ	F シャープエッジ		TPGB 110304MEF 110308MEF	F	0.4 0.8	2.1 1.8	3											
E	Rホーニング	E008 R0.08mmホーニング		TPGB 110302T00815ME 110304T00815ME 110308T00815ME	T00815	0.2 0.4 0.8	2.3 2.1 1.8	3	●	○	●	●	●	●	●	●	●	●	●
T	チャンファ	T01215 0.12mm x 15° チャンファ		TPGB 160304T00815ME 160308T00815ME	T00815	0.4 0.8	1.8 1.5	3	●	●	●	□	●					●	●
S	チャンファ+ホーニング	S01225 0.12mm x 25° チャンファ+ホーニング		TPGB 110304S01225MES 110308S01225MES	S01225	0.4 0.8	2.1 1.8	3	●									●	●
				TPGB 110302S01035MET 110304S01035MET 110308S01035MET	S01035	0.2 0.4 0.8	2.3 2.1 1.8	3	●	○	●	●							
				TPGB 160304S01035MET 160308S01035MET	S01035	0.4 0.8	1.8 1.5	3			●	□						●	●
				TPGB 080202T00815SE 080204T00815SE	T00815	0.2 0.4	1.8 1.6	1		○	●							●	●
				TPGB 090202T00815SE 090204T00815SE	T00815	0.2 0.4	1.8 1.6	1		○	○	●						●	●
				TPGB 110302T00815SE 110304T00815SE 110308T00815SE	T00815	0.2 0.4 0.8	1.9 1.8 1.5	1		○								●	●
				TPGB 160302T00815SE 160304T00815SE	T00815	0.2 0.4	1.9 1.8	1										●	●
				TPGB 080202S01035SET 080204S01035SET	S01035	0.2 0.4	1.8 1.6	1			●							●	
				TPGB 090202S01035SET 090204S01035SET	S01035	0.2 0.4	1.8 1.6	1			●							●	
				TPGB 110304S01035SET 110308S01035SET	S01035	0.4 0.8	1.8 1.5	1										●	●
				TPGB 160304S01035SET 160308S01035SET	S01035	0.4 0.8	1.8 1.5	1										●	□
				TPGW 160404T00815ME 160408T00815ME	T00815	0.4 0.8	1.8 1.5	3		○	●								
				TPGW 160404S01035MET 160408S01035MET	S01035	0.4 0.8	1.8 1.5	3			●							●	
				TPGW 160404T00815SE	T00815	0.4	1.8	1										●	

適合ホルダ参照ページ

C15 下表参照

- CBNダイヤモンド
- CBN
- ダイヤモンド
- ポジ
- C
- D
- S
- T
- V
- W
- ソリッド
- 溝入れ

CBN・ダイヤモンドの販売個数は、1ケース1個入りです

●：標準在庫（1個入りのみ在庫） ○：準標準在庫（在庫をご確認ください） □：次期カタログより抹消予定