

ポジ

*厚み記号「01」の厚さが異なります

刃先仕様		ダイヤモンド全般		シャープエッジ		寸法 (mm)					使用コーナ数	ダイヤモンド				適合ホルダ参照ページ		
形状	型番	IC	S	D1	RE	LE	KPD001	KPD010	KPD230	KPD250								
	*CCGW	040101SE	4.3	1.8	2.3	0.1	1.3	●				1	●	●	●	●	F19 F39	
		040102SE				0.2	1.3											
		040104SE				0.4	1.3											
		CCGW	060201SE	6.35	2.38	2.8	0.1	2.3	●				1	●	●	●	●	下表参照
		060202SE	0.2				2.3											
		060204SE	0.4				2.3											
		CCGW	09T302SE	9.525	3.97	4.4	0.2	2.7	●				1	●	●	●	●	下表参照
		09T304SE	0.4				2.7											
		09T308SE	0.8				2.7											
		*CCGW	040101NE	4.3	1.8	2.3	0.1	1.7	●				1	●	●	●	●	F19 F39
			040102NE				0.2	1.6										
			040104NE				0.4	1.6										
		CCGW	060201NE	6.35	2.38	2.8	0.1	3.1	●				1	●	●	●	●	下表参照
		060202NE	0.2				3.0											
		060204NE	0.4				3.0											
		CCGW	09T301NE	9.525	3.97	4.4	0.1	3.4	●				1	●	●	●	●	下表参照
		09T302NE	0.2				3.4											
		09T304NE	0.4				3.4											
		*CCGW	040101	4.3	1.8	2.3	0.1	1.9	●	●			1	●	●	●	●	F19 F39
		040102	0.2				1.9											
		040104	0.4				1.9											
	CCGW	060201	6.35	2.38	2.8	0.1	3.5	●	●			1	●	●	●	●	下表参照	
	060202	0.2				3.5												
	060204	0.4				3.5												
	CCGW	09T301	9.525	3.97	4.4	0.1	3.8	●	□			1	●	●	●	●	下表参照	
	09T302	0.2				3.8												
	09T304	0.4				3.7												
	09T308	0.8	3.6					●										
	CCMT	060202SE	6.35	2.38	2.8	0.2	2.2	●				1	●	●	●	●	下表参照	
		060204SE				0.4	2.2											
		CCMT	09T301SE	9.525	3.97	4.4	0.1	2.7	●				1	●	●	●	●	下表参照
		09T302SE	0.2				2.7											
		09T304SE	0.4				2.7											
		09T308SE	0.8	2.7					●									
		CCMT	060201NE	6.35	2.38	2.8	0.1	2.8	●				1	●	●	●	●	下表参照
		060202NE	0.2				2.8											
		060204NE	0.4				2.8											
		CCMT	09T301NE	9.525	3.97	4.4	0.1	3.4	●				1	●	●	●	●	下表参照
		09T302NE	0.2				3.4											
		09T304NE	0.4				3.4											
	09T308NE	0.8	3.3					●										
	CCMT	060201	6.35	2.38	2.8	0.1	3.3	●	●			1	●	●	●	●	下表参照	
	060202	0.2				3.3												
	060204	0.4				3.2												
	CCMT	09T301	9.525	3.97	4.4	0.1	3.9	●	●			1	●	●	●	●	下表参照	
	09T302	0.2				3.9												
	09T304	0.4				3.9												
	09T308	0.8	3.8					●										

・型番末尾のSEはスモールエッジ、NEはニューバリューエッジを示します。

チップ型番	適合ホルダ参照ページ
CC..0602タイプ	E22,E23,E37,F19,F39
CC..09T3タイプ	E22,E23,E37,F39,F65

CBN・ダイヤモンドの販売個数は、1ケース1個入りです