

● ホルダ寸法

型 番		在庫		最小 加工径	寸 法 (mm)						GAMO	基準 コーナ R (RE)	ク ラ ン ト ホ ール	形 状	部 品														
		R	L		DMIN	DCON	H	LF	LH	WF					WF ₂														
エクセ レント バー	S06H-STLB ^{R/L} 06-08AE	●	●	8	6	5	100	12	3.8	0.5	12°	0.2	無	Fig. 1	SB-2035TR	FT-6													
	A08X-STLP ^{R/L} 08-10AE	●	●	10	8	7	120	16	5	0.5	10°	0.4	有	Fig. 2	SB-1TR														
	A08X-STLP ^{R/L} 09-10AE	●	●												SB-2545TR	FT-8													
	A10L-STLP ^{R/L} 09-12AE	●	●	12	10	9	140	20	6.2	0.9	8°																		
	A10L-STLP ^{R/L} 11-12AE	●	●						6	0.7	10°																		
	A12M-STLP ^{R/L} 11-14AE	●	●	14					7.2	0.8	7°					SB-3060TR	FT-10												
	A12M-STLP ^{R/L} 09-16AE	●	●	16	12	11	150	24	8	0.6	5°					SB-2545TR	FT-8												
	A16Q-STLP ^{R/L} 11-18AE	●	●	18	16	15	180	30	9.2		3.5°					SB-3060TR	FT-10												
	A20R-STLP ^{R/L} 11-22AE	●	●	22	20	19	200	36	11.2		2°																		
	A20R-STLP ^{R/L} 16-25AE	●	●	25					13																				
A25S-STLP ^{R/L} 16-27AE	●	●	27	25	24	250	46	13.7		0°						SB-4065TR	FT-15												
鋼	S06H-STLB ^{R/L} 06-08A	●	●	8	6	5	100	12	3.8	0.5	12°	0.2	0.4	無	Fig. 3	SB-2035TR	FT-6												
	S08X-STLP ^{R/L} 08-10A	●	●	10	8	7	120	16	5	0.5	10°					SB-1TR													
	S08X-STLP ^{R/L} 09-10A	●	●									SB-2545TR				FT-8													
	S10L-STLP ^{R/L} 09-12A	●	●	12	10	9	140	20	6.2	0.9	8°																		
	S10L-STLP ^{R/L} 11-12A	●	●						6	0.7	10°																		
	S12M-STLP ^{R/L} 11-14A	●	●	14	12	11	150	24	7.2	0.8	7°					SB-3060TR	FT-10												
	S12M-STLP ^{R/L} 09-16A	●	●	16					8	0.6	5°					SB-2545TR	FT-8												
	S16Q-STLP ^{R/L} 11-18A	●	●	18	16	15	180	30	9.2		3.5°					SB-3060TR	FT-10												
	S20R-STLP ^{R/L} 11-22A	●	●	22	20	19	200	36	11.2	0.7	2°																		
	S25S-STLP ^{R/L} 16-27A	●	●	27	25	24	250	46	13.7		0°						SB-4065TR	FT-15											
超 硬	C06J-STLB ^{R/L} 06-08AN	●	●	8	6	5.4	110	10	3.8	0.5	12°	0.2	無	Fig. 5	SB-2035TR	FT-6													
	E08L-STLP ^{R/L} 08-10AN	●	●	10	8	7	140	14	5	0.5	10°	0.4	有	Fig. 6	SB-1TR														
	E08L-STLP ^{R/L} 09-10AN	●	●																										
	E10N-STLP ^{R/L} 09-12AN	●	●	12	10	9	160	18	6.2	0.9	8°							SB-2545TR	FT-8										
	E10N-STLPR09-12AN2/3	●																											
	E10N-STLPR09-12AN1/2	●																											
	E10N-STLP ^{R/L} 11-12AN	●	●																										
	E10N-STLPR11-12AN2/3	●		14	12	11	105	23	6	0.7	10°							SB-3060TR	FT-10										
	E10N-STLPR11-12AN1/2	●																											
	E12Q-STLP ^{R/L} 11-14A	●	●																										
	E12Q-STLPR 11-14A-2/3	●																											
	E12Q-STLPR 11-14A-1/2	●		16	12	11	90	23	7.2	0.8	7°																		
	E12Q-STLP ^{R/L} 09-16A	●	●																										
	E12Q-STLPR 09-16A-2/3	●																											
	E12Q-STLPR 09-16A-1/2	●																											
	E16X-STLP ^{R/L} 11-18A	●	●	18	16	15	220	28	9.2		3.5°								SB-3060TR	FT-10									
	E16X-STLPR 11-18A-2/3	●																											
	E16X-STLPR 11-18A-1/2	●																											
	E20S-STLP ^{R/L} 11-22A	●	●																										
	E20S-STLPR 11-22A-2/3	●		22	20	19	165	32	11.2		2°																		
	E20S-STLPR 11-22A-1/2	●																											
	E20S-STLP ^{R/L} 16-25A	●	●																										
	E20S-STLPR 16-25A-2/3	●																											
	E20S-STLPR 16-25A-1/2	●		25	20	19	125	32	13		0°								SB-4065TR	FT-15									
	E20S-STLP ^{R/L} 16-25A	●	●																										
	E20S-STLPR 16-25A-2/3	●																											
E20S-STLPR 16-25A-1/2	●																												
E25T-STLP ^{R/L} 16-27A	●	●	27	25	24	300	38	13.7																					
E25T-STLPR 16-27A-2/3	●																												

●：標準在庫

チップ材種 旋削チップ CBNダイヤモンド 外径 スモールツール 内径 溝入れ 突切り ねじ切り ドリル ソリッドツール ミーリング ツーリング 機器 イシヤシヤ 部品 技術資料 SICKセミコン 索引