


## SS-DRA(加工深さ : 5 x DC)



# 5D

・PLはチップ先端からコーナまでの距離を示す ● K6~K9 参照

### ● ホルダ寸法

型番	在庫	寸法(mm)						部品		適合チップ ● K6~K9
		適合チップサイズ DC		DCON (h6)	OAL	LU	LS	止めねじ	レンチ	
		min.	max.							
SS10- DRA080M-5	●	7.94	8.49	10	96	42.5	40	HS-2524TRP	FTP-5	DA0794M-...~DA0840M-...
	●	8.50	8.99		99	45.0				DA0850M-...~DA0890M-...
	●	9.00	9.49		102	47.5				DA0900M-...~DA0940M-...
	●	9.50	9.99		105	50.0				DA0950M-...~DA0990M-...
SS12- DRA100M-5	●	10.00	10.49	12	113	52.5	45	HS-2534TRP	FTP-5	DA1000M-...~DA1040M-...
	●	10.50	10.99		116	55.0				DA1050M-...~DA1090M-...
	●	11.00	11.49		120	57.5				DA1100M-...~DA1140M-...
	●	11.50	11.99		123	60.0				DA1150M-...~DA1190M-...
SS14- DRA120M-5	●	12.00	12.49	14	126	62.5	48	HS-3048TRP	DTP-6	DA1200M-...~DA1240M-...
	●	12.50	12.99		129	65.0				DA1250M-...~DA1290M-...
	●	13.00	13.49		132	67.5				DA1300M-...~DA1340M-...
	●	13.50	13.99		135	70.0				DA1350M-...~DA1390M-...
SS16- DRA140M-5	●	14.00	14.49	16	141	72.5	50	HS-4067TRP	DTP-7	DA1400M-...~DA1440M-...
	●	14.50	14.99		144	75.0				DA1450M-...~DA1490M-...
	●	15.00	15.99		151	80.0				DA1500M-...~DA1590M-...
SS18- DRA160M-5	●	16.00	16.99	18	158	85.0	56	HS-4067TRP	DTP-7	DA1600M-...~DA1690M-...
	●	17.00	17.99		164	90.0				DA1700M-...~DA1790M-...
SS20- DRA180M-5	●	18.00	18.99	20	173	95.0	60	HS-4067TRP	DTP-7	DA1800M-...~DA1890M-...
	●	19.00	19.99		179	100.0				DA1900M-...~DA1990M-...
SS25- DRA200M-5	●	20.00	20.99	25	191	105.0	60	HS-4067TRP	DTP-7	DA2000M-...~DA2090M-...
	●	21.00	21.99		197	110.0				DA2100M-...~DA2150M-...
	●	22.00	22.99		204	115.0				DA2200M-...~DA2250M-...
	●	23.00	23.99		210	120.0				DA2300M-...~DA2350M-...
SS32- DRA240M-5	●	24.00	24.99	32	216	125.0	60	HS-4067TRP	DTP-7	DA2400M-...~DA2450M-...
●	25.00	25.50	226		130.0	DA2500M-...~DA2550M-...				

● : 標準在庫