

# ねじ規格

形状	型番	在庫	寸法 (mm)							角度		トルク (N·m)	備考
			A	B	C	D	E	F	α	θ			
	AJ -6X38	●	M6X1.0	38.0	6.0	10.0	3.0	3.0	-	-	-		
	-8X44-9.5	●	M8X1.25	44.0	9.5	6.0	4.0	4.0	-	-	-		
	-10X46	●	M10X1.5	46.0	11.5	8.0	5.0	5.0	-	-	-		
	AJ -519TR	●	M5X0.8	19.0	10.0	-	T15	-	-	40°	-		
	BH 3X6	●	M3X0.5	6.0	-	2.0	2.0	-	-	-	-		
	3X12	●	M3X0.5	12.0	-	2.0	2.0	-	-	-	-		
	6X25	●	M6X1.0	25.0	-	4.0	4.0	-	-	-	-		
	BH 6X10TR	●	M6X1.0	10.0	12.0	5.0	T25	-	-	-	6.5		
	CP 8X15TL	●	M8X1.25	15.0	15.0	-	T25	-	-	-	-	6.0	L…左ねじを示す
	8X23TL	●		23.0									
	CS -2D	●	M4X0.7	21.5	6.4	3.5	2.5	2.0	-	-	1.7		
	-3D	●	M5X0.8	22.0	8.0	4.0	3.0	2.5	-	-	3.9		
	-5D	●	M5X0.8	28.0	8.0	4.0	3.0	2.5	-	-	3.0		
	CS -3D-TR	●	M5X0.8	22.0	8.0	4.0	T15	T15	-	-	3.9		
	GS -50	●	M5X0.8	13.0	7.5	-	3.0	-	-	82°	-		
	HF 16X40HA	●	M16X2.0	24.0	40.0	16.0	12.0	10.0	14.0	-	-	-	クーラント用穴付き
	20X53H	●	M20X2.5	35.0	43.0	18.0	14.0						
	20X53HA	●		33.0	50.0	20.0							
	24X60H	●	M24X3.0	40.5	65.0	19.5	17.0						
	24X60HA	●		36.0		24.0							
HF 16X40S	●	M16X2.0	29.0	40.0	11.0	14.0	10.0	-	-	-			
	HH 3X6	●	M3X0.5	6.0	5.5	3.0	2.5	-	-	-	-		
	3X12	●		12.0									
	HH 4X16	●	M4X0.7	16.0	7.0	4.0	3.0	-	-	-			
	HH 5X15	●	M5X0.8	15.0	8.5	5.0	4.0	-	-	-			
	5X16	●		16.0									
	5X20	●		20.0									
	5X25	●		25.0									
	5X30	●		30.0									
	HH 6X12	●		12.0									
	HH 6X16	●	16.0										
	HH 6X16A	●	16.0										
	HH 6X18	●	M6X1.0	18.0	10.0	6.0	5.0	-	-	-			
	HH 6X18A	●		18.0									
	HH 6X20	●		20.0									
	HH 6X25	●		25.0									
	HH 6X30	●	30.0										
HH 8X20	●	M8X1.25	20.0	13.0	8.0	6.0	-	-	-				
HH 8X25	●		25.0										

●：標準在庫

P

品名