

一般圧力計

製作仕様

形状			型番				性能			
大きさ	ケース形状	接続部	金属ケース				蒸気用	耐熱用	耐振用	
			一般用		耐食用		M	H	V	
60φ	A	-	G	G211-111		G211-131		○	○	○
			R	112		132				
	B	取付穴	G	G221-111		G221-131				
			R	112		132				
	D	前フランジ	G	G232-111		G232-131				
			R	112		132				
	中間フランジ	G	G233-111		G233-131					
		R	112		132					
75φ	A	-	1/4	G	G311-111		G311-131			
			R	112		132				
		3/8	G	G311-211		G311-231				
		R	212		232					
	B	取付穴	1/4	G	G321-111		G321-131			
			R	112		132				
		3/8	G	G321-211		G321-231				
		R	212		232					
	D	前フランジ	1/4	G	G332-111		G332-131			
			R	112		132				
		3/8	G	G332-211		G332-231				
		R	212		232					
中間フランジ	1/4	G	G333-111		G333-131					
	R	112		132						
	3/8	G	G333-211		G333-231					
	R	212		232						
100φ	A	-	3/8	G	G411-211		G411-231			
			R	212		232				
		1/2	G	G411-311		G411-331				
		R	312		332					
	B	取付穴	3/8	G	G421-211		G421-231			
			R	212		232				
		1/2	G	G421-311		G421-331				
		R	312		332					
	D	前フランジ	3/8	G	G432-211		G432-231			
			R	212		232				
		1/2	G	G432-311		G432-331				
		R	312		332					
中間フランジ	3/8	G	G433-211		G433-231					
	R	212		232						
	1/2	G	G433-311		G433-331					
	R	312		332						
150φ	A	-	3/8	G	G611-211		G611-231			
			R	212		232				
		1/2	G	G611-311		G611-331				
		R	312		332					
	B	取付穴	3/8	G	G621-211		G621-231			
			R	212		232				
		1/2	G	G621-311		G621-331				
		R	312		332					
	D	前フランジ	3/8	G	G632-211		G632-231			
			R	212		232				
		1/2	G	G632-311		G632-331				
		R	312		332					
中間フランジ	3/8	G	G633-211		G633-231					
	R	212		232						
	1/2	G	G633-311		G633-331					
	R	312		332						
200φ	A	-	3/8	G	G811-211		-			
			R	212		-				
		1/2	G	G811-311		-				
			R	312		-				
	B	取付穴	3/8	G	G821-211		-			
			R	212		-				
1/2		G	G821-311		-					
		R	312		-					

▼ 圧力指示計

▼ 一般圧力計