

S3M寸法一覧表

〈S3M0100A〉 選択可能な材質：アルミ

歯数	寸法(mm)							適応軸穴径 (mm) ※軸穴公差H7																													
	PD	OD	LA	W	H	F	M																														
24	22.92	22.16	15	11	2	26	16	4	5	6	6.35	7	8	9																							
25	23.87	23.11				28	18	6	6.35	7	8	9																									
26	24.83	24.07				28	18	6	6.35	7	8	9																									
28	26.74	25.98				31	20	6	6.35	7	8	9	10	11																							
30	28.65	27.89				33	22	6	6.35	7	8	9	10	11	12																						
32	30.56	29.80				35	22	6	6.35	7	8	9	10	11	12																						
36	34.38	33.62				40	28	6	6.35	7	8	9	10	11	12	14	15	16																			
40	38.20	37.44				44	32	8	9	10	11	12	14	15	16	17																					
44	42.02	41.25				47	34	8	9	10	11	12	14	15	16	17	18	19	20																		
48	45.84	45.07				48	36	8	9	10	11	12	14	15	16	17	18	19	20	22																	
50	47.75	46.98				51	36	8	9	10	11	12	14	15	16	17	18	19	20	22	24	25															
60	57.30	56.53				61	41	8	9	10	11	12	14	15	16	17	18	19	20	22	24	25	28	30													

〈S3M0100B〉 選択可能な材質：アルミ

歯数	寸法(mm)								適応軸穴径 (mm) ※軸穴公差H7																												
	PD	OD	LA	LB	W	H	K	D	F	M																											
24	22.92	22.16	15	23	11	2	8	14	26	16	4	5	6																								
25	23.87	23.11						16	28	18	6	6.35	7	8																							
26	24.83	24.07						16	28	18	6	6.35	7	8																							
28	26.74	25.98						18	31	20	6	6.35	7	8	9																						
30	28.65	27.89						20	33	22	6	6.35	7	8	9																						
32	30.56	29.80						20	35	22	6	6.35	7	8	9																						
36	34.38	33.62						26	40	28	6	6.35	7	8	9	10	11	12																			
40	38.20	37.44						30	44	32	8	9	10	11	12	14	15																				
44	42.02	41.25						32	47	34	8	9	10	11	12	14	15	16	17																		
48	45.84	45.07						34	48	36	8	9	10	11	12	14	15	16	17																		
50	47.75	46.98						34	51	36	8	9	10	11	12	14	15	16	17																		
60	57.30	56.53						39	61	41	8	9	10	11	12	14	15	16	17	18	19	20															

〈S3M0100C〉 選択可能な材質：アルミ

歯数	寸法(mm)							適応軸穴径 (mm) ※軸穴公差H7													
	PD	OD	LA	LB	W	H	K	D	F	M											
14	13.37	12.61	15	23	11	2	10	16	16	10	4	5	6	6.35	7	8					
15	14.32	13.56						18	18	11	4	5	6	6.35	7	8					
16	15.28	14.52						20	20	12	4	5	6	6.35	7	8					
18	17.19	16.43						23	23	12	4	5	6	6.35	7	8					
20	19.10	18.34						23	23	13	4	5	6	6.35	7	8	9				
22	21.01	20.25						25	25	14	4	5	6	6.35	7	8	9				

※青塗部はタップ長さが不足する為、準標準のセットスクリーンが付属されます。(P3 参照)

●製品コード例

