

S5M寸法一覧表

〈S5M0100A〉 選択可能な材質：アルミ

歯数	寸法(mm)						適応軸穴径 (mm) ※軸穴公差H7																										
	PD	OD	LA	W	H	F	M																										
14	22.28	21.32	16	11	2.5	26	16	7	8																								
15	23.87	22.91				28	18	7	8																								
16	25.46	24.5				31	20	7	8	9																							
18	28.65	27.69				33	22	7	8	9	10	11																					
20	31.83	30.87				35	22	7	8	9	10	11	12																				
22	35.01	34.05				40	28	7	8	9	10	11	12	14	15																		
24	38.2	37.24				44	32	7	8	9	10	11	12	14	15	16	17																
25	39.79	38.83				44	32	7	8	9	10	11	12	14	15	16	17																
26	41.38	40.42				47	34	8	9	10	11	12	14	15	16	17	18																
28	44.56	43.6				48	36	8	9	10	11	12	14	15	16	17	18	19	20														
30	47.75	46.79				51	36	10	11	12	14	15	16	17	18	19	20	22															
32	50.93	49.97				54	41	10	11	12	14	15	16	17	18	19	20	22	24	25													
36	57.3	56.34				61	41	10	11	12	14	15	16	17	18	19	20	22	24	25	28												
40	63.66	62.7				69	50	10	11	12	14	15	16	17	18	19	20	22	24	25	28	30	32										
44	70.03	69.07				74	53	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38										
48	76.39	75.43				83	63	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42								
50	79.58	78.62				86	66	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45							
60	95.49	94.53				99	78	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50					

〈S5M0100B〉 選択可能な材質：アルミ

歯数	寸法(mm)										適応軸穴径 (mm) ※軸穴公差H7																									
	PD	OD	LA	LB	W	H	K	D	F	M																										
15	23.87	22.91	16	28	11	2.5	12	15	28	18	7																									
16	25.46	24.5						17	31	20	7	8	9																							
18	28.65	27.69						19	33	22	7	8	9																							
20	31.83	30.87						19	35	22	7	8	9																							
22	35.01	34.05						25	40	28	7	8	9	10	11	12																				
24	38.2	37.24						29	44	32	7	8	9	10	11	12	14	15																		
25	39.79	38.83						29	44	32	7	8	9	10	11	12	14	15																		
26	41.38	40.42						31	47	34	8	9	10	11	12	14	15	16	17																	
28	44.56	43.6						33	48	36	8	9	10	11	12	14	15	16	17																	
30	47.75	46.79						33	51	36	10	11	12	14	15	16	17																			
32	50.93	49.97						38	54	41	10	11	12	14	15	16	17	18	19	20																
36	57.3	56.34						38	61	41	10	11	12	14	15	16	17	18	19	20																
40	63.66	62.7						47	69	50	10	11	12	14	15	16	17	18	19	20	22	24	25	28												
44	70.03	69.07						50	74	53	12	14	15	16	17	18	19	20	22	24	25	28	30													
48	76.39	75.43						60	83	63	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38										
50	79.58	78.62						63	86	66	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40									
60	95.49	94.53						75	99	78	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50					

〈S5M0150A〉 選択可能な材質：鋼材、アルミ

歯数	寸法(mm)						適応軸穴径 (mm) ※軸穴公差H7																										
	PD	OD	LA	W	H	F	M																										
14	22.28	21.32	22	17	2.5	26	16	7	8																								
15	23.87	22.91				28	18	7	8																								
16	25.46	24.5				31	20	7	8	9																							
18	28.65	27.69				33	22	7	8	9	10	11																					
20	31.83	30.87				35	22	7	8	9	10	11	12																				
22	35.01	34.05				40	28	7	8	9	10	11	12	14	15																		
24	38.2	37.24				44	32	7	8	9	10	11	12	14	15	16	17																
25	39.79	38.83				44	32	7	8	9	10	11	12	14	15	16	17																
26	41.38	40.42				47	34	8	9	10	11	12	14	15	16	17	18																
28	44.56	43.6				48	36	8	9	10	11	12	14	15	16	17	18	19	20														
30	47.75	46.79				51	36	10	11	12	14	15	16	17	18	19	20	22															
32	50.93	49.97				54	41	10	11	12	14	15	16	17	18	19	20	22	24	25													
36	57.3	56.34				61	41	10	11	12	14	15	16	17	18	19	20	22	24	25	28												
40	63.66	62.7				69	50	10	11	12	14	15	16	17	18	19	20	22	24	25	28	30	32										
44	70.03	69.07				74	53	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38										
48	76.39	75.43				83	63	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42								
50	79.58	78.62				86	66	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45							
60	95.49	94.53				99	78	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50					

※青塗部はタップ長さが不足する為、準標準のセットスクリューが付属されます。(P3 参照)

●製品コード例

S2 - **44** **S5M** **0150** **A** **F** - **20** **T3** **X**

- ブリー歯数
 - ブリー歯形
 - ブリー呼び幅 (使用ベルト幅mm×10)
 - ブリー形状
 - 軸穴径(mm) 例) φ7は07と記入
 - フランジ P.3 表2参照
 - キー溝(US9公差) P.3 表3参照
 - タップ加工 P.3 表3参照
- S1: 鋼材+表面処理無し
 S2: 鋼材+黒染
 S3: 鋼材+無電解ニッケルメッキ
 A1: アルミ+表面処理無し
 A4: アルミ+白アルマイト